

4

3

2




1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.




LOC	DIST	REVISIONS						
		P	LTR	DESCRIPTION	ECN	DATE	DWN	APVD
			F1	ADD TYPE	ECO-06-018202	14-JUL-06	KY.DU	N.F
			F2	REMOVE CONTACT FIGURE	ECO-07-014825	22-JUN-07	Y.ZX	Y.BH



VIEW C

CONNECTION DIAGRAM (BOTTOM VIEW)
結線図 (底面図)

DRILLING DIAGRAM (BOTTOM VIEW)
基板加工図 (底面図)



NOTES:

1. TERMINAL DIMENSIONS BEFORE SOLDER DIP
端子寸法は予備半田前の寸法

2. LAST SUFFIX
NON : WASHABLE TYPE
無し : 半田付け後PC基板洗浄可能な型

3. LOT NUMBERING SYSTEM AS FOLLOWS:
ロットNo. 表示法




Diagram dimension 作図寸法	Tolerance 公差
0.99mm max.	±0.1mm
1 - 2.99mm	±0.2mm
3mm min.	±0.3mm

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN	H.SASAKI	Tyco Electronics (Shenzhen) Co.,Ltd	
DIMENSIONS: mm		CHK	N.FUNAYAMA		
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ±		APVD	A.NAGAI	NAME PCH-L2MH CUSTOMER DRAWING	
MATERIAL SEE MATERIAL TABLE		PRODUCT SPEC	—	SIZE	A3
FINISH —		APPLICATION SPEC	—	CAGE CODE	00779
		WEIGHT	—	DRAWING NO	1461353
		CUSTOMER DRAWING		RESTRICTED TO	—
		SCALE	5:1	SHEET	1 OF 2
				REV	F2

4

3

2

1



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS						
		P	LTR	DESCRIPTION	ECN	DATE	DWN	APVD
HB								

Ⓕ	1461353-8	PCH-118L2M,000	107-79019 (TRAY)	108-79670	18V	PCH-118L2MH	h
Ⓑ	1461353-7	PCH-105L2MH,000M	107-79046 (TUBE) Ⓑ	108-79665	5V	PCH-105L2MH	g
	1461353-6	PCH-124L2MH,000	107-79019 (TRAY)	108-79669	24V	PCH-124L2MH	f
	1461353-5	PCH-112L2MH,000	107-79019 (TRAY)	108-79668	12V	PCH-112L2MH	e
	1461353-4	PCH-109L2MH,000	107-79019 (TRAY)	108-79667	9V	PCH-109L2MH	d
	1461353-3	PCH-106L2MH,000	107-79019 (TRAY)	108-79666	6V	PCH-106L2MH	c
	1461353-2	PCH-105L2MH,000	107-79019 (TRAY)	108-79665	5V	PCH-105L2MH	b
	1461353-1	PCH-103L2MH,000	107-79019 (TRAY)	108-79664	3V	PCH-103L2MH	a
	AMP PART NO	EC TYPE NAME	PACKING SPECIFICATION	PRODUCT SPEC	PART B	PART A	TYPE

RELAY TYPE

AR	AR	AR	AR	AR	AR	AR	AR	AR			UV RESIN	UV SEAL(VENT HOLE)	16
AR	AR	AR	AR	AR	AR	AR	AR	AR			EPOXY RESIN	SEAL	15
AR	AR	AR	AR	AR	AR	AR	AR	AR	CLASS E		UEW	MAGNETIC WIRE	14
2	2	2	2	2	2	2	2	2		SOLDER DIP	CP WIRE	COIL TERMINAL	13
1	1	1	1	1	1	1	1	1			Ag ALLOY	STATONARY CONTACT	12
1	1	1	1	1	1	1	1	1			Ag ALLOY	MOVABLE CONTACT	11
1	1	1	1	1	1	1	1	1			Cu ALLOY	HINGE SPRING	10
1	1	1	1	1	1	1	1	1		SOLDER DIP	Cu ALLOY	NO TERMINAL	9
1	1	1	1	1	1	1	1	1		SOLDER DIP	Cu ALLOY	MOVABLE SPRING	8
1	1	1	1	1	1	1	1	1	UL 94V-0		PA NYLON	CARD	7
1	1	1	1	1	1	1	1	1	UL 94V-0		PBT	CASE	6
1	1	1	1	1	1	1	1	1	UL 94HB		PA NYLON	BOBBIN	5
1	1	1	1	1	1	1	1	1	UL 94V-0		PBT	BASE	4
1	1	1	1	1	1	1	1	1		Ni PLATED	STEEL	CORE	3
1	1	1	1	1	1	1	1	1		CuNi PLATED	STEEL	ARMATURE	2
1	1	1	1	1	1	1	1	1		CuNi PLATED	STEEL	YOKE	1
h	g	f	e	d	c	b	a		INCOMBUSTIBILITY	TREATMENT	MATERIAL	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN		 Tyco Electronics (Shenzhen) Co.,Ltd					
DIMENSIONS: mm		CHK							
		APVD		NAME					
		PRODUCT SPEC		PCH-L2MH CUSTOMER DRAWING					
MATERIAL SEE MATERIAL TABLE		FINISH		APPLICATION SPEC		DRAWING NO		RESTRICTED TO	
		—		—		C- 1461353			
		WEIGHT		SIZE		CAGE CODE		SHEET	
		—		A3		00779		2 OF 2	
		CUSTOMER DRAWING		SCALE		REV		F2	
				5:1		F2			