



RECOMMENDED PC BOARD MOUNTING DIMENSIONS
 FOR .063 [1.60] THICK PC BOARD AND
 .012 [.305] STENCIL THICK.

- ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS
- TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADERS ARE HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD
- MATERIAL: HOUSING - LCP, COLOR: BLACK.
POSTS - PHOSPHOR BRONZE
- 0.000127 [.000005] GOLD IN CONTACT AREA,
0.00254-0.00508 [.0000100-.0000200] MATTE TIN-LEAD ON SOLDER TAIL,
ALL OVER 0.00127 [.000050] NICKEL.
- THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING
- 0.000127 [.000005] GOLD IN CONTACT AREA,
0.00254-0.00508 [.0000100-.0000200] MATTE TIN ON SOLDER TAIL,
ALL OVER 0.00127 [.000050] NICKEL.

PLATING	C	B	A	NO. OF POSITIONS	PART NUMBER	PLATING	C	B	A	NO. OF POSITIONS	PART NUMBER
6	101.19	99.06	39	40	9-146279-0	4	101.19	99.06	39	40	4-146279-0
6	98.65	96.52	38	39	8-146279-9	4	98.65	96.52	38	39	3-146279-9
6	96.11	93.98	37	38	8-146279-8	4	96.11	93.98	37	38	3-146279-8
6	93.57	91.44	36	37	8-146279-7	4	93.57	91.44	36	37	3-146279-7
6	91.03	88.90	35	36	8-146279-6	4	91.03	88.90	35	36	3-146279-6
6	88.49	86.36	34	35	8-146279-5	4	88.49	86.36	34	35	3-146279-5
6	85.95	83.82	33	34	8-146279-4	4	85.95	83.82	33	34	3-146279-4
6	83.41	81.28	32	33	8-146279-3	4	83.41	81.28	32	33	3-146279-3
6	80.87	78.74	31	32	8-146279-2	4	80.87	78.74	31	32	3-146279-2
6	78.33	76.20	30	31	8-146279-1	4	78.33	76.20	30	31	3-146279-1
6	75.79	73.66	29	30	8-146279-0	4	75.79	73.66	29	30	3-146279-0
6	73.25	71.12	28	29	7-146279-9	4	73.25	71.12	28	29	2-146279-9
6	70.71	68.58	27	28	7-146279-8	4	70.71	68.58	27	28	2-146279-8
6	68.17	66.04	26	27	7-146279-7	4	68.17	66.04	26	27	2-146279-7
6	65.63	63.5	25	26	7-146279-6	4	65.63	63.5	25	26	2-146279-6
6	63.09	60.96	24	25	7-146279-5	4	63.09	60.96	24	25	2-146279-5
6	60.55	58.42	23	24	7-146279-4	4	60.55	58.42	23	24	2-146279-4
6	58.01	55.88	22	23	7-146279-3	4	58.01	55.88	22	23	2-146279-3
6	55.47	53.34	21	22	7-146279-2	4	55.47	53.34	21	22	2-146279-2
6	52.93	50.80	20	21	7-146279-1	4	52.93	50.80	20	21	2-146279-1
6	50.39	48.26	19	20	7-146279-0	4	50.39	48.26	19	20	2-146279-0
6	47.85	45.72	18	19	6-146279-9	4	47.85	45.72	18	19	1-146279-9
6	45.31	43.18	17	18	6-146279-8	4	45.31	43.18	17	18	1-146279-8
6	42.77	40.64	16	17	6-146279-7	4	42.77	40.64	16	17	1-146279-7
6	40.23	38.10	15	16	6-146279-6	4	40.23	38.10	15	16	1-146279-6
6	37.69	35.56	14	15	6-146279-5	4	37.69	35.56	14	15	1-146279-5
6	35.15	33.02	13	14	6-146279-4	4	35.15	33.02	13	14	1-146279-4
6	32.61	30.48	12	13	6-146279-3	4	32.61	30.48	12	13	1-146279-3
6	30.07	27.94	11	12	6-146279-2	4	30.07	27.94	11	12	1-146279-2
6	27.53	25.40	10	11	6-146279-1	4	27.53	25.40	10	11	1-146279-1
6	24.99	22.86	9	10	6-146279-0	4	24.99	22.86	9	10	1-146279-0
6	22.45	20.32	8	9	5-146279-9	4	22.45	20.32	8	9	146279-9
6	19.91	17.78	7	8	5-146279-8	4	19.91	17.78	7	8	146279-8
6	17.37	15.24	6	7	5-146279-7	4	17.37	15.24	6	7	146279-7
6	14.83	12.70	5	6	5-146279-6	4	14.83	12.70	5	6	146279-6
6	12.29	10.16	4	5	5-146279-5	4	12.29	10.16	4	5	146279-5
6	9.75	7.62	3	4	5-146279-4	4	9.75	7.62	3	4	146279-4
6	7.21	5.08	2	3	5-146279-3	4	7.21	5.08	2	3	146279-3
6	4.67	2.54	1	2	5-146279-2	4	4.67	2.54	1	2	146279-2
6	2.13	-	0	1	5-146279-1	4	2.13	-	0	1	146279-1

THIS DRAWING IS A CONTROLLED DOCUMENT. DWN T. HOFFMAN 6/12/95
 CHK G. DUBNICZKI 3/18/96
 APD G. DUBNICZKI 3/18/96

tyco Electronics Tyco Electronics Corporation
 Harrisburg, Pa 17105-3608

PRODUCT SPEC: HEADER ASSEMBLY, MOD II, BREAKWAY,
 SINGLE ROW, HIGH TEMPERATURE, VERTICAL
 W/.025 SQ POSTS, .100 C

SIZE: A1 CAGE CODE: 00779 DRAWING NO: 146279
 WEIGHT: - RESTRICTED TO: -

MATERIAL: 3 SEE TABLE CUSTOMER DRAWING SCALE: 4:1 SHEET: 1 OF 1 REV: F