


Inductors

Military, MIL-PRF-15305 Qualified, Type LT and Commercial, Molded



FEATURES

- Wide inductance range in small package.
- Flame retardant coating.
- Precision performance, excellent reliability, sturdy construction.
- Epoxy molded construction provides superior moisture protection.

INDUCTANCE RANGE AND MILITARY STANDARD					
MODEL	INDUCTANCE RANGE Mil. Range in bold face		CLASSIFICATION		MILITARY STANDARD
	FROM	TO	GRADE	CLASS	
IM-1	0.10 μ H	100 μ H	—	—	—
IM-2	0.022 μ H	0.082 μ H	—	—	—
	0.10μH	1μH	1	B	MS75083
	1.2μH	27μH	1	A	MS75084
IM-4	33μH	1000μH	1	A	MS75085
	0.15μH	4.7μH	1	B	MS18130
	5.6μH	33μH	1	A	MS14046
	36μH	240μH	1	A	MS90538
IM-6	0.10 μ H	2.7 μ H	1	B	MS75008 Not QPL'd
	3.3μH	27μH	1	A	MS75101
	33 μ H	220 μ H	—	—	—
IM-8	270 μ H	1000 μ H	1	A	MS90539 Not QPL'd
	1100 μ H	3600 μ H	1	A	MS90540 Not QPL'd
IM-9	68 μ H	150 μ H	1	A	MS14047 Not QPL'd
IM-10	3900 μ H	10,000 μ H	1	A	MS90541 Not QPL'd

ELECTRICAL SPECIFICATIONS

Inductance Tolerance: $\pm 1\%$, $\pm 3\%$, $\pm 5\%$, $\pm 10\%$, $\pm 20\%$. Other tolerances available on request.

Insulation Resistance: 1000 Megohm minimum per MIL-STD-202, Method 302, Test Condition B.

Dielectric Strength: Per MIL-STD-202, Method 301: 1000 VAC for IM-2, -4, -6, -8, -9 and -10. 200 VAC for IM-1.

MECHANICAL SPECIFICATIONS

Terminal Strength: Per MIL-STD-202, Method 211, Test Condition A: For IM-1, 3 pounds pull. For IM-2, -4, -6, -8, -9 and -10, 5 pounds pull and twist.

Weight: IM-1 = .25 gram maximum.

IM-2 = .30 gram maximum.

IM-4 = .65 gram maximum.

IM-6 = .95 gram maximum.

IM-8 = 1.5 gram maximum.

IM-9 = 2.0 gram maximum.

IM-10 = 2.5 gram maximum.

MATERIAL SPECIFICATIONS

Encapsulant: Epoxy.

Standard Terminals: IM-1 and IM-2, 24 AWG; IM-4, IM-6 and IM-9, 22 AWG; IM-8, 21 AWG; and IM-10, 20 AWG, tinned copper.

TEST EQUIPMENT*

- H/P 4342A Q-Meter.
- Measurements Corporation Megacycle Meter, Model 59.
- Wheatstone bridge.

*Test procedures per MIL-PRF-15305.

DIMENSIONS in inches [millimeters]					
MODEL		A (Dia.)	B	C (Typ.)	D (Dia.)
IM-1	Maximum	0.086 [2.18]	0.210 [5.33]	1.62 [41.15]	0.0215 [.546]
	Minimum	0.070 [1.78]	0.190 [4.83]	1.38 [35.05]	0.0185 [.470]
IM-2	Maximum	0.105 [2.67]	0.260 [6.60]	1.63 [41.40]	0.0215 [.546]
	Minimum	0.085 [2.16]	0.240 [6.10]	1.25 [31.75]	0.0185 [.470]
IM-4	Maximum	0.165 [4.19]	0.385 [9.78]	1.63 [41.40]	0.027 [.686]
	Minimum	0.145 [3.68]	0.365 [9.27]	1.25 [31.75]	0.023 [.584]
IM-6	Maximum	0.200 [5.08]	0.450 [11.43]	1.63 [41.40]	0.027 [.686]
	Minimum	0.180 [4.57]	0.430 [10.92]	1.25 [31.75]	0.023 [.584]
IM-8	Maximum	0.225 [5.72]	0.570 [14.48]	1.63 [41.40]	0.030 [.762]
	Minimum	0.205 [5.21]	0.550 [13.97]	1.25 [31.75]	0.026 [.660]
IM-9	Maximum	0.260 [6.60]	0.570 [14.48]	1.63 [41.40]	0.027 [.686]
	Minimum	0.240 [6.10]	0.550 [13.97]	1.25 [31.75]	0.023 [.584]
IM-10	Maximum	0.250 [6.35]	0.750 [19.05]	1.63 [41.40]	0.034 [.864]
	Minimum	0.230 [5.84]	0.730 [18.54]	1.25 [31.75]	0.030 [.762]

ENVIRONMENTAL PERFORMANCE		
TEST	CONDITIONS	SPECIFICATIONS
Barometric Pressure	Test Condition C	MIL-STD-202, Method 105
Thermal Shock	Test Condition A-1	MIL-STD-202, Method 107
Flammability	—	MIL-STD-202, Method 111
Overload	—	MIL-PRF-15305
Low Temperature Storage	—	MIL-PRF-15305
Resistance to Soldering Heat	Test Condition A	MIL-STD-202, Method 210
Resistance to Solvents	—	MIL-STD-202, Method 215



STANDARD ELECTRICAL SPECIFICATIONS										
MODEL	IND. (μH)	TOL.	MIL. STD.	MIL. TYPE	Q MIN.	TEST FREQ. L & Q (MHz)	SELF-RESONANT* FREQ. MIN. (MHz)	DCR MAX. (Ohms)	RATED** DC CURRENT (mA)	
IM-1	0.10	± 10%	—	—	35	25.0	680.0	0.13	895	PHENOLIC CORE
IM-1	0.12	± 10%	—	—	35	25.0	650.0	0.15	835	
IM-1	0.15	± 10%	—	—	35	25.0	560.0	0.18	760	
IM-1	0.18	± 10%	—	—	35	25.0	540.0	0.21	705	
IM-1	0.22	± 10%	—	—	30	25.0	500.0	0.25	645	
IM-1	0.27	± 10%	—	—	30	25.0	440.0	0.38	525	
IM-1	0.33	± 10%	—	—	25	25.0	410.0	0.49	460	
IM-1	0.39	± 10%	—	—	25	25.0	380.0	0.59	420	
IM-1	0.47	± 10%	—	—	25	25.0	340.0	0.62	410	
IM-1	0.56	± 10%	—	—	40	25.0	250.0	0.18	510	IRON CORE
IM-1	0.68	± 10%	—	—	40	25.0	215.0	0.20	485	
IM-1	0.82	± 10%	—	—	40	25.0	200.0	0.22	465	
IM-1	1.0	± 10%	—	—	40	25.0	190.0	0.25	435	
IM-1	1.2	± 10%	—	—	35	7.9	170.0	0.28	410	
IM-1	1.5	± 10%	—	—	40	7.9	150.0	0.49	310	
IM-1	1.8	± 10%	—	—	40	7.9	135.0	0.56	290	
IM-1	2.2	± 10%	—	—	45	7.9	130.0	0.72	257	
IM-1	2.7	± 10%	—	—	45	7.9	110.0	0.85	236	
IM-1	3.3	± 10%	—	—	45	7.9	100.0	1.2	198	
IM-1	3.9	± 10%	—	—	50	7.9	95.0	1.5	178	
IM-1	4.7	± 10%	—	—	55	7.9	88.0	2.1	150	
IM-1	5.6	± 10%	—	—	55	7.9	78.0	2.8	130	
IM-1	6.8	± 10%	—	—	55	7.9	69.0	3.2	122	
IM-1	8.2	± 10%	—	—	45	7.9	52.0	4.4	104	
IM-1	10.0	± 10%	—	—	45	7.9	47.0	5.2	95	
IM-1	12.0	± 10%	—	—	40	2.5	31.0	3.0	126	
IM-1	15.0	± 10%	—	—	40	2.5	26.0	3.4	118	
IM-1	18.0	± 10%	—	—	40	2.5	23.0	3.8	112	
IM-1	22.0	± 10%	—	—	45	2.5	20.0	4.3	105	
IM-1	27.0	± 10%	—	—	45	2.5	17.0	4.7	100	
IM-1	33.0	± 10%	—	—	45	2.5	15.0	5.2	95	
IM-1	39.0	± 10%	—	—	45	2.5	13.5	6.8	83.5	
IM-1	47.0	± 10%	—	—	45	2.5	12.5	8.2	76	
IM-1	56.0	± 10%	—	—	45	2.5	11.5	10.0	69	
IM-1	68.0	± 10%	—	—	45	2.5	10.5	11.5	64	
IM-1	82.0	± 10%	—	—	45	2.5	10.0	16.0	54.5	
IM-1	100.0	± 10%	—	—	45	2.5	9.5	17.5	52	
IM-2	0.022	± 20%	—	—	50	50.0	900.0	0.025	2400	PHENOLIC CORE
IM-2	0.027	± 10%	—	—	40	25.0	875.0	0.03	2200	
IM-2	0.033	± 10%	—	—	40	25.0	850.0	0.035	2000	
IM-2	0.039	± 10%	—	—	40	25.0	825.0	0.04	1900	
IM-2	0.047	± 10%	—	—	40	25.0	800.0	0.045	1800	
IM-2	0.056	± 10%	—	—	40	25.0	775.0	0.05	1700	
IM-2	0.068	± 10%	—	—	40	25.0	750.0	0.06	1500	
IM-2	0.082	± 10%	—	—	40	25.0	725.0	0.07	1400	
IM-2	0.10	± 10%	MS75083	LT4K	40	25.0	680.0	0.08	1350	PHENOLIC CORE
IM-2	0.12	± 10%	-1	339	40	25.0	640.0	0.09	1270	
IM-2	0.15	± 10%	-2	340	40	25.0	600.0	0.10	1200	
IM-2	0.18	± 10%	-3	341	38	25.0	550.0	0.12	1105	
IM-2	0.22	± 10%	-4	342	35	25.0	510.0	0.14	1025	
IM-2	0.27	± 10%	-5	343	33	25.0	430.0	0.16	960	
IM-2	0.33	± 10%	-6	344	33	25.0	410.0	0.22	815	
IM-2	0.39	± 10%	-7	345	30	25.0	365.0	0.30	700	
IM-2	0.47	± 10%	-8	346	30	25.0	330.0	0.35	650	
IM-2	0.56	± 10%	-9	347	30	25.0	300.0	0.50	545	
IM-2	0.68	± 10%	-10	348	30	25.0	275.0	0.60	495	
IM-2	0.82	± 10%	-11	349	28	25.0	250.0	0.85	415	
IM-2	1.0	± 10%	-12	350	28	25.0	230.0	1.0	385	
IM-2	1.2	± 10%	-13	351	25	25.0			385	
IM-2	1.2	± 10%	MS75084	LT10K	25	7.9	150.0	0.18	590	IRON CORE
IM-2	1.5	± 10%	-01	061	28	7.9	140.0	0.22	535	
IM-2	1.8	± 10%	-02	062	30	7.9	125.0	0.30	455	
IM-2	2.2	± 10%	-03	063	30	7.9	115.0	0.40	395	
IM-2	2.7	± 10%	-04	064	30	7.9	100.0	0.55	355	
IM-2	3.3	± 10%	-05	065	37	7.9	90.0	0x.85	270	
IM-2	3.9	± 10%	-06	066	45	7.9	80.0	1.0	250	
IM-2	4.7	± 10%	-07	067	45	7.9	75.0	1.2	230	
IM-2			-08	068	45	7.9			230	

*Measured with full length lead. **Rated DC current based on maximum temperature rise as shown in table.

NOTE: Listing of Military Standard does not imply qualification. Contact factory for latest government QPL information.
NOTE: Products with dashes instead of Military Standard value and type designations are not qualified.

STANDARD ELECTRICAL SPECIFICATIONS										
MODEL	IND. (μH)	TOL.	MIL. STD.	MIL. TYPE	Q MIN.	TEST FREQ. L & Q (MHz)	SELF-RESONANT* FREQ. MIN. (MHz)	DCR MAX. (Ohms)	RATED** DC CURRENT (mA)	
IM-2	5.6	± 10%	MS75084	LT10K	50	7.9	65.0	1.8	185	IRON CORE
IM-2	6.8	± 10%	-09	069	50	7.9	60.0	2.0	175	
IM-2	8.2	± 10%	-10	070	55	7.9	55.0	2.7	155	
IM-2	10.0	± 10%	-11	071	55	7.9	50.0	3.7	130	
IM-2	12.0	± 10%	-12	072	45	2.5	40.0	2.7	155	
IM-2	15.0	± 10%	-13	073	40	2.5	35.0	2.8	150	
IM-2	18.0	± 10%	-14	074	50	2.5	30.0	3.1	145	
IM-2	22.0	± 10%	-15	075	50	2.5	25.0	3.3	140	
IM-2	27.0	± 10%	-16	076	50	2.5	20.0	3.5	135	
IM-2	33.0	± 10%	MS75085	LT10K	45	2.5	24.0	3.4	130	FERRITE CORE
IM-2	39.0	± 10%	-1	078	45	2.5	22.0	3.6	125	
IM-2	47.0	± 10%	-2	079	45	2.5	20.0	4.5	110	
IM-2	56.0	± 10%	-3	080	45	2.5	18.0	5.7	100	
IM-2	68.0	± 10%	-4	081	45	2.5	15.0	6.7	92	
IM-2	82.0	± 10%	-5	082	50	2.5	14.0	7.3	88	
IM-2	100.0	± 10%	-6	083	50	2.5	13.0	8.0	84	
IM-2	120.0	± 10%	-7	084	30	0.79	12.0	13.0	66	
IM-2	150.0	± 10%	-8	085	30	0.79	11.0	15.0	61	
IM-2	180.0	± 10%	-9	086	30	0.79	10.0	17.0	57	
IM-2	220.0	± 10%	-10	087	30	0.79	9.0	21.0	52	
IM-2	270.0	± 10%	-11	088	30	0.79	8.0	25.0	47	
IM-2	330.0	± 10%	-12	089	30	0.79	7.0	28.0	45	
IM-2	390.0	± 10%	-13	090	30	0.79	6.5	35.0	40	
IM-2	470.0	± 10%	-14	091	30	0.79	6.0	42.0	36	
IM-2	560.0	± 10%	-15	092	30	0.79	5.0	46.0	35	
IM-2	680.0	± 10%	-16	093	30	0.79	4.0	60.0	30	
IM-2	820.0	± 10%	-17	094	30	0.79	3.8	65.0	29	
IM-2	1000.0	± 10%	-18	095	30	0.79	3.4	72.0	28	
IM-4	0.15	± 20%	MS18130	LT4K	50	25.0	525.0	0.03	2450	PHENOLIC CORE
IM-4	0.22	± 20%	-1	074	50	25.0	450.0	0.055	1810	
IM-4	0.33	± 20%	-2	075	45	25.0	360.0	0.09	1400	
IM-4	0.47	± 20%	-3	076	45	25.0	310.0	0.12	1225	
IM-4	0.56	± 10%	-4	077	50	25.0	280.0	0.135	1150	
IM-4	0.68	± 10%	-5	078	50	25.0	250.0	0.15	1100	
IM-4	0.82	± 10%	-6	079	50	25.0	220.0	0.22	900	
IM-4	1.0	± 10%	-7	080	50	25.0	200.0	0.29	785	
IM-4	1.2	± 10%	-8	081	33	7.9	180.0	0.42	650	
IM-4	1.5	± 10%	-9	082	33	7.9	160.0	0.50	600	
IM-4	1.8	± 10%	-10	083	33	7.9	150.0	0.65	525	
IM-4	2.2	± 10%	-11	084	33	7.9	135.0	0.95	435	
IM-4	2.7	± 10%	-12	085	33	7.9	120.0	1.20	385	
IM-4	3.3	± 10%	-13	086	33	7.9	110.0	2.0	300	
IM-4	3.9	± 10%	-14	087	33	7.9	100.0	2.30	280	
IM-4	4.7	± 10%	-15	088	33	7.9	90.0	2.60	260	
IM-4	5.6	± 10%	MS14046	LT10K	45	7.9	60.0	0.32	495	IRON CORE
IM-4	6.8	± 10%	-1	128	50	7.9	55.0	0.50	395	
IM-4	8.2	± 10%	-2	129	50	7.9	50.0	0.60	360	
IM-4	10.0	± 10%	-3	130	55	7.9	45.0	0.90	290	
IM-4	12.0	± 10%	-4	131	65	2.5	42.0	1.10	265	
IM-4	15.0	± 10%	-5	132	65	2.5	40.0	1.40	240	
IM-4	18.0	± 10%	-6	133	75	2.5	34.0	2.25	185	
IM-4	22.0	± 10%	-7	134	75	2.5	30.0	2.50	175	
IM-4	27.0	± 10%	-8	135	60	2.5	25.0	2.60	170	
IM-4	33.0	± 10%	-9	136	65	2.5	19.0	3.0	165	
IM-4	33.0	± 10%	-10	137	65	2.5	19.0	3.0	165	

*Measured with full length lead. **Rated DC current based on maximum temperature rise as shown in table.

NOTE: Listing of Military Standard does not imply qualification. Contact factory for latest government QPL information.

NOTE: Products with dashes instead of Military Standard value and type designations are not qualified.



STANDARD ELECTRICAL SPECIFICATIONS										
MODEL	IND. (μH)	TOL.	MIL. STD.	MIL. TYPE	Q MIN.	TEST FREQ. L & Q (MHz)	SELF-RESONANT* FREQ. MIN. (MHz)	DCR MAX. (Ohms)	RATED** DC CURRENT (mA)	
IM-4	36.0	± 5%	MS90538	LT10K	60	2.5	15.5	2.50	180	IRON CORE
IM-4	39.0	± 5%	-1	001	60	2.5	14.5	2.60	176	
IM-4	43.0	± 5%	-2	002	60	2.5	13.7	2.70	172	
IM-4	47.0	± 5%	-3	003	60	2.5	13.0	2.75	170	
IM-4	51.0	± 5%	-4	004	55	2.5	12.7	2.85	167	
IM-4	56.0	± 5%	-5	005	55	2.5	12.0	3.0	164	
IM-4	62.0	± 5%	-6	006	55	2.5	11.5	3.15	160	
IM-4	68.0	± 5%	-7	007	55	2.5	11.0	3.30	156	
IM-4	75.0	± 5%	-8	008	55	2.5	10.5	3.70	147	
IM-4	82.0	± 5%	-9	009	55	2.5	10.3	3.90	143	
IM-4	91.0	± 5%	-10	010	50	2.5	10.0	4.30	136	
IM-4	100.0	± 5%	-11	011	50	2.5	9.5	4.50	133	
IM-4	110.0	± 5%	-12	012	50	2.5	8.9	4.90	128	
IM-4	120.0	± 5%	-13	013	60	0.79	8.7	5.20	124	
IM-4	130.0	± 5%	-14	014	65	0.79	8.5	5.45	121	
IM-4	150.0	± 5%	-15	015	65	0.79	8.0	6.05	114	
IM-4	160.0	± 5%	-16	016	65	0.79	7.5	6.40	111	
IM-4	180.0	± 5%	-17	017	65	0.79	7.0	6.75	108	
IM-4	200.0	± 5%	-18	018	65	0.79	6.5	7.10	106	
IM-4	220.0	± 5%	-19	019	65	0.79	6.2	7.45	103	
IM-4	240.0	± 5%	-20	020	65	0.79	5.9	7.80	101	
IM-4	270.0	± 5%	-21	021	65	0.79	5.7	11.0	129	
IM-4	300.0	± 5%	—	—	65	0.79	5.4	11.5	125	
IM-4	330.0	± 5%	—	—	65	0.79	5.1	12.0	123	
IM-4	360.0	± 5%	—	—	65	0.79	4.8	15.5	108	
IM-4	390.0	± 5%	—	—	65	0.79	4.5	16.3	105	
IM-4	430.0	± 5%	—	—	65	0.79	4.2	17.1	102	
IM-4	470.0	± 5%	—	—	65	0.79	3.9	17.9	100	
IM-4	510.0	± 5%	—	—	65	0.79	3.7	18.8	98	
IM-4	560.0	± 5%	—	—	65	0.79	3.5	24.7	85	
IM-4	620.0	± 5%	—	—	65	0.79	3.3	25.9	83	
IM-4	680.0	± 5%	—	—	55	0.79	3.1	27.2	81	
IM-4	750.0	± 5%	—	—	55	0.79	2.9	28.6	79	
IM-4	820.0	± 5%	—	—	55	0.79	2.7	30.0	77	
IM-4	910.0	± 5%	—	—	55	0.79	2.5	31.5	76	
IM-4	1000.0	± 5%	—	—	55	0.79	2.3	33.1	74	
IM-4	1100.0	± 5%	—	—	30	0.25	2.1	43.5	64	
IM-4	1200.0	± 5%	—	—	30	0.25	2.0	45.7	63	
IM-4	1300.0	± 5%	—	—	30	0.25	1.9	49.0	61	
IM-4	1500.0	± 5%	—	—	30	0.25	1.8	52.5	59	
IM-4	1600.0	± 5%	—	—	30	0.25	1.7	54.0	58	
IM-4	1800.0	± 5%	—	—	30	0.25	1.6	56.7	56	
IM-6	0.10	± 20%	MS75008	LT4K	(Not QPL'd)	25.0	510.0	.020	3600	PHENOLIC CORE
IM-6	0.12	± 20%	—	—	55	25.0	510.0	.025	3300	
IM-6	0.15	± 20%	-21	027	55	25.0	510.0	.030	3000	
IM-6	0.18	± 20%	—	—	55	25.0	450.0	.030	2900	
IM-6	0.22	± 20%	-22	028	50	25.0	415.0	.035	2800	
IM-6	0.27	± 20%	—	—	50	25.0	380.0	.050	2400	
IM-6	0.33	± 20%	-23	029	50	25.0	350.0	.065	2000	
IM-6	0.39	± 20%	—	—	50	25.0	320.0	.080	1800	
IM-6	0.47	± 20%	-24	030	50	25.0	300.0	.085	1700	
IM-6	0.56	± 10%	-25	031	50	25.0	270.0	.125	1450	
IM-6	0.68	± 10%	-26	032	45	25.0	250.0	.150	1300	
IM-6	0.82	± 10%	-27	033	40	25.0	210.0	.205	1100	
IM-6	1.0	± 10%	-28	034	40	25.0	200.0	.290	930	
IM-6	1.2	± 10%	-29	035	30	7.9	180.0	.400	785	
IM-6	1.5	± 10%	-30	036	30	7.9	170.0	.485	700	
IM-6	1.8	± 10%	-31	037	30	7.9	150.0	.740	580	
IM-6	2.2	± 10%	-32	038	30	7.9	140.0	.970	505	
IM-6	2.7	± 10%	-33	039	30	7.9	120.0	1.20	460	

*Measured with full length lead. **Rated DC current based on maximum temperature rise as shown in table.

NOTE: Listing of Military Standard does not imply qualification. Contact factory for latest government QPL information.
NOTE: Products with dashes instead of Military Standard value and type designations are not qualified.



STANDARD ELECTRICAL SPECIFICATIONS										
MODEL	IND. (μH)	TOL.	MIL. STD.	MIL. TYPE	Q MIN.	TEST FREQ. L & Q (MHz)	SELF-RESONANT* FREQ. MIN. (MHz)	DCR MAX. (Ohms)	RATED** DC CURRENT (mA)	
IM-6	3.3	± 10%	MS75101	LT10K		LT10K				
IM-6	3.9	± 10%	-01	169	30	7.9	70.0	0.140	990	IRON CORE
IM-6	4.7	± 10%	-02	170	30	7.9	65.0	0.155	870	
IM-6	5.6	± 10%	-03	171	30	7.9	60.0	0.210	745	
IM-6	6.8	± 10%	-04	172	30	7.9	50.0	0.280	645	
IM-6	8.2	± 10%	-05	173	30	7.9	50.0	0.375	560	
IM-6	10.0	± 10%	-06	174	30	7.9	48.0	0.440	540	
IM-6	12.0	± 10%	-07	175	30	7.9	42.0	0.605	440	
IM-6	15.0	± 10%	-08	176	50	2.5	36.0	1.05	370	
IM-6	18.0	± 10%	-09	177	55	2.5	30.0	1.20	310	
IM-6	22.0	± 10%	-10	178	60	2.5	30.0	1.95	255	
IM-6	27.0	± 10%	-11	179	60	2.5	24.0	2.20	240	
IM-6	33.0	± 10%	-12	180	65	2.5	22.0	2.75	205	
IM-6	39.0	± 10%	—	—	75	2.5	20.0	3.5	185	
IM-6	47.0	± 10%	—	—	75	2.5	18.0	3.8	176	
IM-6	56.0	± 10%	—	—	75	2.5	16.0	4.0	170	
IM-6	68.0	± 10%	—	—	75	2.5	15.0	4.4	164	
IM-6	82.0	± 10%	—	—	75	2.5	12.0	4.7	156	
IM-6	100.0	± 10%	—	—	75	2.5	10.0	5.3	143	
IM-6	120.0	± 10%	—	—	65	2.5	8.0	6.0	133	
IM-6	150.0	± 10%	—	—	65	0.79	6.0	5.0	124	
IM-6	180.0	± 10%	—	—	65	0.79	5.4	5.8	118	
IM-6	220.0	± 10%	—	—	65	0.79	5.0	6.6	114	
IM-6	270.0	± 10%	—	—	65	0.79	4.7	7.4	112	
IM-6	270.0	± 5%	MS90539	LT10K	(Not QPL'd)					IRON CORE
IM-6	300.0	± 5%	-01	022	65	0.79	5.6	8.2	110	
IM-6	330.0	± 5%	-02	023	65	0.79	5.3	8.7	107	
IM-6	360.0	± 5%	-03	024	65	0.79	5.0	9.1	105	
IM-6	390.0	± 5%	-04	025	65	0.79	4.7	9.6	102	
IM-6	430.0	± 5%	-05	026	65	0.79	4.5	10.0	100	
IM-6	470.0	± 5%	-06	027	65	0.79	4.3	10.6	97	
IM-6	510.0	± 5%	-07	028	65	0.79	4.0	11.1	95	
IM-6	560.0	± 5%	-08	029	65	0.79	3.8	11.6	93	
IM-6	620.0	± 5%	-09	030	65	0.79	3.6	12.3	91	
IM-6	680.0	± 5%	-10	031	60	0.79	3.5	13.0	88	
IM-6	750.0	± 5%	-11	032	60	0.79	3.4	13.7	85	
IM-6	820.0	± 5%	-12	033	60	0.79	3.3	14.4	83	
IM-6	910.0	± 5%	-13	034	60	0.79	3.1	15.1	81	
IM-6	1000.0	± 5%	-14	035	60	0.79	2.9	15.8	79	
IM-6	1000.0	± 5%	-15	036	60	0.79	2.8	16.5	78	
IM-8	1100.0	± 5%	MS90540	LT10K	(Not QPL'd)					IRON CORE
IM-8	1200.0	± 5%	-01	037	60	0.25	2.8	21.0	78	
IM-8	1300.0	± 5%	-02	038	60	0.25	2.7	22.0	76	
IM-8	1500.0	± 5%	-03	039	60	0.25	2.6	23.0	75	
IM-8	1600.0	± 5%	-04	040	65	0.25	2.4	25.0	72	
IM-8	1800.0	± 5%	-05	041	65	0.25	2.3	26.0	70	
IM-8	2000.0	± 5%	-06	042	65	0.25	2.2	28.0	68	
IM-8	2200.0	± 5%	-07	043	65	0.25	2.1	29.0	67	
IM-8	2400.0	± 5%	-08	044	70	0.25	2.0	30.0	66	
IM-8	2700.0	± 5%	-09	045	70	0.25	1.9	31.0	64	
IM-8	3000.0	± 5%	-10	046	70	0.25	1.8	33.0	62	
IM-8	3300.0	± 5%	-11	047	70	0.25	1.7	35.0	61	
IM-8	3600.0	± 5%	-12	048	70	0.25	1.6	38.0	58	
IM-8	3600.0	± 5%	-13	049	70	0.25	1.5	40.0	57	

*Measured with full length lead. **Rated DC current based on maximum temperature rise as shown in table.

NOTE: Listing of Military Standard does not imply qualification. Contact factory for latest government QPL information.

NOTE: Products with dashes instead of Military Standard value and type designations are not qualified.



STANDARD ELECTRICAL SPECIFICATIONS										
MODEL	IND. (μH)	TOL.	MIL. STD.	MIL. TYPE	Q MIN.	TEST FREQ. L & Q (MHz)	SELF-RESONANT* FREQ. MIN. (MHz)	DCR MAX. (Ohms)	RATED** DC CURRENT (mA)	
IM-9	68.0	± 10%	MS14047	LT10K	(Not QPL'd)					
			-01	138	70	2.5	13.0	3.3	168	IRON CORE
IM-9	82.0	± 10%	-02	139	65	2.5	11.7	3.5	162	
IM-9	100.0	± 10%	-03	140	65	2.5	10.7	3.8	155	
IM-9	120.0	± 10%	-04	141	75	0.79	9.3	4.7	142	
IM-9	150.0	± 10%	-05	142	75	0.79	8.3	5.3	132	
IM-10	3900.0	± 5%	MS90541	LT10K	(Not QPL'd)					
			-01	050	80	0.25	1.45	44.0	61	IRON CORE
IM-10	4300.0	± 5%	-02	051	80	0.25	1.40	46.0	59	
IM-10	4700.0	± 5%	-03	052	80	0.25	1.35	48.0	58	
IM-10	5000.0	± 5%	-04	053	80	0.25	1.30	50.0	57	
IM-10	5600.0	± 5%	-05	054	80	0.25	1.25	53.0	56	
IM-10	6200.0	± 5%	-06	055	80	0.25	1.20	56.0	54	
IM-10	6800.0	± 5%	-07	056	80	0.25	1.15	59.0	52	
IM-10	7500.0	± 5%	-08	057	80	0.25	1.10	62.0	51	
IM-10	8200.0	± 5%	-09	058	80	0.25	1.05	65.0	50	
IM-10	9100.0	± 5%	-10	059	80	0.25	1.0	68.0	49	
IM-10	10000.0	± 5%	-11	060	80	0.25	0.95	72.0	47	

*Measured with full length lead. **Rated DC current based on maximum temperature rise as shown in table.

NOTE: Listing of Military Standard does not imply qualification. Contact factory for latest government QPL information.

NOTE: Products with dashes instead of Military Standard value and type designations are not qualified.

MAXIMUM TEMPERATURE RISE		
		OPERATING TEMPERATURE RANGE
IM-1	0.10μH to .47μH = 35°C at + 90°C ambient 0.56μH to 1000μH = 15°C at + 90°C ambient	- 55°C to + 125°C - 55°C to + 105°C
IM-2	0.022μH to 1.0μH = 35°C at + 90°C ambient 1.2μH to 27μH = 15°C at + 90°C ambient 33μH to 1000μH = 15°C at + 90°C ambient	- 55°C to + 125°C - 55°C to + 105°C - 55°C to + 105°C
IM-4	0.15μH to 4.7μH = 35°C at + 90°C ambient 5.6μH to 33μH = 15°C at + 90°C ambient 36μH to 240μH = 15°C at + 90°C ambient 270μH to 1800μH = 35°C at + 90°C ambient	- 55°C to + 125°C - 55°C to + 105°C - 55°C to + 105°C - 55°C to + 125°C
IM-6	0.1μH to 2.7μH = 35°C at + 90°C ambient 3.3μH to 1000μH = 15°C at + 90°C ambient	- 55°C to + 125°C - 55°C to + 105°C
IM-8, IM-9, IM-10	= 15°C at + 90°C ambient	- 55°C to + 105°C

ORDERING INFORMATION		
IM-2 MODEL	10μH INDUCTANCE VALUE	± 10% INDUCTANCE TOLERANCE

ORDERING INFORMATION - MILITARY PART NUMBER						
MS75084 MILITARY STANDARD	- 12 INDUCTANCE VALUE	OR	LT TYPE	10 GRADE AND CLASS	K FAMILY	072 ID NUMBER



Notice

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.