


JAN Qualified N-Channel 60-V (D-S) MOSFET

PRODUCT SUMMARY			
$V_{(BR)DSS}$ Min (V)	$r_{DS(on)}$ Max (Ω)	$V_{GS(th)}$ (V)	I_D (A)
60	3 at $V_{GS} = 10$ V	0.8 to 2	0.99



FEATURES

- Military Qualified
- Low On-Resistance: 1.3 Ω
- Low Threshold: 1.7 V
- Low Input Capacitance: 35 pF
- Fast Switching Speed: 8 ns
- Low Input and Output Leakage

BENEFITS

- Guaranteed Reliability
- Low Offset Voltage
- Low-Voltage Operation
- Easily Driven Without Buffer
- High-Speed Circuits
- Low Error Voltage

APPLICATIONS

- Military Applications
- Direct Logic-Level Interface: TTL/CMOS
- Drivers: Relays, Solenoids, Lamps, Hammers, Displays, Memories, Transistors, etc.
- Battery Operated Systems
- Solid-State Relays

ABSOLUTE MAXIMUM RATINGS $T_A = 25$ °C, unless otherwise noted				
Parameter		Symbol	Limit	Unit
Drain-Source Voltage		V_{DS}	60	V
Gate-Source Voltage		V_{GS}	± 20	
Continuous Drain Current ($T_J = 150$ °C)	$T_C = 25$ °C	I_D	0.99	A
	$T_C = 100$ °C		0.62	
Pulsed Drain Current ^a		I_{DM}	3	
Power Dissipation	$T_C = 25$ °C	P_D	6.25	W
	$T_A = 25$ °C		0.725	
Thermal Resistance, Junction-to-Ambient ^b		R_{thJA}	170	°C/W
Thermal Resistance, Junction-to-Case		R_{thJC}	20	
Operating Junction and Storage Temperature Range		T_J, T_{stg}	- 55 to 150	°C

Notes:

- a. Pulse width limited by maximum junction temperature.
 b. Not required by military spec.

SPECIFICATIONS ^a $T_A = 25\text{ }^\circ\text{C}$, unless otherwise noted						
Parameter	Symbol	Test Conditions	Limits			Unit
			Min	Typ ^b	Max	
Static						
Drain-Source Breakdown Voltage	$V_{(BR)DSS}$	$V_{DS} = 0\text{ V}, I_D = 10\text{ }\mu\text{A}$	60	75		V
Gate Threshold Voltage	$V_{GS(th)}$	$V_{DS} = V_{GS}, I_D = 1\text{ mA}$	0.8	1.7	2	
		$T_C = -55\text{ }^\circ\text{C}$			2.5	
Gate-Body Leakage	I_{GSS}	$V_{DS} = 0\text{ V}, V_{GS} = \pm 20\text{ V}$			± 100	nA
		$T_C = 125\text{ }^\circ\text{C}$			± 500	
Zero Gate Voltage Drain Current	I_{DSS}	$V_{DS} = 48\text{ V}, V_{GS} = 0\text{ V}$			1	μA
		$T_C = 125\text{ }^\circ\text{C}$			100	
On-State Drain Current	$I_{D(on)}$	$V_{DS} = 10\text{ V}, V_{GS} = 10\text{ V}$		2		A
Drain-Source On-Resistance ^c	$r_{DS(on)}$	$V_{GS} = 5\text{ V}, I_D = 0.3\text{ A}$		2	5	Ω
		$V_{GS} = 10\text{ V}, I_D = 1\text{ A}$		1.3	3	
		$T_C = 125\text{ }^\circ\text{C}$		2.4	5.6	
Forward Transconductance ^c	g_{fs}	$V_{DS} = 7.5\text{ V}, I_D = 0.525\text{ A}$	170	350		mS
Diode Forward Voltage	V_{SD}	$I_S = 0.99\text{ A}, V_{GS} = 0\text{ V}$	0.7	0.8	1.6	V
Dynamic						
Input Capacitance	C_{iss}	$V_{DS} = 25\text{ V}, V_{GS} = 0\text{ V}, f = 1\text{ MHz}$		35	50	pF
Output Capacitance	C_{oss}			25	40	
Reverse Transfer Capacitance	C_{rss}			7	10	
Drain-Source Capacitance	C_{ds}			30		
Switching^d						
Turn-On Time	t_{ON}	$V_{DD} = 25\text{ V}, R_L = 23\text{ }\Omega$		8	10	ns
Turn-Off Time	t_{OFF}	$I_D \cong 1\text{ A}, V_{GEN} = 10\text{ V}, R_g = 25\text{ }\Omega$		8.5	10	

Notes:

- $T_A = 25\text{ }^\circ\text{C}$ unless otherwise noted.
- FOR DESIGN AID ONLY, not subject to production testing.
- Pulse test: $PW \leq 300\text{ }\mu\text{s}$ duty cycle $\leq 2\%$.
- Switching time is essentially independent of operating temperature.
- For typical characteristics curves see the 2N6659/2N6660, VQ1004J/P data sheet.

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package/tape drawings, part marking, and reliability data, see <http://www.vishay.com/ppg?70223>.



Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.