

INTERNATIONAL RECTIFIER



2N681 & 2N5204 SERIES

25 and 35 Amp RMS SCRs

Major Ratings and Characteristics



	2N681-92	2N5204-07	Units
$I_{T(RMS)}$	25	35	A
$I_{T(AV)}$	18*	22*	A
θ_{TC}	-65 to 85*	-40 to 40	°C
I_{TSM}			
@ 50 Hz	145	285	A
@ 60 Hz	160*	300*	
i_{2t}			A ² s
@ 50 Hz	103	410	
@ 60 Hz	94	375	
I_{GT}	40	40	mA
dv/dt		100*	V/ μ s
dI/dt	75-100	100	A/ μ s
T_J	-65 to 125*	-40 to 125*	°C
$V_{RRM}, V_{ORM} \text{ range}^\#$	25-800	600-1200	V

*JEDEC registered value.

Description/Features

- General purpose stud mounted
- Broad forward and reverse voltage range – through 1200 volts
- Can be supplied to meet stringent military, aerospace and other high-reliability requirements

CASE STYLE AND DIMENSIONS



Conforms to JEDEC Outline **TO-208AA (TO-48)**
Dimensions in Millimeters and (Inches)

VOLTAGE RATINGS (Applied gate voltage zero or negative)

Part Numbers	V_{RRM}, V_{DRM} - Max. Repetitive Peak Reverse and Off-State Voltage (V)	V_{RSM} Max. Non Repetitive Peak Reverse Voltage $t_p \leq 5$ ms (V)
	$T_J = -65^\circ\text{C}$ to 125°C	$T_J = -65^\circ\text{C}$ to 125°C
2N681	25*	35*
2N682	60*	75*
2N683	100*	150*
2N685	200*	300*
2N687	300*	400*
2N688	400*	500*
2N689	500*	600*
2N690	600*	720*
2N691	700*	840*
2N692	800*	960*
	$T_J = -40^\circ\text{C}$ to 125°C	$T_J = -40^\circ\text{C}$ to 125°C
2N5204	600	720
2N5205	800	960
2N5206	1000	1200
2N5207	1200	1440

ELECTRICAL SPECIFICATIONS

	2N681-92	2N5204-07	Units	Conditions
ON-STATE				
$I_T(\text{RMS})$ Max. RMS on-state current	25	35	A	
$I_T(\text{AV})$ Max. average on-state current	16*	22*	A	
θ $T_C =$	-65 to 65*	-40 to 40*	$^\circ\text{C}$	180° half sine wave conduction
I_{TSM} Max. peak one cycle, non-repetitive surge current	145	285	A	50 Hz half cycle sine wave or 6 ms rectangular pulse
	150*	300*		60 Hz half cycle sine wave or 5 ms rectangular pulse
	170	340		50 Hz half cycle sine wave or 6 ms rectangular pulse
	180	355		60 Hz half cycle sine wave or 5 ms rectangular pulse
I_{T1}^2 Max. I_{T1}^2 capability, for fusing	103	410	A^2s	$t = 10$ ms Rated V_{RRM} applied following surge, initial $T_J = 125^\circ\text{C}$
	94	375		$t = 8.3$ ms
I_{T2}^2 Max. I_{T2}^2 capability, for individual device fusing	145	580	A^2s	$t = 10$ ms $V_{RRM} = 0$ following surge, initial $T_J = 125^\circ\text{C}$
	135	530		$t = 8.3$ ms
$I_{T2}^2 \sqrt{t}$ Max. $I_{T2}^2 \sqrt{t}$ capability, for individual device fusing ①	1450	5800	$\text{A}^2 \sqrt{\text{s}}$	$t = 0.1$ to 10 ms initial $T_J \leq 125^\circ\text{C}$ V_{RRM} following surge = 0.
V_{TM} Max. peak on-state voltage	2*	2.3*	V	$T_J = 25^\circ\text{C}$, $I_T(\text{AV}) = 18\text{A}$ (60A peak) 2N681, $I_T(\text{AV}) = 22\text{A}$ (70A peak) 2N5204
I_H Max. holding current	20 @ 25°C †	200* @ -40°C	mA	Anode supply = 24V, initial $I_T = 1.0\text{A}$.
BLOCKING				
dv/dt Min. critical rate-of-rise of off-state voltage	100†	100*	V/ μs	$T_J = 125^\circ\text{C}$. Exponential to 100% rated V_{DRM}
	250†	250		$T_J = 125^\circ\text{C}$. Exponential to 87% rated V_{DRM}

*JESDEC Registered value.

① I_{T2}^2 for time $t_x = I_{T2}^2 \sqrt{t} = \sqrt{t_x}$.

† Typical

ELECTRICAL SPECIFICATIONS (Continued)

BLOCKING (Continued)			2N681-92	2N5204-07	Units	Conditions
$I_{R(-)}$ & $I_{D(-)}$ V_{RRM} & $V_{DRM} =$	Max. reverse and off-state current 5V	$I_{R(AV)}$ & $I_{D(AV)}$ (Average Values)	I_{RM} & I_{DM} (Peak Values)	mA	$T_J = 125^\circ\text{C}$, gate open circuited.	
25 to 150V	6.5*	—				
200 & 250V	6.0*	—				
300V	5.0*	—				
400V	4.0*	—				
500V	3.0*	—				
600V	2.5*	3.3*				
700V	2.25*	—				
800V	2.0*	2.5*				
1000V	—	2.0*				
1200V	—	1.7*				
SWITCHING						
t_d	Typical delay time	1	1	μs	$T_C = 25^\circ\text{C}$, $V_{DM} = \text{rated } V_{DRM}$, $I_{TM} = 10\text{A}$ dc resistive circuit. Gate pulse: 10V, 400 μs source, $t_p = 6\text{ }\mu\text{s}$, $t_r = 0.1\text{ }\mu\text{s}$.	
di/dt	Max. non-repetitive rate of rise of turned-on current $V_{DM} =$ 25 to 600V = 700 to 800V	100 75	— —	A/ μs	$T_C = 125^\circ\text{C}$, $V_{DM} = \text{rated } V_{DRM}$, $I_{TM} = 2 \times di/dt$. Gate pulse: 20V, 150 μs , $t_p = 6\text{ }\mu\text{s}$, $t_r = 0.1\text{ }\mu\text{s}$ max. Per JEDEC standard RS-397, 5.2.2.6.	
		—	100		$T_C = 125^\circ\text{C}$, $V_{DM} = 600\text{V}$, $I_{TM} = 200\text{A}$ @ 400 Hz, max., Gate pulse: 20V, 150 μs , $t_p = 6\text{ }\mu\text{s}$, $t_r = 0.1\text{ }\mu\text{s}$ max., Per JEDEC standard RS-397, 5.2.2.6.	
TRIGGERING						
P_{GM}	Max. peak gate power	5*	60*	W	$t_p \leq 5\text{ ms}$ for 2N681 series; $t_p \leq 500\text{ }\mu\text{s}$ for 2N5204 series.	
$P_{G(AV)}$	Max. average gate power	0.5*	0.5*	W		
I_{GM}	Max. peak positive gate current	2*	2	A		
$+V_{GM}$	Max. peak positive gate voltage	10*	—	V		
$-V_{GM}$	Max. peak negative gate voltage	5*	5*	V		
I_{GT}	Max. required DC gate current to trigger	80* 40 18.5	80* 40 20	mA	$T_C = \text{min. rated value. Max. required gate trigger current is the lowest value which will trigger all units with +6V anode-to-cathode.}$ $T_C = 25^\circ\text{C}$ $T_C = 125^\circ\text{C}$	
	Typical DC gate current to trigger	30	30		$T_C = 25^\circ\text{C}$ +6V anode-to-cathode	
V_{GT}	Max. required DC gate voltage to trigger	3* 2 1.5	3* 2 1.5	V	$T_C = -65^\circ\text{C}$. Max. required gate trigger voltage is the lowest value which will trigger all units with +6V anode-to-cathode. $T_C = 25^\circ\text{C}$ $T_C = 25^\circ\text{C}$ +6V anode-to-cathode	
	Typical DC gate voltage to trigger	1.5	1.5			
V_{GD}	Max. DC gate voltage not to trigger	0.25*	0.25*	V	$T_C = 125^\circ\text{C}$. Max. gate voltage not to trigger is the maximum value which will not trigger any unit with rated V_{DRM} anode-to-cathode.	

THERMAL-MECHANICAL SPECIFICATIONS

		2N681-B2	2N5204-07	Units	Conditions
T_J	Operating junction temperature range	-65° to 125°	-40° to 125°	°C	
T_{stg}	Storage temperature range	-55° to 125°	-40° to 125°	°C	
R_{thJC}	Max. internal thermal resistance, junction to case	1.5	1.5*	deg. C/W	DC operation
R_{thCS}	Thermal resistance, case to sink	0.35	0.35	deg. C/W	Mounting surface smooth, flat and greased.
Mounting torque to nut ±10%		20.(27.5)		lbf · in.	Lubricated threads (non-lubricated threads).
		0.23(.32)		kgf · m	
		2.3(3.1)		N·m	
	to device	25		lbf · in.	Lubricated threads.
		0.25		kgf · m	
		2.8		N·m	
wt	Approximate weight	14(0.49)	14(0.5)	g (oz.)	
	Case Style	TO-208AA (TO-48)			

*JEDEC Registered value.

2N681 Series




Fig. 1 — Maximum Allowable Case Temperature Vs. Average On-State Current, 2N681 Series




Fig. 2 — Maximum On-State Voltage Vs. Current, 2N681 Series

2N681 Series




Fig. 3 — Maximum Low Level On-State Power Loss Vs. Current (Sinusoidal Current Waveform), 2N681 Series




Fig. 4 — Maximum High Level On-State Power Loss Vs. Current (Sinusoidal Current Waveform), 2N681 Series




Fig. 5 — Gate Characteristics, 2N681 Series




Fig. 5A — Area of All Possible Triggering Points Vs. Temperature 2N681 Series

2N681 Series




Fig. 6 - Maximum Transient Thermal Impedance, Junction to Case, Vs. Pulse Duration, 2N681 Series




Fig. 7 - Maximum Non-Repetitive Surge Current, Vs. Number of Current Pulses, 2N681 Series

2N5204 Series




Fig. 8 - Maximum Allowable Case Temperature Vs. Average On-State Current (Sinusoidal Current Waveform), 2N5204 Series




Fig. 9 - Maximum Allowable Case Temperature Vs. Average On-State Current (Rectangular Current Waveform), 2N5204 Series

2N5204 Series




Fig. 10 - Maximum Low-Level On-State Power Loss Vs. Average On-State Current (Sinusoidal Current Waveform), 2N5204 Series




Fig. 11 - Maximum High-Level On-State Power Loss Vs. Average On-State Current (Sinusoidal Current Waveform), 2N5204 Series




Fig. 12 - Maximum Low-Level On-State Power Loss Vs. Average On-State Current (Rectangular Current Waveform), 2N5204 Series




Fig. 13 - Maximum High-Level On-State Power Loss Vs. Average On-State Current (Rectangular Current Waveform), 2N5204 Series




Fig. 14 - Maximum Instantaneous On-State Voltage Vs. Instantaneous On-State Current, 2N5204 Series




Fig. 15 - Maximum Transient Thermal Resistance, Junction to Case, Vs. Pulse Duration, 2N5204 Series



Notice

The products described herein were acquired by Vishay Intertechnology, Inc., as part of its acquisition of International Rectifier's Power Control Systems (PCS) business, which closed in April 2007. Specifications of the products displayed herein are pending review by Vishay and are subject to the terms and conditions shown below.

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.

International Rectifier®, IR®, the IR logo, HEXFET®, HEXSense®, HEXDIP®, DOL®, INTERO®, and POWIRTRAIN® are registered trademarks of International Rectifier Corporation in the U.S. and other countries. All other product names noted herein may be trademarks of their respective owners.