





Product Number: 236-505
PCB TERMINAL STRIP 2 SOLDER PINS / POLE 5 POLE PIN SPACING 7.5/7.62 MM / 0.3 IN

RoHS compliant



Diameter of drilled hole: $1,1^{+0,1}$ mm
 $L = (\text{No. of poles} \times \text{pin spacing}) + 2,3$ mm

Product group	4 (Printed Circuit)
Weight	5.599 g
Color	gray
No. of connection Points	5
No. of potentials	5
pole count	5
Height	13 mm
Height	0.512 in
Width	39.8 mm
Width	1.567 in
Depth	14 mm
Depth	0.551 in
Pin spacing from	7.5 mm

Pin spacing up to	7.62 mm
Pin spacing from	0.295 in
Pin spacing up to	0.3 in
Pollution degree	2
Measured voltage EN	630 V
Measured shock voltage	6 kV
Current intensity EN	24 A
Pollution degree	2
Measured voltage EN	1000 V
Measured shock voltage	6 kV
Current intensity EN	24 A
Connection method	CAGE CLAMP® CONNECTION
Cross section [mm ²]	0.08 - 2.5 mm ²
Wiring method	solid
Cross section [mm ²]	0.08 - 2.5 mm ²
Cross section [mm ²]	0.25 - 1.5 mm ²
Cross section [mm ²]	0.25 - 1.5 mm ²
Cross section [AWG]	28 - 12 AWG
Strip length from	5 mm
Strip length to	6 mm
Material group	I