
Item no.: 280-519
Product description: DOUBLE DECK TERMINAL BLOCK THROUGH/THROUGH



Produkt kann von Bild abweichen / product may differ

Packing unit 50 pieces

Product group	1 (Rail Mounted Terminal Blocks)
Number of levels	2
Cross section [mm ²]	0.08 - 2.5 mm ²
Cross section [AWG]	28 - 12 AWG
Connection method	CAGE CLAMP® CONNECTION
Measured voltage EN	500 V
Measured shock voltage	6 kV
Pollution degree	3
Current intensity EN	20 A
Weight	10.057 g
Color	gray
Wiring type	Front-entry
No. of connection Points	4
No. of potentials	2
Height	58.5 mm
Height	2.3 in
Width	5 mm
Width	0.197 in
Depth	64 mm
Depth	2.52 in
Strip length from	8 mm

Strip length to
Strip length
Mounting

9 mm
0.33 in
TS 35



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
280-519	ABS	05-HG476175/1-PDA	500	20	2,5
280-519	BV	07436/Co	500	20	2,5
280-519	CCA	NL5855	500	20	2,5
280-519	CSA	154112-1536071	300/600	20/5	28-12
280-519	DEMKO	93117	500		2,5
280-519	GL	17295-00HH	500	20	2,5
280-519	KEMA	2082859.07	500	20	2,5
280-519	LR	91/20112(E6)	500	20	2,5
280-519	NEMKO	L86905	500	20	2,5
280-519	PRS	TE/1718/880590/08	500	20	2,5
280-519	RMR	11130002	500	20	2,5
280-519	UR	E45172	300/150/300	15/15/5	28-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected