


Item no.: 250-102
 Product description: 1-CONDUCTOR PCB TERMINAL STRIP 1 FRONT SOLDER
 PIN / POLE 2 POLE PIN SPACING 3.5 MM / 0.138 IN WITH
 PUSH BUTTONS WITH TEST SLOT FOR TEST PLUG TO 1.3
 MM Ø



Produkt kann von Bild abweichen / product may differ

Packing unit 560 4*140 pieces

RoHS compliant

Product group	4 (Printed Circuit)
Weight	1.083 g
Color	gray
No. of connection Points	2
No. of potentials	2
pole count	2
Height	13.1 mm
Height	0.516 in
Width	8.5 mm
Width	0.335 in
Depth	12 mm
Depth	0.472 in
Pin spacing from	3.5 mm
Pin spacing from	0.138 in
Pollution degree	2
Measured voltage EN	160 V
Measured shock voltage	2.5 kV

Current intensity EN	8 A
Pollution degree	2
Measured voltage EN	320 V
Measured shock voltage	2.5 kV
Current intensity EN	8 A



Cross section [mm ²]	0.2 - 1.5 mm ²
Wiring method	solid
Cross section [mm ²]	0.2 - 1.5 mm ²
Wiring method	fine-stranded
Cross section [mm ²]	0.25 - 1 mm ²
Wiring method	fine-stranded (with ferrule and plastic collar)
Cross section [mm ²]	0.25 - 1 mm ²
Wiring method	fine-stranded (with ferrule, without plastic collar)
Cross section [AWG]	24 - 16 AWG
Strip length from	8.5 mm
Strip length to	9.5 mm
Material group	I
Contact surface	Copper
xxx-xxx/000-002	yellow
xxx-xxx/000-004	black
xxx-xxx/000-005	red
xxx-xxx/000-006	blue
xxx-xxx/000-009	light gray
xxx-xxx/000-012	orange
xxx-xxx/000-014	brown
xxx-xxx/000-017	light green
xxx-xxx/000-024	violet
xxx-xxx/000-050	white



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
250-102	ABS	04-HG469925/1-PDA	250	2	0,5-1,5
250-102	BV	11915/A0	200	2	0,5-1,5
250-102	CCA	NL6336	250	8	0,2-1,5
250-102	CSA	154112-1132097	300	10	20-16
250-102	DNV	E-9215	250	2	0,5-1,5
250-102	GL	17296-00HH	250	2	0,5-1,5
250-102	KEMA	2114919.01	250	8	0,2-1,5
250-102	RMR	11130002	250	2	0,5-1,5
250-102	UR	E45172	300	5	24-16

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected