


Item no.: 264-162
 Product description: 2-CONDUCTOR TERMINAL STRIP WITH SNAP-IN MOUNTING FEET FOR SHEET THICKNESS 0.6-1.2 MM 3.5 MMØ FOR ALUMINUM RAIL 210-154 OR WITH MOUNTING ADAPTER 209-120 FOR TS 35 12 POLE



Produkt kann von Bild abweichen / product may differ

Packing unit 25 pieces

Product group	9 (Std Chassis Mt Blocks)
pole count	12
Cross section [mm ²]	0.08 - 2.5 mm ²
Cross section [AWG]	28 - 12 AWG
Connection method	CAGE CLAMP® CONNECTION
Measured voltage EN	800 V
Measured shock voltage	8 kV
Pollution degree	3
Current intensity EN	24 A
Weight	47.72 g
Color	gray
Wiring type	Front-entry
No. of connection Points	24
No. of potentials	12
Height	22 mm
Height	0.867 in
Width	79 mm
Width	3.11 in

Depth	32 mm
Depth	1.26 in
Strip length from	8 mm
Strip length to	9 mm
Strip length	0.33 in
xxx-xxx/000-006	blue



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
264-162	ABS	04-HG476174/1-PDA	800	24	2,5
264-162	BV	07436/C0			0,08-2,5
264-162	CCA	NL6511	800	24	2,5
264-162	CSA	18677-23	600	20	26-12
264-162	DNV	E-9215	800	24	2,5
264-162	GL	17295-00HH	800	24	2,5
264-162	KEMA	2110272.04	800	24	2,5
264-162	KR	HMB05880-EL002	800	24	
264-162	LR	92/20242(E5)	800	24	2,5
264-162	PRS	TE/1718/880590/08	800		2,5
264-162	RMR	11130002	800	24	2,5
264-162	UR	E45172	300	20	28-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected