





Color: light gray

Similar to illustration

Dimensions in mm  
L = (pole no. x pin spacing) + 2.2 mm

- Universal connection for all conductor types
- Easy cable pre-assembly and on-unit wiring via vertical and horizontal CAGE CLAMP® actuation
- Strain relief plates and housings for field assembly
- 100% protected against mismatching
- Coding option available

## Notes

### Safety Information

The MCS – MULTI CONNECTION SYSTEM includes connectors without breaking capacity in accordance with DIN EN 61984. When used as intended, these connectors must not be connected/disconnected when live or under load. When used as intended, these connectors must not be connected/disconnected when live or under load. The circuit design should ensure header pins, which can be touched, are not live when unmated.

### Variants:

#### Other pole numbers

Gold-plated or partially gold-plated contact surfaces

Other versions (or variants) can be requested from WAGO Sales or configured at <https://configurator.wago.com/>.

**Electrical data**

Ratings per			IEC/EN 60664-1		
Overvoltage category	III	III	II		
Pollution degree	3	2	2		
Nominal voltage	160 V	160 V	320 V		
Rated surge voltage	2.5 kV	2.5 kV	2.5 kV		
Rated current	10 A	10 A	10 A		

Approvals per			UL 1059		
Use group	B	C	D		
Rated voltage	300 V	-	300 V		
Rated current	10 A	-	10 A		

Approvals per			CSA		
Use group	B	C	D		
Rated voltage	300 V	-	300 V		
Rated current	10 A	-	10 A		

**Connection data**

Clamping units	8
Total number of potentials	8
Number of connection types	1
Number of levels	1

Connection 1	
Connection technology	CAGE CLAMP®
Actuation type	Operating tool
Actuation direction 1	Operation parallel to conductor entry
Actuation direction 2	Operation perpendicular to conductor entry
Solid conductor	0.08 ... 1.5 mm <sup>2</sup> / 28 ... 14 AWG
Fine-stranded conductor	0.08 ... 1.5 mm <sup>2</sup> / 28 ... 14 AWG
Fine-stranded conductor; with insulated ferrule	0.25 ... 1.5 mm <sup>2</sup>
Fine-stranded conductor; with uninsulated ferrule	0.25 ... 1.5 mm <sup>2</sup>
Note (conductor cross-section)	Terminating 1.5 mm <sup>2</sup> conductors is possible; however insulation diameter does not allow clamping units to be terminated in a row.
Strip length	6 ... 7 mm / 0.24 ... 0.28 inches
Pole number	8
Conductor entry direction to mating direction	0 °

**Physical data**

Pin spacing	3.5 mm / 0.138 inches
Width	30.2 mm / 1.189 inches
Height	13.4 mm / 0.528 inches
Depth	18.6 mm / 0.732 inches

**Mechanical data**

Variable coding	Yes
Anti-rotation protection	Yes

**Plug-in connection**

Contact type (pluggable connector)	Female connector/socket
Connector (connection type)	for conductor
Mismating protection	Yes

**Material data**

Note (material data)	<a href="#">Information on material specifications can be found here</a>
Color	light gray
Material group	I
Insulation material (main housing)	Polyamide (PA66)
Flammability class per UL94	V0
Clamping spring material	Chrome-nickel spring steel (CrNi)
Contact material	Copper alloy
Contact Plating	Tin
Fire load	0.096 MJ
Weight	6.1 g

**Environmental requirements**

Limit temperature range	-60 ... +100 °C
Processing temperature	-35 ... +60 °C

**Environmental Testing (Environmental Conditions)**

Test specification	DIN EN 50155 (VDE 0115-200):2022-06
Railway applications – Rolling stock – Electronic equipment	
Test procedure	DIN EN 61373 (VDE 0115-0106):2011-04
Railway applications – Rolling stock equipment – Shock and vibration tests	
Spectrum/Installation location	Service life test, Category 1, Class A/B
Function test with noise-like vibration	Test passed according to Section 8 of the standard
Frequency	$f_1 = 5 \text{ Hz}$ to $f_2 = 150 \text{ Hz}$ $f_1 = 5 \text{ Hz}$ to $f_2 = 150 \text{ Hz}$
Acceleration	0.101g (highest test level used for all axes) 0.572g (highest test level used for all axes) 5g (highest test level used for all axes)
Test duration per axis	10 min. 5 h
Test directions	X, Y and Z axes X, Y and Z axes X, Y and Z axes
Monitoring for contact faults/interruptions	Passed
Voltage drop measurement before and after each axis	Passed
Simulated service life test through increased levels of noise-like vibration	Test passed according to Section 9 of the standard
Extended test scope: Monitoring for contact faults/interruptions	Passed Passed
Extended test scope: Voltage drop measurement before and after each axis	Passed Passed
Shock test	Test passed according to Section 10 of the standard
Shock form	Half sine
Shock duration	30 ms
Number of shocks per axis	3 pos. und 3 neg.
Vibration and shock stress for rolling stock equipment	Passed

**Commercial data**

Product Group	3 (Multi Conn. System)
eCl@ss 10.0	27-44-03-09
eCl@ss 9.0	27-44-03-09
ETIM 9.0	EC002638
ETIM 8.0	EC002638
PU (SPU)	50 pcs
Packaging type	Box
Country of origin	DE
GTIN	4044918493093
Customs tariff number	85366990990

**Environmental Product Compliance**

RoHS Compliance Status	Compliant, No Exemption
------------------------	-------------------------

**Approvals / Certificates****General approvals**

Approval	Standard	Certificate Name
CCA DEKRA Certification B.V.	EN 61984	2169534.02
CCA DEKRA Certification B.V.	EN 61984	nl-54190
CSA DEKRA Certification B.V.	C22.2	1465035
UL Underwriters Laboratories Inc.	UL 1977	E 45171
UR Underwriters Laboratories Inc.	UL 1059	E45172

**Declarations of conformity and manufacturer's declarations**

Approval	Standard	Certificate Name
Railway WAGO GmbH & Co. KG	-	Railway Ready

**Approvals for marine applications**

Approval	Standard	Certificate Name
ABS American Bureau of Shipping	-	19-HG1869876-PDA
DNV DNV GL SE	-	TAE000016Z
LR Lloyds Register	IEC 61984	96/20035 (E5)

## Downloads

### Environmental Product Compliance

#### Compliance Search

Environmental Product  
Compliance 734-108



## Documentation

#### Additional Information

##### Technical Section

03.04.2019

pdf

2027.26 KB



## CAD/CAE-Data

#### CAD data

2D/3D Models 734-108



#### CAE data

EPLAN Data Portal  
734-108



ZUKEN Portal 734-108



## 1 Compatible Products

### 1.1 System counterpart

#### 1.1.1 Distribution connector



[Item No.: 734-368](#)

2-conductor combi strip; 100% protected  
against mismatching; 1.5 mm<sup>2</sup>; 8-pole; Pin  
spacing 3.5 mm; light gray



[Item No.: 734-368/037-000](#)

2-conductor combi strip; 100% protected  
against mismatching; 1.5 mm<sup>2</sup>; Locking  
lever; 8-pole; Pin spacing 3.5 mm; light  
gray



[Item No.: 734-368/008-000](#)

2-conductor combi strip; 100% protected  
against mismatching; Snap-in mounting  
feet; 1.5 mm<sup>2</sup>; Locking lever; 8-pole; Pin  
spacing 3.5 mm; light gray

#### 1.1.2 Male connector/plug



[Item No.: 734-308](#)

1-conductor male connector; CAGE  
CLAMP®; 1.5 mm<sup>2</sup>; Pin spacing 3.5 mm; 8-  
pole; 100% protected against mismatching;  
1.50 mm<sup>2</sup>; light gray



[Item No.: 734-308/019-000](#)

1-conductor male connector; CAGE  
CLAMP®; 1.5 mm<sup>2</sup>; Pin spacing 3.5 mm; 8-  
pole; 100% protected against mismatching;  
clamping collar; 1,50 mm<sup>2</sup>; light gray



[Item No.: 734-308/018-000](#)

1-conductor male connector; CAGE  
CLAMP®; 1.5 mm<sup>2</sup>; Pin spacing 3.5 mm; 8-  
pole; 100% protected against mismatching;  
DIN-35 rail/panel mounting; Snap-in  
mounting feet; 1,50 mm<sup>2</sup>; light gray



[Item No.: 734-168/105-604/997-407](#)

THR male header; 1.0 x 1.0 mm solder pin;  
angled; 100% protected against mismatching;  
in tape-and-reel packaging; Pin spacing  
3.5 mm; 8-pole; black



[Item No.: 734-168/105-604](#)

THR male header; 1.0 x 1.0 mm solder pin;  
angled; 100% protected against mismatching;  
Pin spacing 3.5 mm; 8-pole; black



[Item No.: 734-138/105-604/997-407](#)

THR male header; 1.0 x 1.0 mm solder pin;  
straight; 100% protected against mismatching;  
in tape-and-reel packaging; Pin spacing  
3.5 mm; 8-pole; black



[Item No.: 734-138/105-604](#)

THR male header; 1.0 x 1.0 mm solder pin;  
straight; 100% protected against mismatching;  
Pin spacing 3.5 mm; 8-pole; black



[Item No.: 734-408](#)

THT double-deck male header; 1.0 x 1.0  
mm solder pin; angled; 100% protected  
against mismatching; Pin spacing 3.5 mm;  
16-pole; light gray



[Item No.: 734-408/001-000](#)

THT double-deck male header; 1.0 x 1.0  
mm solder pin; angled; 100% protected  
against mismatching; Pin spacing 3.5 mm;  
16-pole; light gray



[Item No.: 734-168](#)

THT male header; 1.0 x 1.0 mm solder pin;  
angled; 100% protected against mismatching;  
Pin spacing 3.5 mm; 8-pole; light gray



[Item No.: 734-138/010-000](#)

THT male header; 1.0 x 1.0 mm solder pin;  
straight; 100% protected against mismatching;  
Gold-plated contacts; Pin spacing  
3.5 mm; 8-pole; light gray



[Item No.: 734-138](#)

THT male header; 1.0 x 1.0 mm solder pin;  
straight; 100% protected against mismatching;  
Pin spacing 3.5 mm; 8-pole; light gray

## 1.1.2 Male connector/plug

**Item No.: 734-138/046-000**

THT male header; 1.0 x 1.0 mm solder pin; straight; 100% protected against mismatching; Pin spacing 3.5 mm; 8-pole; light gray

## 1.2 Optional Accessories

## 1.2.1 Ferrule

## 1.2.1.1 Ferrule

**Item No.: 216-301**Ferrule; Sleeve for 0.25 mm<sup>2</sup> / AWG 24; insulated; electro-tin plated; yellow**Item No.: 216-321**Ferrule; Sleeve for 0.25 mm<sup>2</sup> / AWG 24; insulated; electro-tin plated; yellow**Item No.: 216-131**Ferrule; Sleeve for 0.25 mm<sup>2</sup> / AWG 24; uninsulated; electro-tin plated; silver-colored**Item No.: 216-302**Ferrule; Sleeve for 0.34 mm<sup>2</sup> / 22 AWG; insulated; electro-tin plated; light turquoise**Item No.: 216-322**Ferrule; Sleeve for 0.34 mm<sup>2</sup> / 22 AWG; insulated; electro-tin plated; light turquoise**Item No.: 216-132**Ferrule; Sleeve for 0.34 mm<sup>2</sup> / AWG 24; uninsulated; electro-tin plated**Item No.: 216-241**Ferrule; Sleeve for 0.5 mm<sup>2</sup> / 20 AWG; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; white**Item No.: 216-201**Ferrule; Sleeve for 0.5 mm<sup>2</sup> / 20 AWG; insulated; electro-tin plated; white**Item No.: 216-221**Ferrule; Sleeve for 0.5 mm<sup>2</sup> / 20 AWG; insulated; electro-tin plated; white**Item No.: 216-141**Ferrule; Sleeve for 0.5 mm<sup>2</sup> / 20 AWG; uninsulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 1/08.92**Item No.: 216-101**Ferrule; Sleeve for 0.5 mm<sup>2</sup> / AWG 22; uninsulated; electro-tin plated; silver-colored**Item No.: 216-121**Ferrule; Sleeve for 0.5 mm<sup>2</sup> / AWG 22; uninsulated; electro-tin plated; silver-colored**Item No.: 216-242**Ferrule; Sleeve for 0.75 mm<sup>2</sup> / 18 AWG; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; gray**Item No.: 216-262**Ferrule; Sleeve for 0.75 mm<sup>2</sup> / 18 AWG; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; gray**Item No.: 216-202**Ferrule; Sleeve for 0.75 mm<sup>2</sup> / 18 AWG; insulated; electro-tin plated; gray**Item No.: 216-222**Ferrule; Sleeve for 0.75 mm<sup>2</sup> / 18 AWG; insulated; electro-tin plated; gray**Item No.: 216-142**Ferrule; Sleeve for 0.75 mm<sup>2</sup> / 18 AWG; uninsulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 1/08.92**Item No.: 216-102**Ferrule; Sleeve for 0.75 mm<sup>2</sup> / AWG 20; uninsulated; electro-tin plated; silver-colored**Item No.: 216-122**Ferrule; Sleeve for 0.75 mm<sup>2</sup> / AWG 20; uninsulated; electro-tin plated; silver-colored**Item No.: 216-243**Ferrule; Sleeve for 1 mm<sup>2</sup> / AWG 18; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; red**Item No.: 216-263**Ferrule; Sleeve for 1 mm<sup>2</sup> / AWG 18; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; red**Item No.: 216-203**Ferrule; Sleeve for 1 mm<sup>2</sup> / AWG 18; insulated; electro-tin plated; red**Item No.: 216-223**Ferrule; Sleeve for 1 mm<sup>2</sup> / AWG 18; insulated; electro-tin plated; red**Item No.: 216-103**Ferrule; Sleeve for 1 mm<sup>2</sup> / AWG 18; uninsulated; electro-tin plated**Item No.: 216-143**Ferrule; Sleeve for 1 mm<sup>2</sup> / AWG 18; uninsulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 1/08.92**Item No.: 216-123**Ferrule; Sleeve for 1 mm<sup>2</sup> / AWG 18; uninsulated; electro-tin plated; silver-colored**Item No.: 216-204**Ferrule; Sleeve for 1.5 mm<sup>2</sup> / AWG 16; insulated; electro-tin plated; black**Item No.: 216-224**Ferrule; Sleeve for 1.5 mm<sup>2</sup> / AWG 16; insulated; electro-tin plated; black**Item No.: 216-244**Ferrule; Sleeve for 1.5 mm<sup>2</sup> / AWG 16; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; black**Item No.: 216-264**Ferrule; Sleeve for 1.5 mm<sup>2</sup> / AWG 16; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; black**Item No.: 216-284**Ferrule; Sleeve for 1.5 mm<sup>2</sup> / AWG 16; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; black**Item No.: 216-124**Ferrule; Sleeve for 1.5 mm<sup>2</sup> / AWG 16; uninsulated; electro-tin plated

### 1.2.1.1 Ferrule



#### Item No.: 216-144

Ferrule; Sleeve for 1.5 mm<sup>2</sup> / AWG 16; un-insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 1/08.92; silver-colored

#### Item No.: 216-104

Ferrule; Sleeve for 1.5 mm<sup>2</sup> / AWG 16; un-insulated; electro-tin plated; silver-colored

### 1.2.2 Insulation stop

#### 1.2.2.1 Insulation stop



#### Item No.: 734-671

Insulation stop; 0.08 - 0.2 mm<sup>2</sup> "s" (0.14 mm<sup>2</sup> "f-st"); 8 pieces/strip; light gray

### 1.2.3 Marking

#### 1.2.3.1 Marking strip



#### Item No.: 210-332/350-202

Marking strips; as a DIN A4 sheet; MAR-KED; 1-16 (240x); Height of marker strip: 3 mm; Strip length 182 mm; Horizontal marking; Self-adhesive; white



#### Item No.: 210-332/350-204

Marking strips; as a DIN A4 sheet; MAR-KED; 17-32 (240x); Height of marker strip: 3 mm; Strip length 182 mm; Horizontal marking; Self-adhesive; white



#### Item No.: 210-332/350-206

Marking strips; as a DIN A4 sheet; MAR-KED; 33-48 (240x); Height of marker strip: 3 mm; Strip length 182 mm; Horizontal marking; Self-adhesive; white

### 1.2.4 Strain relief

#### 1.2.4.1 Strain relief housing



#### Item No.: 734-608

Strain relief housing; for female and male connectors; 2 parts; Pin spacing 3.5 mm; 8-pole; light gray



#### Item No.: 734-128

Strain relief plate; for female and male connectors; 12.5 mm wide; 1 part; Pin spacing 3.5 mm; light gray

## 1.2.5 Test and measurement

## 1.2.5.1 Testing accessories



## Item No.: 735-500

WAGO Test pin; 1 mm Ø; 30 V AC / 60 V DC; CAT0; 1 A; 6 mm uninsulated; Test lead for soldering up to 0,5mm<sup>2</sup>

## 1.2.6 Tool

## 1.2.6.1 Operating tool



## Item No.: 734-190

Combination operating tool; natural



## Item No.: 734-231

Operating tool; black



## Item No.: 210-719

Operating tool; Blade: 2.5 x 0.4 mm; with a partially insulated shaft



## Item No.: 210-647

Operating tool; Blade: 2.5 x 0.4 mm; with a partially insulated shaft; multicoloured



## Item No.: 210-251

Operating tool; for MCS MICRO and MINI with CAGE CLAMP® connection; yellow



## Item No.: 210-250

Operating tool; for MCS MINI and MIDI with CAGE CLAMP® connection; red



## Item No.: 734-191

Operating tool; made of insulating material; 1-way; loose; black




## Item No.: 734-230

Operating tool; made of insulating material; 1-way; white

## Installation Notes


## Conductor termination




Inserting a conductor via (2.5 x 0.4) mm screwdriver – CAGE CLAMP® actuation perpendicular to conductor entry.



Inserting a conductor via (2.5 x 0.4) mm screwdriver – CAGE CLAMP® actuation parallel to conductor entry.




Inserting a conductor into CAGE CLAMP® unit via operating tool (734-191).




Inserting a conductor into CAGE CLAMP® unit via operating tool (210-251 or 210-250).

## Coding



Coding a female connector – removing coding finger(s).

## Testing




Testing via 1 mm Ø test pin (735-500) – CAGE CLAMP® connection – touch contact.

## Marking



Labeling via direct marking or self-adhesive strips.

## Installation



Strain relief housing for 734 Series Male and Female Connectors with CAGE CLAMP® connection