


Data Sheet | Item Number: 713-1468/107-000


THT male header, 2-row; 0.8 x 0.8 mm solder pin; straight; 100% protected against mismatching; with orientation nose; Threaded flange; Pin spacing 3.5 mm; 16-pole; black

<https://www.wago.com/713-1468/107-000>




Color: ■ black

Similar to illustration



Dimensions in mm
 $L = [(pole\ no./2) - 1] \times pin\ spacing + 13.6\ mm$



- Male headers may be mounted horizontally or vertically via straight or angled solder pins
- Header housing is molded of THT-compatible insulation material for lead-free reflow soldering
- Separated pin slots prevent damage and make the headers touch-proof when unplugged
- 100% protected against mismatching
- Coding option available

Notes	
Safety Information	The MCS – MULTI CONNECTION SYSTEM includes connectors without breaking capacity in accordance with DIN EN 61984. When used as intended, these connectors must not be connected/disconnected when live or under load. When used as intended, these connectors must not be connected/disconnected when live or under load. The circuit design should ensure header pins, which can be touched, are not live when unmated.
Variants:	Other pole numbers Other solder pin lengths Gold-plated or partially gold-plated contact surfaces Other versions (or variants) can be requested from WAGO Sales or configured at https://configurator.wago.com/ .



Electrical data

Ratings per IEC/EN 60664-1				Approvals per UL 1059			
Overvoltage category	III	III	II	Use group	B	C	D
Pollution degree	3	2	2	Rated voltage	150 V	50 V	-
Nominal voltage	80 V	160 V	250 V	Rated current	10 A	10 A	-
Rated surge voltage	2.5 kV	2.5 kV	2.5 kV				
Rated current	10 A	10 A	10 A				

Approvals per CSA			
Use group	B	C	D
Rated voltage	150 V	-	-
Rated current	12 A	-	-

Connection data

Total number of potentials	16	Connection 1	
Number of connection types	1	Pole number	16
Number of levels	2		

Physical data

Pin spacing	3.5 mm / 0.138 inches
Width	38.1 mm / 1.5 inches
Height	17.3 mm / 0.681 inches
Height from the surface	13.5 mm / 0.531 inches
Depth	13.3 mm / 0.524 inches
Solder pin length	3.8 mm
Solder pin dimensions	0.8 x 0.8 mm
Drilled hole diameter with tolerance	1.2 ^(+0.1) mm

Mechanical data

Variable coding	Yes
Anti-rotation protection	Yes

Plug-in connection

Contact type (pluggable connector)	Male connector/plug
Connector (connection type)	for PCB
Mismating protection	Yes
Mating direction to the PCB	90 °
Locking of plug-in connection	Threaded flange

PCB contact

PCB contact	THT
Solder pin arrangement	over the entire male connector (in-line)
Number of solder pins per potential	1



Material data	
Note (material data)	Information on material specifications can be found here
Color	black
Material group	I
Insulation material (main housing)	Polyphthalamide (PPA GF)
Flammability class per UL94	V0
Contact material	Electrolytic copper (E _{CU})
Contact Plating	Tin
Fire load	0.096 MJ
Weight	4.9 g

Environmental requirements	
Limit temperature range	-60 ... +100 °C
Processing temperature	-35 ... +60 °C

Commercial data	
Product Group	3 (Multi Conn. System)
eCl@ss 10.0	27-44-04-02
eCl@ss 9.0	27-44-04-02
ETIM 9.0	EC002637
ETIM 8.0	EC002637
PU (SPU)	25 pcs
Packaging type	Box
Country of origin	PL
GTIN	4045454809461
Customs tariff number	85366930000

Environmental Product Compliance	
CAS-No.	7439-92-1
REACH Candidate List Substance	Lead
RoHS Compliance Status	Compliant,With Exemption
RoHS Exemption	6(c)
SCIP notification number (Austria)	cdf476d4-58bb-4566-b76e-01d26a769321
SCIP notification number (Belgium)	d5162f37-1f76-41a1-bcf1-cf77dba0b616
SCIP notification number (Bulgaria)	520e2aae-f60e-4c4d-ad2d-e5a4b33bdd94
SCIP notification number (Czech Republic)	5c9bf379-2460-43df-9a8b-a109ce244ab5
SCIP notification number (Denmark)	09851d2c-d51c-4c9f-b5f5-b97f4e026be5
SCIP notification number (Finland)	c1f62820-b458-404c-8a03-17d0898aafa3
SCIP notification number (France)	638f6b7f-44ed-4fb2-be61-a4d9205df658
SCIP notification number (Germany)	e257a1c7-b176-4ce3-9892-76b69a2dc877
SCIP notification number (Hungary)	45b9b489-5533-409b-ab9d-daa73cf8a52c
SCIP notification number (Italy)	e7b29a11-8f13-43f1-adfe-1990bb87adea
SCIP notification number (Netherlands)	c38a8271-33fc-45d0-8a6b-f46899f2a000
SCIP notification number (Poland)	86b1b069-0a05-4fcb-8d05-05555a1a8f14
SCIP notification number (Romania)	3af53571-606c-4b28-b118-4fdf137d8a87
SCIP notification number (Sweden)	f5f35718-c7fe-44eb-819c-4034d4233d4f



Approvals / Certificates

General approvals



Approval	Standard	Certificate Name
CB DEKRA Certification B.V.	IEC 61984	NL-102427
CSA CSA Group	C22.2	2315087
KEMA/KEUR DEKRA Certification B.V.	EN 61984	71-133740
UL Underwriters Laboratories Inc.	UL 1059	UL-US-L45172-6187124-22905991-1

Downloads

Environmental Product Compliance

Compliance Search	
Environmental Product Compliance 713-1468/107-000	↓

Documentation

Additional Information			
Technical Section	03.04.2019	pdf 2027.26 KB	↓

CAD/CAE-Data

CAD data
2D/3D Models 713-1468/107-000



CAE data
ZUKEN Portal 713-1468/107-000



PCB Design
Symbol and Footprint via SamacSys 713-1468/107-000
Symbol and Footprint via Ultra Librarian 713-1468/107-000



1 Compatible Products

1.1 System counterpart

1.1.1 Female connector/socket



Item No.: [713-1108/107-000](#)
1-conductor female connector, 2-row; CA-GE CLAMP®; 1.5 mm²; Pin spacing 3.5 mm; 16-pole; 100% protected against mismatching; Screw flange; 1,50 mm²; black

1.2 Optional Accessories

1.2.1 Coding


1.2.1.1 Coding



Item No.: [714-101](#)
Coding key; orange

Installation Notes

Coding



Coding a male header by inserting a coding pin.