


Item no.: 750-514
 Product description: 2-CHANNEL RELAY OUTPUT MODULE AC 125 V, DC 30 V



Produkt kann von Bild abweichen / product may differ

Packing unit 1 piece

RoHS compliant

Product group	15 (I/O System)
Number of outputs	2 CHANGEOVER CONTACTS (SPDT)
Current consumption typ (internal)	70 mA
Switching voltage	AC 125 V / DC 30 V
Switching power	62.5 VA / 30 W
Switching current (max)	AC 0.5 A / DC 1 A
Switching current (min)	DC 0,01mA / 10mV
Max. switching frequency	20 / min
Pull-in time max.	4 ms
Drop-out time max.	4 ms
Contact material	Silver alloy, gold-plated
Mechanical life	1 x 10 ⁸ switching operations
Electrical life	2 x 10 ⁵ (AC 0.5 A / 125 V) 5x 10 ⁵ (DC 1 A / 30 V)
Isolation	1.5 kV EFF. (FIELD/SYSTEM), 2.5 kV RATED SURGE VOLTAGE; OVERVOLTAGE CATEGORY III
Internal data width (Bit)	2 Bit
Operating temperature	0 °C ... + 55 °C
Storage temperature	-25 °C ... +85 °C

Relative air humidity	95 %
Vibration resistance	acc. IEC 60068-2-6
Shock resistance	acc. IEC 60068-2-27
Degree of protection	IP 20
Conformity marking	CE



Approvals	ATEX
Cross section [mm ²]	0.08 - 2.5 mm ²
Cross section [AWG]	28 - 14 AWG
Connection method	CAGE CLAMP® CONNECTION
Weight	49.5 g
Color	light gray
Height	64 mm
Height	2.52 in
Width	12 mm
Width	0.472 in
Depth	100 mm
Depth	3.937 in
Strip length from	8 mm
Strip length to	9 mm
Strip length	0.33 in
Mounting	TS 35



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
750-514	ABS	03-HG374860/3-PDA			
750-514	BSH	Bescheinigung Nr. 467			
750-514	DNV	A-12306			
750-514	GL	26 898 - 05 HH			
750-514	KEMA	01 ATEX 1024 X			
750-514	PRS	TE/1720/880590/08			
750-514	Rina	ELE153207CS001			
750-514	UL	E175199 Sec.1			

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected