



PRODUCT SEARCH

TYPE NUMBER e.g.120-A-111

PRODUCTS

COMPANY

CONTACT US

SUPPORT

SITE MAP

e.g.20.874.002

PRODUCTS



CROSS-REFERENCE

**Eurostyle Screw Terminal Strips for Panel / Chassis Mounting**



**TYPE 323-FU-16.5-V (-HDS)**  
10 mm spacing - 1 to 12 poles



Distributor Stock Check



Series	Download PDF	3D Model	Can plug with	How to order	Color specifications	Print
--------	--------------	----------	---------------	--------------	----------------------	-------



**When locating connector, allow 0.5 mm clearance around it for process-induced variations.**

**Description**

The -FU designation provides a higher clearance and therefore higher creepage distances to meet certain VDE design requirements.  
The -V designation indicates that a wire stop is provided inside the block to control the wire insertion depth.

- Raised base
- With wire stop
- 16.5 mm height
- Recommended mounting hardware: M3.5 pan head screw (#6-32 pan head screw) or similar sized sheet metal screw, self-tapping screw or rivet.

**Technical Data**

**Center to Center Spacing:** 10 mm (0.394 in.)  
**Nominal Cross Section:** 2.5 mm<sup>2</sup> (3874 mils<sup>2</sup>)  
**Wire Stripping Length:** 6 mm (0.25 in.)

**Application**

The panel and chassis mounted series are ideal for connecting electrical control panels to external power sources, signal sources, other electrical panels and electrical loads of many types and sizes. The electrical panel's or electrical enclosure's internal components and circuitry are connected to their appropriate external electrical circuitry through these terminal blocks. The screw tightened connections result in high contact forces thus promoting safe wire secureness and retention, low electrical resistance and safe reusable connections. All wire retention screws are captive in their towers and they cannot fall out during transportation, installation and use. Wire protectors are available to protect small gauge stranded wires from screw damage. These terminal strips can be completely enclosed within the enclosures or be placed at an enclosure opening with one side accessible for external

**Approval Information**

UL File No.E69841   
CSA File No.LR24322

Rating	Current(A)	Voltage(V)	Application group	AWG
UL	30	300	B,D	22-10
CSA	25	300	B,D,E	26-10

\* UL 300V / C and 600V / D: if mounted on a suitable insulated surface, on standoffs, or equivalent means to maintain spacing from live parts to the mounting surface.

**Screw Tightening Torque:**

UL: 4.5 lbf·in  
CSA: 0.51 Nm

**International Approvals:**



**Material**

**Molding:** Polyamide, self extinguishing to UL 94, V-2, color off-white  
**Temperature limits:**  
**Short Time:** 140°C (284°F)  
**Continuous:** RTI 105°C (221°F)  
**Low Limit:** -40°C (-40°F)  
**Comparative Tracking Index:** CTI≥600V

cabling and the other for internal wiring. They can be specially marked to your specifications.

**Oxygen Index Rating:** 25%

**Terminal Body:** Nickel plated copper alloy

**Wire Protector:** Stainless steel strip

**Screw:** M3, Slotted head, zinc plated blue passivated, steel substrate

[Top of page](#)

### How to order

**Item** — **323-FU-16.5-V (-HDS)**

**Options**

- CN: Consecutive Numbering (hot stamped numbers)
- SM: Special Marking (please provide sketch)
- BS: Copper Alloy Screw
- PS: Zinc plated clear Passivated, steel substrate
- G05: Gold Plating (5 micro inches)
- G30: Gold Plating (30 micro inches)
- S30: Silver Plating (30 micro inches)

**Request sample**

**Request quote**

Quantity

**Accessories**

[BST Marking Strips for terminal strips.](#)

[Jumper Combs, Series 300-J.](#)

**Note:** Plated component for non HDS versions only: terminal body

**Ordering Note:** Series 300 Terminal Strips can be supplied in other colors. Can be supplied in polyamide UL 94 V-0. Please consult factory.

**323-FU-16.5-V**

WIRE PROTECTOR:  
with: - HDS

POLES:  
01 to 12

/

**Add to shopping cart**

2008, WECO Electrical Connectors Inc.

ISO 9001 registered quality management system