



## **Description**

- Pinstrip
- Plug-In Direction Parallel to PCB and Wire Entrance Perpendicular to PCB when plugged with 950-FL-DS

## **Technical Data**

**Center to Center Spacing:** 5 mm (0.197 in.)

**Recommended Hole Diameter in PC Board:** 1.6 mm (0.063 in.)

## **Material**

**Molding:** PBT GF (glass fiber reinforced), self extinguishing UL 94, V-0, color black

**Temperature limits:**

**Short Time:** 200°C (392°F)

**Continuous:** RTI 105°C (221°F)

**Low Limit:** -40°C (-40°F)

**Comparative Tracking Index:** CTI≥600V

**Oxygen Index Rating:** 32%

**Solder Pin:** solder side: 1.3 mm (0.052 in.), plug-in side: 1.3 mm (0.052 in.), Tin plated copper alloy