


Center to Center Spacing: 5 mm (0.197 in.)
 Recommended Hole Diameter in PC Board: 1.3 mm (0.051 in.)

REVISIONS		RELEASE				
REV.	DESCRIPTION OF REVISION	DATE (YY-MM-DD)	DRAWN	VERIFIED FOR ENG.	APPROVED: MFG. ENG.	APPROVED: PROJ. CNTR.
-	First release	05-06-14	C.C.	S.R.	X	X

Rating	Current(A)	Voltage(V)
UL	10	300
CSA	10	300

CUSTOMER APPROVAL	
DATE:.....	
COMPANY:.....	
NAME:.....	



WECCO ITEM: 971-SLK/08-003

0	0	X	X	X	<small>THIS INFORMATION DISCLOSED HEREIN WAS ORIGINATED BY AND IS THE PROPERTY OF WECCO ELECTRICAL CONNECTORS INC. AND EXCEPT FOR USES EXPRESSLY GRANTED TO A SECOND PARTY, WECCO ELECTRICAL CONNECTORS INC. RESERVES ALL PATENT, PROPRIETARY, DESIGN, USE, SALE, MANUFACTURING AND REPRODUCTION RIGHTS THEREIN. THIS DOES NOT APPLY TO ANY VENDOR PARTS.</small>	DRAWN	DATE (YMD)	WECCO Electrical Connectors Inc. 19900 CLARK GRAHAM, BATE D'URFE, QC, H9X-3R8, CANADA				
0	0	X	X	X		MATERIAL	C.C.	05-06-14	DESCRIPTION:			
0	0	X	X	X		SEE B.O.M.	S.R.	05-06-14	971-SLK/08-NZ			
0	0	X	X	X		FINISH	WEIGHT (g)	IHA139/REV-10/02-09-04	UNITS	SIZE	DRAWING NUMBER:	REV.
2	8	LST-1.1X8.5-SN-NZ	13.499.314	CuZn gal Sn	SEE B.O.M.	X		mm	A	13.498.150	-	
1	9/24	MLD-971-SLK/24	13.497.070	PBT VO , BLACK	TOLERANCES ARE IN MILLIMETERS UNLESS OTHERWISE INDICATED: .X = ±.3 .XX = ±.12 ANGLES ± 1°	REPLACES:	SCALE		X	SHEET	1 OF 1	
⊗	QTY.	DESCRIPTION	DRAWING NR.	MAT'L & FINISH	NONE							
BILL OF MATERIALS												