



**Depprogrammable Terminal Strips for Panel / Chassis Mounting**

**TYPE 302-NFLW-DS**


8 mm spacing - 1 to 12 poles



Distributor Stock Check



302-NFLW-DS



One possible variation of assembly



RoHS WEEE Pb free surface compliant

**Description**

These standard and low profile (N) versions were designed for use when space restrictions prevent horizontal insertion of the plug.

- Socket
- Low profile
- Plug-in direction perpendicular to wire entry direction when plugged with 302-NSLW (-HDS)
- Plug-in direction parallel with wire entry direction when plugged with 302-NSV (-DS)
- Entry for the plug is funnel-shaped to ease insertion
- Recommended mounting hardware: M2.5 pan head screw (#3-48 pan head screw) or similar sized sheet metal screw, self-tapping screw or rivet.



**Technical Data**

**Center to Center Spacing:** 8 mm (0.315 in.)

**Nominal Cross Section:**

1.5 mm<sup>2</sup> (2325 mils<sup>2</sup>)

**Wire Stripping Length:** 7 mm (0.28 in.)



Dimensions: mm (in.)

Length of Connector (L)

L = No. of Poles x Center to Center Spacing - 2 mm

**When locating connector, allow 0.5 mm clearance around it for process-induced variations.**

**Approval Information**

UL File No.E69841   
 CSA File No.LR24322

Rating	Current(A)	Voltage(V)	Application group	AWG
UL	10	300	B,D	22-14
CSA	10	300	B,D,E	26-14

\* UL 300V / C: if mounted on a suitable insulated surface, on standoffs, or equivalent means to maintain spacing from live parts to the mounting surface.

UL: Wire range is extended to 26 AWG for factory wiring.

**Screw Tightening Torque:**

UL: 3.5 lbf·in  
 CSA: 0.4 Nm

**Material**

**Molding:** Polyamide, self extinguishing to UL 94, V-2, color off-white

**Temperature limits:**

**Short Time:** 140°C (284°F)

**Continuous:** RTI 105°C (221°F)

**Low Limit:** -40°C (-40°F)

**Comparative Tracking Index:** CTI > 600

**Oxygen Index Rating:** 25%

**Application**

Whether panel, chassis, printed circuit or wire harness mounted, the 300 series terminal blocks are robust and versatile assets to complement your wiring needs. Male or female plugs can be on the wire harness or they can be on the panel, chassis or PCB. Male and female components can be adjusted for "connect ground first" type configurations where one of the components male or female is extended forward more than the other poles. Configurations with both male and female components can be designed to mate their appropriate counterparts. Plug in directions and wire entries can be oriented almost anyway possible with respect to the mounting surface. Insertion and extraction forces can be optimized for ease of use or for robustness to vibrations by utilizing different available models and sizes. All are designed to assure good stable electrical conductivity, good heat dissipation and repeated cycles of use. They can be specially marked to your specifications. The screw tightened connections result in high contact forces thus promoting safe wire secureness and retention, low electrical resistance and safe reusable connections. All wire retention screws are captive in their towers and they cannot fall out during transportation, installation and use. Wire protectors are available to protect small gauge stranded wires from screw damage.

**Terminal Body:** Nickel plated copper alloy  
**Wire Protector and Contact Spring:** Tin plated copper alloy  
**Screw:** M2.6, Slotted head, zinc plated blue passivated, steel substrate

**Item**

**302-NFLW-DS**

**Options**

- CN: Consecutive Numbering (hot stamped numbers)
- SM: Special Marking (please provide sketch)
- BS: Copper Alloy Screw
- PS: Clear Chromate Passivated, zinc plated, Steel Screws
- G05: Gold Plating (5 micro inches)
- G30: Gold Plating (30 micro inches)
- S30: Silver Plating (30 micro inches)

**Note:** Plated component: contact spring

**Ordering Note:** Series 300-S Terminal Strips can be supplied in other colors. Please consult factory.

**Accessories**

**302-NFLW-DS/**

POLES:  
01 to 12