



PRODUCT SEARCH

302-NSLW-HDS/08

e.g.20.874.002

PRODUCTS

COMPANY

CONTACT US

SUPPORT

SITE MAP

PRODUCTS



CROSS-REFERENCE

Deploable Terminal Strips for Panel / Chassis Mounting

TYPE 302-NSLW (-HDS)

8 mm spacing - 1 to 12 poles



Distributor Stock Check



Series	Download PDF	3D Model	Can plug with	How to order	Color specifications	Print
--------	--------------	----------	---------------	--------------	----------------------	-------




302-NSLW (-HDS)



One assembly



RoHS WEEE Pb free surface compliant



Dimensions: mm (in.)

Length of Connector (L)

L = No. of Poles x Center to Center Spacing - 2 mm

When locating connector, allow 0.5 mm clearance around it for process-induced variations.

Approval Information

UL File No.E69841



CSA File No.LR24322



Rating	Current(A)	Voltage(V)	Application group	AWG
UL	6	300	B,D	26-14
CSA	10	300	B,D,E	26-12

* UL 300V / C: if mounted on a suitable insulated surface, on standoffs, or equivalent means to maintain spacing from live parts to the mounting surface.
 UL: Wire range is extended to 26 AWG for factory wiring.
 Version DS is CSA certified for 26-14 AWG.

Description

- Standard Plug
- Plug-in direction perpendicular to wire entry direction when plugged with **302-NFLW-DS**
- Recommended mounting hardware: M2.5 pan head screw (#3-48 pan head screw) or similar sized sheet metal screw, self-tapping screw or rivet.

Technical Data

Center to Center Spacing: 8 mm (0.315 in.)
Nominal Cross Section: 1.5 mm² (2325 mils²)
Wire Stripping Length: 5 mm (0.20 in.)

Application

Whether panel, chassis, printed circuit or wire harness mounted, the 300 series terminal blocks are robust and versatile assets to complement your wiring needs. Male or female plugs can be on the wire harness or they can be on the panel, chassis or PCB. Male and female components can be adjusted for "connect ground first" type configurations where one of the components male or female is extended forward more than the other poles. Configurations with both male and female components can be designed to mate their appropriate counterparts. Plug in directions and wire entries can be oriented almost anyway possible with respect to the mounting surface. Insertion and extraction forces can be optimized for ease of use or for robustness to vibrations by utilizing different available models and sizes. All are designed to assure good stable electrical conductivity, good heat dissipation and repeated cycles of use. They can be specially marked to your specifications. The screw tightened connections result in high contact forces thus promoting safe wire secureness and retention, low electrical resistance and safe reusable connections. All wire retention screws are captive in their towers and they cannot fall out during transportation, installation and use. Wire protectors are available to protect small gauge stranded wires from screw damage.

Screw Tightening Torque:

UL: 3.5 lbf·in
 CSA: 0.4 Nm
Rated Impulse Withstand Voltage: 2500 V

Material

Molding: Polyamide, self extinguishing to UL 94, V-2, color off-white
Temperature limits:
Short Time: 140°C (284°F)
Continuous: RTI 105°C (221°F)
Low Limit: -40°C (-40°F)
Comparative Tracking Index: CTI ≥ 600V
Oxygen Index Rating: 25%

Terminal Body: Nickel plated copper alloy
Plug Pin: Tin plated copper alloy
Wire Protector: Stainless steel strip
Screw: M2.6, Yellow chromate passivated, zinc plated, steel

 [Top of page](#)

How to order

Item — **302-NSLW (-HDS)**

Options

- CN: Consecutive Numbering (hot stamped numbers)
- SM: Special Marking (please provide sketch)
- BS: Copper Alloy Screw
- PS: Zinc plated clear Passivated, steel substrate
- G05: Gold Plating (5 micro inches)
- G30: Gold Plating (30 micro inches)
- S30: Silver Plating (30 micro inches)

- Request sample**
- Request quote**

Quantity

Accessories

[BST Marking Strips for terminal strips.](#)
[Jumper Combs, Series 300-J.](#)

Note: Plated components: terminal body and pin

Ordering Note: Series 300-S Terminal Strips can be supplied in other colors. Please consult factory.

302-NSLW

WIRE PROTECTOR:
with: - HDS

POLES:
01 to 12

[Add to shopping cart](#)

2008, WECO Electrical Connectors Inc.

ISO 9001 registered quality management system