



PRODUCT SEARCH

TYPE NUMBER e.g.120-A-111

ARTICLE NUMBER e.g.20.874.002

PRODUCTS



CROSS-REFERENCE

Eurostyle Screw Terminal Strips for Panel / Chassis Mounting

TYPE 326 (-HDS)

14.5 mm spacing - 1 to 12 poles



Distributor Stock Check



Series	Download PDF	3D Model	Can plug with	How to order	Color specifications	Print
--------	--------------	----------	---------------	--------------	----------------------	-------



RoHS WEEE Pb free surface compliant

Description

- Standard version
- Recommended mounting hardware: M4 pan head screw (#8-32 pan head screw) or similar sized sheet metal screw, self-tapping screw or rivet.

Technical Data


**Center to Center Spacing:** 14.5 mm (0.571 in.)

**Nominal Cross Section:** 10 mm<sup>2</sup> (15497 mils<sup>2</sup>)

**Wire Stripping Length:** 9 mm (0.35 in.)

Application

The panel and chassis mounted series are ideal for connecting electrical control panels to external power sources, signal sources, other electrical panels and electrical loads of many types and sizes. The electrical panel's or electrical enclosure's internal components and circuitry are connected to their appropriate external electrical circuitry through these terminal blocks. The screw tightened connections result in high contact forces thus promoting safe wire secureness and retention, low electrical resistance and safe reusable connections. All wire retention screws are captive in their towers and they cannot fall out during transportation, installation and use. Wire protectors are available to protect small gauge stranded wires from screw damage. These terminal strips can be completely enclosed within the enclosures or be placed at an enclosure opening with one side accessible for external cabling and the other for internal wiring. They can be specially marked to your specifications.



Dimensions: mm (in.)

Length of Connector (L)

L = No. of Poles x Center to Center Spacing - 3 mm

When locating connector, allow 0.5 mm clearance around it for process-induced variations.

Approval Information

UL File No.E69841

CSA File No.LR24322

Rating	Current(A)	Voltage(V)	Application group	AWG
UL	50	300	B,D	14-8
CSA	55	300	B	14-8
CSA	10	300	D,E	14-8

\* UL 300V / C and 600 V / B,C,D: if mounted on a suitable insulated surface, on standoffs, or equivalent means to maintain spacing from live parts to the mounting surface.

Screw Tightening Torque:

UL: 10.0 lbf·in

CSA: 1.2 Nm

International Approvals:



Material

**Molding:** Polyamide, self extinguishing to UL 94, V-0, color off-white

Temperature limits:

**Short Time:** 140°C (284°F)

**Continuous:** RTI 105°C (221°F)

**Low Limit:** -40°C (-40°F)

**Comparative Tracking Index:** CTI≥600V

**Oxygen Index Rating:** 33%

**Terminal Body:** Nickel plated copper alloy

**Wire Protector:** Stainless steel strip

**Screw:** M4, Slotted head, zinc plated blue passivated, steel substrate

[Top of page](#)

### How to order

**Item** — 326 (-HDS)

**Options**

- CN: Consecutive Numbering (hot stamped numbers)
- SM: Special Marking (please provide sketch)
- G05: Gold Plating (5 micro inches)
- G30: Gold Plating (30 micro inches)
- S30: Silver Plating (30 micro inches)
- WS: Wire Stop (to control the wire insertion depth)

**Request sample**

**Request quote**

Quantity

**Accessories**

[BST Marking Strips for terminal strips.](#)

[Jumper Combs, Series 300-J.](#)

**Note:** Plated component for non HDS versions only: terminal body WS is for HDS versions only

**Ordering Note:** Series 300 Terminal Strips can be supplied in other colors. Please consult factory.

326

WIRE PROTECTOR:  
with: - HDS

POLES:  
01 to 12

[Add to shopping cart](#)

2008, WECO Electrical Connectors Inc.

ISO 9001 registered quality management system