



**Plug-in Screw Connector System for Printed Circuit Boards**

**TYPE 971-FBS (-DS)**

5 mm spacing - 2 to 24 poles



Distributor Stock Check




971-FBS (-DS)



One possible variation of assembly



RoHS WEEE Pb free surface compliant



**Dimensions: mm (in.)**

Length of Connector (L)

L = No. of Poles x Center to Center Spacing

**When locating connector, allow 0.5 mm clearance around it for process-induced variations.**

**Description**

- Plug
- Plug-In Direction and Wire Entrance Parallel to PCB when plugged with 950-SVG (-DS), 951-B-SV (-DS)
- Plug-In Direction and Wire Entrance Perpendicular to PCB when plugged with 971-FBSP, 971-SLK /-SLS /-SLW
- End-to-end stackable while maintaining the 5 mm spacing.

**Technical Data**

**Center to Center Spacing:** 5 mm (0.197 in.)

**Nominal Cross Section:**

2.5 mm<sup>2</sup> (3874 mils<sup>2</sup>)

**Wire Stripping Length:** 6.5 mm (0.26 in.)

**Approval Information**

UL File No.E69841

CSA File No.LR24322

Rating	Current(A)	Voltage(V)	Application group	AWG
UL	10	300	B,D	22-14
CSA	15	300	B,D,E	22-10

\* Version DS is CSA certified for 26-14 AWG.  
UL: 24-26 AWG range for factory wiring only.

**Screw Tightening Torque:**

UL: 4.5 lbf·in

CSA: 0.51 Nm

**International Approvals:**



**Rated Impulse Withstand Voltage:** 2500 V

**Material**

**Version:** 2 to 12 poles

**Molding:** Polyamide, self extinguishing UL 94, V-0, color grey  
**Temperature limits:**  
**Short Time:** 140°C (284°F)  
**Continuous:** RTI 105°C (221°F)  
**Low Limit:** -40°C (-40°F)  
**Comparative Tracking Index:** CTI > 600  
**Oxygen Index Rating:** 32%

**Version:** 13 to 24 poles  
**Molding:** Polyamide (glass fiber reinforced), self extinguishing UL 94, V-0, color grey  
**Temperature limits:**  
**Short Time:** 200°C (392°F)  
**Continuous:** RTI 105°C (221°F)  
**Low Limit:** -40°C (-40°F)  
**Comparative Tracking Index:** CTI > 175  
**Oxygen Index Rating:** 33%

**Terminal Body:** Tin plated copper alloy  
**Wire Protector:** Tin plated copper alloy  
**Spring Clip:** Stainless steel strip  
**Screw:** M3, Slotted head, zinc plated blue passivated, steel substrate

---

**Item**

**971-FBS (-DS)**

**Options**

- CN: Consecutive Numbering (hot stamped numbers)
- SM: Special Marking (please provide sketch)
- PS: Clear Chromate Passivated, zinc plated, Steel Screws
- WG: Wire Guide
- G05: Gold Plating (5 micro inches)
- G30: Gold Plating (30 micro inches)
- S30: Silver Plating (30 micro inches)

**Note:** Plated component: terminal body

**Accessories**

	WIRE PROTECTOR: with: - DS	/	POLES: 02 to 24
<b>971-FBS</b>			