


Data sheet

Commercial Art.No.: 25.392.3253.0

PCB pin header 8413 S / 2 W OB

PCB pin header with pin header, connection method depends on used socket part , 2 poles, pitch: 7.62 mm, type of packing: carton, color: grey



Certificates / Approvals



Technical data

General

Modular spacing	7.62 mm
Soldering process	Wave soldering
Packaging	Carton
Number of poles	2
Number of levels	1
Marking	No
Fastening	None
Mating direction towards (circuit) board	180°

Technical data

Rated current	12 A
Overvoltage Category I	1000 V
Overvoltage Category II	690 V
Overvoltage Category III	400 V
Rated impulse voltage	6 kV

Technical Data UL/CSA

Voltage UL	300 V
Current field wiring	15 A
Current factory wiring	15 A
Voltage CSA	300 V
Current CSA	15 A

Other

Type of insulation material	Thermoplastic
Color	Grey
Height	8.4 mm
Length	14.52 mm
Depth	12 mm
Material contact base	CuZn
Material contact surface	Sn

Classification



ECLASS 8.1	27440402
ETIM 7.0	EC002637
ETIM 6.0	EC002637
ETIM 5.0	EC002637
ETIM 4.0	EC002637

Product compliance

ROHS conformity status	Compliant
REACH-SVHC conformity status	Compliant

A

These dimensions will be especially checked at delivery
Only inspection dimensions
With /E marked dimensions are only valid for internal use



Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. Die Reproduktion, Distribution und Nutzung dieses Dokuments sowie die Kommunikation von its contents to others without express authorization is prohibited.


B

C

Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit /E gekennzeichnete Maße sind nur für interne Zwecke gültig

Schnitt A-A

section A-A



gezeichnete Ausführung:
7-polig
drawn version:
7-poles

Farbe /colour	.F
grau / grey	.0
schwarz/black	.1
grün /green	.7

Artikel-Nr. part number	Pol-Z pole	L	l	Typ type
25.392.3253	2	14,52	7,62	8413 S / 2 W OB
3353	3	22,14	15,24	8413 S / 3 W OB
3453	4	29,76	22,86	8413 S / 4 W OB
3553	5	37,38	30,48	8413 S / 5 W OB
3653	6	45,00	38,10	8413 S / 6 W OB
3753	7	52,62	45,72	8413 S / 7 W OB
3853	8	60,24	53,34	8413 S / 8 W OB
3953	9	67,86	60,96	8413 S / 9 W OB
4053	10	75,48	68,58	8413 S /10 W OB
4153	11	83,10	76,20	8413 S /11 W OB
4253	12	90,72	83,82	8413 S /12 W OB

Weitere Daten siehe Katalog
further data see catalog

Tolerierung nach DIN 7167/Tolerance system acc. to DIN 7167.
(This DIN-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach UU-TQM-05/03 ist einzuhalten.
Conformity with Wieland document UU-TQM-05/03 (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach General tolerance	DIN ISO 2768 - m	CAD - Zeichnung, keine manuellen Änderungen CAD - drawing, no manual modifications allowed	1.Verwendung: First Use:	Blatt: 1 von 1 Sheet: 1 of 1
--	------------------	---	-----------------------------	---------------------------------

	/		Werkstoff/Material	2011	Tag/Date	Name	Zeichnung Nr./Drawing No.	Index	
	/			gezeichnet drawn	28.11.	Schmitt J.			
	/			geprüft checked	-	-			
	/			Normgepr. Stand. check	-	-			
	/	Maßstab/Scale	2:1	Maße in mm/Dimensions are in mm					
	/	Vol.		mm ³	Ofl./Surf.	mm ²	Ersatz für/Replacement for: -		
	/		wieland	Type	Benennung/Tittle				
	/			8413 S /	LP-STIFTLISTE				
	/			.. W OB	Rastermaß 7,62 / pitch 7,62				
	/				PCB header				
Index	Datum / Blatt Date / Sheet								
Änderung/Revision									