


Eurostyle Screw Terminal Strips for Panel / Chassis Mounting

TYPE 327-FU (-HDS)

14.5 mm spacing - 1 to 12 poles



Distributor Stock Check



Description

The -FU designation provides a higher profile and therefore higher creepage distances to meet certain VDE design requirements.

- raised base
- Recommended mounting hardware: M4 pan head screw (#8-32 pan head screw) or similar sized sheet metal screw, self-tapping screw or rivet.

Technical Data


Center to Center Spacing: 14.5 mm (0.571 in.) Nominal Cross Section:

16 mm² (24796 mils²)

Wire Stripping Length: 9 mm (0.35 in.)

Application

The panel and chassis mounted series are ideal for connecting electrical control panels to external power sources, signal sources, other electrical panels and electrical loads of many types and sizes. The electrical panel's or electrical enclosure's internal components and circuitry are connected to their appropriate external electrical circuitry through these terminal blocks. The screw tightened connections result in high contact forces thus promoting safe wire secureness and retention, low electrical resistance and safe reusable connections. All wire retention screws are captive in their towers and they cannot fall out during transportation, installation and use. Wire protectors are available to protect small gauge stranded wires from screw damage. These terminal



Dimensions: mm (in.)

 $Length \ of \ Connector \ (L)$ L = No. of Poles x Center to Center Spacing - 3 mm

When locating connector, allow 0.5 mm clearance around it for process-induced variations.

Approval Information

UL File No.E69841 **N**CSA File No.LR24322

Rating	Current(A)	Voltage(V)	Application group	AWG	
· UL	65	600	B,C,D	14-6	
CSA	80	600	B,C,D,E	14-6	

Screw Tightening Torque:

UL: 16.0 Ifbin CSA: 2.0 Nm

International Approvals:











Material

Molding: Polyamide, self extinguishing to UL 94, V-0, color off-white

enclosures or be place one side accessible fo	ely enclosed within the ed at an enclosure opening wi r external cabling and the oth ey can be specially marked to	Temperature limits: Short Time: 140°C (284°F) Continuous: RTI 105°C (221°F) Low Limit: -40°C (-40°F) Comparative Tracking Index: CTI > 600 Oxygen Index Rating: 33%	
		Terminal Body: Nickel plated copper alloy Wire Protector: Stainless steel strip Screw: M5, Slotted head, zinc plated blue passivated steel substrate	
Item	327-FU (-HDS)		
Options	SM: Special Marking (p PS: Clear Chromate Pas G05: Gold Plating (5 mi G30: Gold Plating (30 n S30: Silver Plating (30	ssivated, zinc plated, Steel Screws (cro inches) nicro inches)	
Note: Plated compone	ent for non HDS versions only	terminal body WS is for HDS versions only	
Ordering Note: Serie	es 300 Terminal Strips can be	supplied in other colors. Please consult factory.	
Accessories	WIRE PROTECTOR:	POLES:	
327-FU	with: - HDS	01 to 12	