




# TYPE Jumper Combs, Type 327-J Inventory Check



RoHS WEEE Pb free compliant



Dimensions: mm (in.)

Length of Jumper (L)  $L = (\text{No. of Poles} \times \text{Center to Center Spacing})$

When locating connector, allow 0.5 mm clearance around it for process-induced variations.

## Description

Series 300-J jumper combs are designed for use with series 300 terminal strips, and allow electrical connection between adjacent poles. Jumper combs are secured in the terminal strip by the wire clamping screws, the exposed portion of the jumper is insulated to prevent accidental shock or short circuiting.

- For use with 326, 327 /-FU and HDS versions
- For electrical connection between adjacent poles

## Material

Jumper: tin plated copper alloy Insulation: PVC, color Insulation: red

### Temperature limits:

**Short Time:** 149°C (300°F)

**Continuous:** 93°C (200°F)

**Low Limit:** -34°C (-30°F)

**Comparative Tracking Index:** CTI > 600

**Oxygen Index Rating:** 39%

## Technical Data

2 to 12 poles

Item Jumper Combs, Type 327-J

POLES:  
02 to 12

327-J/

