



Product details

PCB TERMINAL 8258 / 2 TOP V OB

PCB terminal block with spring connection, without marking, with straight contact, 2-pole, pitch: 5,08 mm, series: 8285/2 TOP V OB



Basic information

Article number	25.781.0253.0
EAN	4015573503328
Unit of measure	Piece
Packaging Quantity	100

Classification

Technical Classification	PCB Terminal Blocks
Wieland Product Families	Unmarked

General Data

Modular spacing	5,08 mm
Connection type	Tension clamp connection
Soldering process	Wave soldering
Number of poles	2
Conductor to circuit board	90°
Number of levels	1
Integrated test socket	Yes
Insulation plate	No
Retaining pins	No
Marking	No

Technical Data

Nominal cross section	2.5 mm ²
Rated current	16 A
Rated current auxiliary power	1000 V
Rated voltage auxiliary power	690 V
Rated voltage VG3	250 V
Rated surge voltage	4 kV
wire strip length	9 mm



Product details

Connection Data

Minimum cross section solid	0.1 mm ²
Maximum cross section solid	4 mm ²
Minimum cross section fine stranded	0.1 mm ²
Maximum cross section fine stranded	2.5 mm ²

Technical Data UL/CSA

Cross section UL	30-12 AWG
Voltage UL	300 V
Current field wiring	20 A
Current factory wiring	20 A
Cross section CSA	22-12 AWG
Voltage CSA	300 V
Current CSA	20 A

Additional Data

Type of insulation material	Thermoplastic
Colour	Grey
Height	17.8 mm
Length	11.6 mm
Depth	15.4 mm