

Datasheet

Item No. 25.640.0753.0

PCB connector 8513 B / 7

PCB female connector, pitch 3,5 mm, wire lead in line with connecting direction, screw connection, 7-pole, colour grey, with marking, series: 8513 B/7



Item No.	25.640.0753.0
EAN	4015573561274
order unit	50 Piece(s)

Approvals



Technical data

General

Modular spacing	3.5 mm
-----------------	--------

Connection Data

Connection type	Screw connection
-----------------	------------------

General

Number of poles	7
Marking	Yes
Fastening	None
Mating direction towards connector	180°

Technical data

Nominal cross section	1.5 mm ²
Rated current	8 A
Rated current auxiliary power	690 V
Rated voltage auxiliary power	250 V
Rated voltage VG3	125
Rated impulse voltage	2.5

Connection Data

Wire strip length	6.5 mm
Minimum cross section solid	0.14 mm ²
Maximum cross section solid	1.5 mm ²
Minimum cross section fine stranded	0.14 mm ²
Maximum cross section fine stranded	1.5 mm ²

Technical Data UL/CSA

Cross section UL	30-16 AWG
Voltage UL	300

Current field wiring	8 A
Current factory wiring	8 A
Cross section CSA	22-14 AWG
Voltage CSA	300 V
Current CSA	5 A

Other

Type of insulation material	Thermoplastic
Colour	Grey
Height	11.1 mm
Length	24.5 mm
Depth	15.5 mm
Material attachment screw	Steel
Material contact base	CuSn
Material contact surface	Sn