



Specifications Sheet

Object	Internal Antenna	Page	1 of 6
Customer		Date	February 19, 2010
System	WLAN/ Bluetooth/ Zigbee	Rev.	A
Model Name	W5I-BO-07-F245	Written by	W. I. KWAK

Electrical Specifications

Frequency Range (MHz)	2400 ~ 2483.5
Band Width (MHz)	83.5
V.S.W.R (Min)	1.9 : 1
Gain (Max)	2.5 ± 1 (dBi)
Input Impedance	50 (Ω)
Polarization	Linear

Mechanical Specifications

Antenna Size (Length x Width x Height)	48 × 8 × 1 mm
Weight	N / A
Connector	I-PEX MHF
Cable Length	245 mm
Radiator Material	Copper
Operation Temperature	- 30 ~ 70 (°C)
Operation Humidity	10 ~ 90 (%)

Option	
Remarks	Data measured at free-space.

WINiZEN Co., Ltd.



Fig 1. Return Loss (Agilent E8357A 300KHz~6GHz PNA Series Network Analyzer)



Fig 2. V.S.W.R (Agilent E8357A 300KHz~6GHz PNA Series Network Analyzer)






Fig 3. Smith Chart (Agilent E8357A 300KHz ~ 6GHz PNA Series Network Analyzer)

LEFT




Fig 4. Measurement Configuration






Fig 5. Axis Definitions (Antenna Center)



- a. Azimuth Pattern (Co-pol) : XY Plane ; Horn Antenna Polarization : Vertical
- b. Elevation Pattern (Co-pol) : XZ Plane ; Horn Antenna Polarization : Horizontal
- c. Elevation Side Pattern (Co-pol) : YZ Plane ; Horn Antenna Polarization : Horizontal

Fig 6. Gain Patterns

a. Azimuth Pattern



b. Elevation Pattern






Fig 7. Antenna Mechanical

