


Data sheet

Commercial Art.No.: 25.155.0353.0

Printed circuit board terminal 8191 R / 3 Z OB

PCB terminal with screw connection with rising cage clamp system, 3 poles, with insulating plate, with solder pin (3.5mm), max. cross section: 2.5 mm², pitch: 5 mm, type of packing: carton, color: grey



Commercial Art.No.	25.155.0353.0
EAN	4015573509917
Order Unit	500

Certificates / Approvals



Technical data

General

Modular spacing	5 mm
Connection type	Screw connection
Soldering process	Wave soldering
Packaging	Carton
Number of poles	3
Conductor to circuit board	180°
Number of levels	1
Integrated test socket	No
Insulation plate	Yes
Retaining pins	No
Marking	No

Technical data

Nominal cross section	2.5 mm ²
Rated current	24 A
Overvoltage Category I	1000 V
Overvoltage Category II	690 V
Overvoltage Category III	250 V
Rated impulse voltage	4 kV
Wire strip length	6.5 mm

Connection Data

Minimum cross section solid	0.14 mm ²
Maximum cross section solid	4 mm ²
Minimum cross section fine stranded	0.14 mm ²
Maximum cross section fine stranded	2.5 mm ²

Wire strip length	6.5 mm
-------------------	--------

Technical Data UL/CSA

Cross section UL	22-12 AWG
Voltage UL	300 V
Current field wiring	20 A
Current factory wiring	30 A
Cross section CSA	22-12 AWG
Voltage CSA	300 V
Current CSA	25 A

Other

Type of insulation material	Thermoplastic
Color	Grey
Height	15 mm
Length	15.85 mm
Depth	11.5 mm
Material attachment screw	Steel
Material contact base	E-Cu
Material contact surface	Sn

Classification


ECLASS 11	
ECLASS 8.1	27440401
ETIM 7.0	EC002643
ETIM 6.0	EC002643
ETIM 5.0	EC002643
ETIM 4.0	EC002643

Product compliance


ROHS conformity status	Compliant/Exempted
ROHS exceptions	III-6(c)
REACH-SVHC conformity status	Duty-To-Declare
REACH-SVHC substances	Lead
REACH-SVHC CAS numbers	7439-92-1

These dimensions will be spot only checked at delivery
Only inspection dimensions
With $\varnothing$ marked dimensions are only valid for internal use

These Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit $\varnothing$ gekennzeichnete Maße sind nur für interne Zwecke gültig



A-A



.F	Farbe/colour
.0	grau/grey
.1	schwarz/black

25.155.2253.F- 25.155.3853.F	8191 R / 2 Z - 8191 R /18 Z	2- 18	T= (Polzahl -1) [number of poles -1] x5	L=T+5	1-18
25.155.0253.F- 25.155.1853.F	8191 R / 2 Z OB - 8191 R /18 Z OB	2- 18	T= (Polzahl -1) [number of poles -1] x5	L=T+5	
Teile-Nr. part-no.	Typ type	Polzahl number of poles	T	L	Beschriftung marking

Tolerierung nach DIN 7167/Tolerance system acc. to DIN 7167.
(This DIN-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverhalts- und Deklarationsliste nach UU-TOM-05/03 ist einzuhalten.
Conformity with Wieland document UU-TOM-05/03 (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach - CAD - Zeichnung, keine manuellen Änderungen
General tolerance EAD - drawing, no manual modifications allowed

1.Verwendung: - Blatt: 1 von 1
First Use: Sheet: 1 of 1

/		Werkstoff/Material	2008	Tag/Date	Name	T	Zeichnung Nr./Drawing No.
/			gezeichnet drawn	18.03.	Dutsch T.		25.155.0253.0
/	Maßstab/Scale		geprüft checked	-	-		
/	5:1		Normspr. Stand. check	-	-		
Made in mm/Dimensions are in mm							

/ Val. mm /Off./Surf. mm Ersatz für/Replacement for: -

	/		wieland	Type	Benennung/Title	PCB TERMINAL LP_KLEMME
	/			Index	Datum / Blatt Date / Sheet	8191 R
Änderung/Revision				Elektrische Verbindungen		

Weitere Daten siehe Katalog
further data see catalog

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet.
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.