

Multilayer Ceramic Antenna

DATA SHEET

6230 GPS /LP Multilayer Ceramic Chip Antenna

March, 2007, V4

							2007/03 V4
	6230 GPS Multilayer Ceramic Antenna (Linear Polarization)			CAN431111301158 2K CAN431111302158 2K CAN431111303158 2K			
Justin Liu spec.doc	C.T.Lee	March, 07	Page 1	sheet 190-1			A4

WIDE BAND MULTILAYER CERAMIC ANTENNA FOR 1575MHz ; 1675MHZ APPLICATION

Product Specification

QUICK REFERENCE DATA

Size	6.15*3.0*1.25 mm
Central Frequency	1.575 GHz
	1.675 GHz
Bandwidth	100 MHz
Gain	1 dBi Max
VSWR	2 max
Polarization	Linear
Azimuth	Omni-directional
Impedance	50Ω
Operating Temperature	-55~125 °C
Termination	Ni/Sn (Environmentally-Friendly Leadless)
Resistance to soldering heats	260°C, 10 sec.



Special Environmental Concerns- Green Products Design: The foil making process is using environmentally friendly aqueous solvent technology. Termination is lead free and packing materials can be re-cycled

						2007/03 V4
	6230 GPS Multilayer Ceramic Antenna (Linear Polarization)		CAN431111301158 2K CAN431111302158 2K CAN431111303158 2K			
Justin Liu spec.doc	C.T.Lee	March, 07	Page 2	sheet 190-2		A4

Mechanical data


Figure	Dimension	Port
	L	-
	W	-
	T	-
	F	Feed termination
		-

Dimension of soldering pad

Figure	Dimensions		Remark
	L	$6.70 \pm 0.15 \text{ mm}$	Feed pad
	W	$3.60 \pm 0.15 \text{ mm}$	
	F	$0.9 \pm 0.15 \text{ mm}$	


					2007/03 V4
	6230 GPS Multilayer Ceramic Antenna (Linear Polarization)		CAN431111301158 2K CAN431111302158 2K CAN431111303158 2K		
Justin Liu spec.doc	C.T.Lee	March, 07	Page 3	sheet 190-3	A4

3. Layout Recommendation in Application



							2007/03 V4
	6230 GPS Multilayer Ceramic Antenna (Linear Polarization)			CAN431111301158 2K CAN431111302158 2K CAN431111303158 2K			
Justin Liu spec.doc	C.T.Lee	March, 07	Page 4	sheet 190-4			A4


4. Measurement of S-parameter



	6230 GPS Multilayer Ceramic Antenna (Linear Polarization)					CAN431111301158 2K CAN431111302158 2K CAN431111303158 2K				2007/03 V4	
Justin Liu	C.T.Lee	March, 07		Page 5	sheet 190-5				A4		
spec.doc											


5.The Environment of Antenna Radiation Pattern

Anechoic Chamber Dimension=8(m) × 4(m) × 4(m)



						2007/03 V4
	6230 GPS Multilayer Ceramic Antenna (Linear Polarization)		CAN431111301158 2K CAN431111302158 2K CAN431111303158 2K			
Justin Liu spec.doc	C.T.Lee	March, 07	Page 6	sheet 190-6		A4

6. 3D Radiation Pattern (100x40 mm demo board)



						2007/03 V4
	6230 GPS Multilayer Ceramic Antenna (Linear Polarization)		CAN431111301158 2K CAN431111302158 2K CAN431111303158 2K			
Justin Liu spec.doc	C.T.Lee	March, 07	Page 7	sheet 190-7		A4

RELIABILITY DATA (Reference to IEC Specification)

IEC 384-10/ CECC 32 100 CLAUSE	IEC 6006868-2 TEST METHOD	TEST	PROCEDURE	REQUIREMENTS
4.4		Mounting	The antenna can be mounted on printed-circuit boards or ceramic substrates by applying wave soldering, reflow soldering (including vapour phase soldering) or conductive adhesive	No visible damage
4.5		Visual inspection and dimension check	Any applicable method using $\times 10$ magnification	In accordance with specification (no chip off 3 mm)
4.6.1		Antenna	Central Frequency at 20 °C	Standard test board in page 4
4.8		Adhesion	A force of 5 N applied for 10 s to the line joining the terminations and in a plane parallel to the substrate	No visible damage
4.9		Bond strength of plating on end face	Mounted in accordance with CECC 32 100, paragraph 4.4	No visible damage

					2007/03 V4		
	6230 GPS Multilayer Ceramic Antenna (Linear Polarization)				CAN431111301158 2K CAN431111302158 2K CAN431111303158 2K		
Justin Liu spec.doc	C.T.Lee	March, 07	Page 8	sheet 190-8			A4

IEC 384-10/ CECC 32 100 CLAUSE	IEC 6006868-2 TEST METHOD	TEST	PROCEDURE	REQUIREMENTS
			Conditions: bending 0.25 mm at a rate of 1mm/s, radius jig. 340 mm, 1 mm warp on FR4 board of 90 mm length	No visible damage
4.10	Tb	Resistance to soldering heat	260 ± 5 °C for 10 ± 0.5 s in a static solder bath	The terminations shall be well tinned after recovery and Central Freq. Change ± 6%
		Resistance to leaching	260 ± 5 °C for 30 ± 1 s in a static solder bath	Using visual enlargement of × 10, dissolution of the termination shall not exceed 15%
4.11	Ta	Solderability	Zero hour test, and test after storage (20 to 24 months) in original atmosphere; un-mounted chips completely immersed for 2 ± 0.5 s in 235 ± 5°C.	The termination must be well tinned, at least 75% is well tinned at termination
4.12	Na	Rapid change of temperature	-25 °C (30 minutes) to +85 °C (30 minutes); 5 cycles	No visible damage
4.14	Ca	Damp heat	500 ± 12 hours at 60 °C; 90 to 95 % RH	No visible damage 2 hours recovery


					2007/03 V4	
	6230 GPS Multilayer Ceramic Antenna (Linear Polarization)		CAN431111301158 2K CAN431111302158 2K CAN431111303158 2K			
Justin Liu spec.doc	C.T.Lee	March, 07	Page 9	sheet 190-9		A4

IEC 384-10/ CECC 32 100 CLAUSE	IEC 6006868-2 TEST METHOD	TEST	PROCEDURE	REQUIREMENTS
4.15		Endurance	500 ± 12 hours at 125 °C;	No visible damage 2 hours recovery

						2007/03 V4	
	6230 GPS Multilayer Ceramic Antenna (Linear Polarization)			CAN431111301158 2K CAN431111302158 2K CAN431111303158 2K			
Justin Liu spec.doc	C.T.Lee	March, 07	Page 10	sheet 190-			A4

									2007/03 V4			
	6230 GPS Multilayer Ceramic Antenna (Linear Polarization)				CAN431111301158 2K CAN431111302158 2K CAN431111303158 2K							
Justin Liu	C.T.Lee		March, 07			Page 11		sheet 190-				A4
spec.doc												


Taping Blister Tape



DIMENSION:

Serial no	Checking note	Index	Spec(mm)
1	Sprocket hole		1.50 ± 0.10
2	Pocket hole		≥ 1
3	Distance sprocket hole/sprocket hole	P_o	4.0 ± 0.10
4	Distance pocket/pocket	P_1	4.0 ± 0.10
5	Distance sprocket hole/pocket	P_2	2.0 ± 0.10
6	Tape width	W	12 ± 0.30
7	Distance sprocket hole/outside	E	1.75 ± 0.10
8	Distance sprocket hole/pocket	F	5.5 ± 0.10
9	Pocket length nominal clearance	A_o	3.38 ± 0.20
10	Pocket length nominal clearance	B_o	6.68 ± 0.20
11	Pocket depth minimum clearance	K_o	1.32 ± 0.20
12	Thickness of tape	T	0.23 ± 0.1
13	10x sprocket hole pitch	$10P_o$	40.0 ± 0.20

						2007/03 V4
		6230 GPS Multilayer Ceramic Antenna (Linear Polarization)		CAN431111301158 2K CAN431111302158 2K CAN431111303158 2K		
Justin Liu	C.T.Lee	March, 07	Page 12	sheet 190-		A4
spec.doc						



Dimensions in mm.
For reel dimensions see Table 3.

HBK039

TAPE WEITH (mm)	A (mm)	N (mm)	C (mm)	W ₁ (mm)	W ₂ MAX. (mm)
12	180	60±1	13 ^{+0.50} / _{-0.20}	12.4 ^{+2.0} / _{-0.0}	18.4

						2007/03 V4
	6230 GPS Multilayer Ceramic Antenna (Linear Polarization)			CAN431111301158 2K CAN431111302158 2K CAN431111303158 2K		
Justin Liu spec.doc	C.T.Lee	March, 07	Page 13	sheet 190-		A4

Revision Control:

Revision	Date	Content	Remark
1	Feb. 15, 2006	New Issued	
2	April. 18, 2006	Modification of dimension	
3	Oct. 4, 2006	Add description of antenna types in code nr.	
4	March, 2007	Add 3D radiation pattern and layout suggestion	

						2007/03 V4	
	6230 GPS Multilayer Ceramic Antenna (Linear Polarization)			CAN431111301158 2K CAN431111302158 2K CAN431111303158 2K			
Justin Liu spec.doc	C.T.Lee	March, 07		Page 14	sheet 190-		A4