

# APPROVAL SHEET

## MULTILAYER CERAMIC CAPACITORS

**High Capacitance Series**

**0402 to 1812 Sizes**

**X7R, X5R & Y5V Dielectrics**

**RoHS Compliance**

**CUSTOMER:**

**PRODUCTION\_PN:**

**ISSUE DATE:**

**APPROVED BY: Derak Peng**

\*Contents in this sheet are subject to change without prior notice.

## 1. DESCRIPTION

MLCC consists of a conducting material and electrodes. To manufacture a chip-type SMT and achieve miniaturization, high density and high efficiency, ceramic condensers are used.

WTC high capacitance MLCC offers low ESR and excellent frequency characteristics to be suited for coupling and decoupling applications in circuit. The high dielectric constant material X7R, X5R and Y5V are used for this series product.

## 2. FEATURES

- a. Small size with high capacitance.
- b. Capacitor with lead-free termination (pure Tin).

## 3. APPLICATIONS


- a. Digital circuit coupling or decoupling applications.
- b. For high frequency and high-density type power suppliers.
- c. For bypassing.

## 4. HOW TO ORDER

<u>1206</u>	<u>F</u>	<u>106</u>	<u>Z</u>	<u>100</u>	<u>C</u>	<u>I</u>
<u>Size</u>	<u>Dielectric</u>	<u>Capacitance</u>	<u>Tolerance</u>	<u>Rated voltage</u>	<u>Termination</u>	<u>Packaging</u>
Inch (mm) <b>0402</b> (1005) <b>0603</b> (1608) <b>0805</b> (2012) <b>1206</b> (3216) <b>1210</b> (3225) <b>1812</b> (4532)	<b>B</b> =X7R <b>X</b> =X5R <b>F</b> =Y5V	Two significant digits followed by no. of zeros. And R is in place of decimal point.  eg.: 106=10x10 <sup>6</sup> =10μF	<b>K</b> =±10% <b>M</b> =±20% <b>Z</b> =-20/+80%	Two significant digits followed by no. of zeros. And R is in place of decimal point.  <b>6R3</b> =6.3 VDC <b>100</b> =10 VDC <b>160</b> =16 VDC <b>250</b> =25 VDC <b>500</b> =50 VDC <b>101</b> =100 VDC	<b>C</b> =Cu/Ni/Sn	<b>T</b> =7" reeled <b>G</b> =13" reeled

## 5. EXTERNAL DIMENSIONS

Size Inch (mm)	L (mm)	W (mm)	T (mm)/Symbol	Remark	M <sub>B</sub> (mm)
0402 (1005)	1.00±0.05	0.50±0.05	0.50±0.05	N #	0.25 +0.05/-0.10
0603 (1608)	1.60±0.10	0.80±0.10	0.80±0.07	S	0.40±0.15
	1.60+0.15/-0.10	0.80+0.15/-0.10	0.80+0.15/-0.10	X	
0805 (2012)	2.00±0.15	1.25±0.10	0.80±0.10	B	0.50±0.20
			1.25±0.10	D #	
	2.00±0.20	1.25±0.20	1.25±0.20	I #	
1206 (3216)	3.20±0.15	1.60±0.15	0.95±0.10	C #	0.60±0.20
			1.25±0.10	D #	
	3.20±0.20	1.60±0.20	1.60±0.20	G #	
			1.15±0.15	J #	
3.20+0.30/-0.10	1.60+0.30/-0.10	1.60+0.30/-0.10	P #		
1210 (3225)	3.20±0.30	2.50±0.20	0.95±0.10	C #	0.75±0.25
			1.25±0.10	D #	
	3.20±0.40	2.50±0.30	1.60±0.20	G #	
			2.00±0.20	K #	
			2.50±0.30	M #	
1812 (4532)	4.50±0.40	3.20±0.30	1.25±0.10	D #	0.75±0.25
			2.00±0.20	K #	
	4.50±0.40	3.20±0.40	2.50±0.30	M #	



# Reflow soldering only is recommended.

## 6. GENERAL ELECTRICAL DATA

Dielectric	X7R	X5R	Y5V
Size	0402, 0603, 0805, 1206, 1210, 1812		
Capacitance range*	0.56μF to 10μF	0.027μF to 22μF	1μF to 100μF
Capacitance tolerance**	K (±10%), M (±20%)		Z (-20/+80%)
Rated voltage (WVDC)	6.3V, 10V, 16V, 25V, 50V, 100V		
Tan δ*	Note 1		
Insulation resistance at U <sub>r</sub>	RxC≥500ΩxF		
Operating temperature	-55 to +125°C	-55 to +85°C	-25 to +85°C
Capacitance characteristic	±15%		+30/-80%
Termination	Ni/Sn (lead-free termination)		

\* Measured at 1.0±0.2Vrms, 1.0kHz±10% for C≤10μF; 0.5±0.2Vrms, 120Hz±20% for C>10μF, 30~70% related humidity, 25°C ambient temperature for X7R, X5R and at 20°C for Y5V.

\*\* Preconditioning for Class II MLCC: Perform a heat treatment at 150±10°C for 1 hour, then leave in ambient condition for 24±2 hours before measurement.

Note 1:

X7R/X5R

Rated vol.	D.F. ≤	Exception of D.F. ≤
≥50V	2.5%	3% 0603 ≥ 0.047μF; 0805 ≥ 0.18μF; 1206 ≥ 0.47μF
25V	3.5%	5% 0805 ≥ 1μF; 1210 ≥ 10μF
		7% 0603 ≥ 0.33μF; 1206 ≥ 4.7μF
		10% 0402 ≥ 0.10μF; 0603 ≥ 0.47μF; 0805 ≥ 2.2μF; 1206 ≥ 6.8μF
16V	3.5%	5% 0402 ≥ 0.033μF; 0603 ≥ 0.15μF; 0805 ≥ 0.68μF; 1206 ≥ 2.2μF; 1210 ≥ 4.7μF
		10% 0603 ≥ 0.68μF; 0805 ≥ 2.2μF; 1206 ≥ 4.7μF; 1210 ≥ 22μF
10V	5%	10% 0402 ≥ 0.33μF; 0603 ≥ 0.33μF; 0805 ≥ 2.2μF; 1206 ≥ 2.2μF; 1210 ≥ 22μF;
		15% 0201 ≥ 0.1μF; 0402 ≥ 1μF
6.3V	10%	15% 0603 ≥ 10μF; 0805 ≥ 4.7μF; 1206 ≥ 47μF; 1210 ≥ 100μF;
		20% 0402 ≥ 2.2μF

Y5V

Rated vol.	D.F. ≤	Exception of D.F. ≤
≥50V	5%	7% 0603 ≥ 0.1μF; 0805 ≥ 0.47μF; 1206 ≥ 4.7μF
35V	7%	---
25V	5%	7% 0402 ≥ 0.047μF; 0603 ≥ 0.1μF; 0805 ≥ 0.33μF; 1206 ≥ 1μF; 1210 ≥ 4.7μF
		9% 0402 ≥ 0.068μF; 0603 ≥ 0.47μF; 1206 ≥ 4.7μF; 1210 ≥ 22μF
16V (C<1.0μF)	7%	9% 0402 ≥ 0.068μF; 0603 ≥ 0.68μF
		12.5% 0402 ≥ 0.22μF
16V (C≥1.0μF)	9%	12.5% 0603 ≥ 2.2μF; 0805 ≥ 3.3μF; 1206 ≥ 10μF; 1210 ≥ 22μF; 1812 ≥ 47μF
		20% 0402 ≥ 0.47μF
10V	12.5%	---
6.3V	20%	---

## 7. CAPACITANCE RANGE

### 7-1 X7R Dielectric

DIELECTRIC		X7R																					
SIZE		0603			0805				1206					1210				1812					
RATED VOLTAGE		6.3	10	16	6.3	10	16	25	6.3	10	16	25	50	10	16	25	50	100	10	16	25	50	100
Capacitance	0.56μF (564)		X	X																			
	0.68μF (684)		X	X																			
	0.82μF (824)		X	X																			
	1.0μF (105)	X	X	X		D	D	D		J	J	J	P	D	D	D	D	K	D	D	D	K	K
	1.5μF (155)					I			J	J	J	P											K
	2.2μF (225)		X		I	I	I	I	J	J	J	P			K	G							M
	3.3μF (335)									P	P	P				G							
	4.7μF (475)				I	I			P	P	P	P		K	K	K							
	6.8μF (685)																						
	10μF (106)								P	P	P			K	K	K			M	M	M		

1. The letter in cell is expressed the symbol of product thickness.

### 7-2 X5R Dielectric

Dielectric		X5R																				
Size		0402				0603				0805				1206				1210				1812
Rated Voltage (VDC)		6.3	10	16	25	6.3	10	16	25	6.3	10	16	25	6.3	10	16	25	6.3	10	16	25	6.3
Capacitance	0.027μF (273)			N																		
	0.033μF (333)			N																		
	0.039μF (393)			N																		
	0.047μF (473)			N																		
	0.056μF (563)		N	N																		
	0.068μF (683)		N	N																		
	0.082μF (823)	N	N	N																		
	0.10μF (104)	N	N	N	N																	
	0.15μF (154)																					
	0.22μF (224)	N	N	N				X	X													
	0.27μF (274)						X	X														
	0.33μF (334)	N	N			X	X	X	X													
	0.39μF (394)						X	X														
	0.47μF (474)	N	N				X	X	X													
	0.68μF (684)	N	N				X	X	X													
	0.82μF (824)					X	X	X														
	1.0μF (105)	N	N			X	X	X	X													
	1.5μF (155)					X				I	I				J	J			K	K		
	2.2μF (225)	N				X	X	X		I	I	I	I		J	J	P		K	K		
	3.3μF (335)									I	I	I	I		P	P	P					
4.7μF (475)	N				X	X			I	I	I	I		P	P	P	P		K	K	K	
6.8μF (685)														P	P							
10μF (106)					X				I	I	I			P	P	P	P	K	K	K	K	
22μF (226)									I	I				P	P			M	M	M		
47μF (476)									I					P				M	M			
100μF (107)																		M				U

1. The letter in cell is expressed the symbol of product thickness.

### 7-3 Y5V Dielectric

DIELECTRIC		Y5V										
SIZE		0402		0603				0805				
RATED VOLTAGE (VDC)		63	10	63	10	16	25	6.3	10	16	25	50
Capacitance	1.0μF (105)	N	N		S	X	X		B	B	D	D
	1.5μF (155)				S				D	D		
	2.2μF (225)			S	S	X			D	D	I	I
	3.3μF (335)								D	D		
	4.7μF (475)			X	X				D	D	I	
	6.8μF (685)								I			
	10μF (106)							I	I	I		
	22μF (226)							I				

DIELECTRIC		Y5V																
SIZE		1206					1210					1812						
RATED VOLTAGE (VDC)		10	16	25	35	50	6.3	10	16	25	35	50	6.3	10	16	25	50	100
Capacitance	1.0μF (105)	C	C	C		C		C	C	C		C		D	D	D	D	D
	1.5μF (155)	C	C	C				C	C	C				D	D	D	D	
	2.2μF (225)	C	C	C		J		C	C	C		G		D	D	D	D	
	3.3μF (335)	J	J	J				C	C	C				D	D	D	D	
	4.7μF (475)	J	J	J	J	P		C	C	D		G		D	D	D	D	
	6.8μF (685)	J	J					C	C	D				D	D	D	D	
	10μF (106)	J	J	P				D	D	G	K	G		D	D	D	K	
	22μF (226)	P	P					K	K	K								
	47μF (476)		P				K	K							M			
	100μF (107)						M											

1. The letter in cell is expressed the symbol of product thickness.





### 8. PACKAGING STYLE AND QUANTITY

Size	Thickness (mm)/Symbol		Paper tape		Plastic tape	
			7" reel	13" reel	7" reel	13" reel
0402 (1005)	0.50±0.05	N	10k	50k	-	-
0603 (1608)	0.80±0.07	S	4k	15k	-	-
	0.80+0.15/-0.10	X	4k	15k	-	-
0805 (2012)	0.80±0.10	B	4k	15k	-	-
	1.25±0.10	D	-	-	3k	10k
	1.25±0.20	I	-	-	3k	10k
1206 (3216)	0.95±0.10	C	-	-	3k	10k
	1.15±0.15	J	-	-	3K	10K
	1.25±0.10	D	-	-	3k	10k
	1.60±0.20	G	-	-	2k	-
	1.60+0.30/-0.10	P	-	-	2k	-
1210 (3225)	0.95±0.10	C	-	-	3k	10k
	1.25±0.10	D	-	-	3k	10k
	1.60±0.20	G	-	-	2k	-
	2.00±0.20	K	-	-	1k	-
	2.50±0.30	M	-	-	1k	-
1812 (4532)	1.25±0.10	D	-	-	1k	-
	2.00±0.20	K	-	-	1k	-
	2.50±0.30	M	-	-	0.5k	-

Unit: pieces

## 9. ELECTRICAL CHARACTERISTICS

### Typical Impedance/ESR vs. Frequency



### 10. RELIABILITY TEST CONDITIONS AND REQUIREMENTS

No.	Item	Test Condition	Requirements																																																																								
1.	Visual and Mechanical	---	* No remarkable defect. * Dimensions to conform to individual specification sheet.																																																																								
2.	Capacitance	Class I:NPO	* Shall not exceed the limits given in the detailed spec.																																																																								
3.	Q/ D.F. (Dissipation Factor)	Cap≤1000pF 1.0±0.2Vrms, 1MHz±10% Cap>1000pF 1.0±0.2Vrms, 1KHz±10%  Class II:X7R, X5R, Y5V Cap≤10μF, 1.0±0.2Vrms, 1kHz±10% Cap>10μF, 0.5±0.2Vrms, 120Hz±20%	* NP0: Cap≥30pF, Q≥1000; Cap<30pF,Q≥400+20C X7R, X5R: <table border="1"> <thead> <tr> <th>Rated vol.</th> <th>D.F. ≤</th> <th colspan="2">Exception of D.F. ≤</th> </tr> </thead> <tbody> <tr> <td rowspan="3">≥ 50V</td> <td rowspan="3">2.5%</td> <td>3%</td> <td>0603≥ 0.047μF; 0805≥ 0.18μF;1206≥ 0.47μF</td> </tr> <tr> <td>5%</td> <td>0805≥ 1μF; 1210≥ 10μF</td> </tr> <tr> <td>7%</td> <td>0603≥ 0.33μF; 1206≥ 4.7μF</td> </tr> <tr> <td rowspan="3">25V</td> <td rowspan="3">3.5%</td> <td>10%</td> <td>0402≥ 0.10μF;0603≥ 0.47μF; 0805≥ 2.2μF; 1206≥ 6.8μF</td> </tr> <tr> <td rowspan="2">16V</td> <td>5%</td> <td>0402≥ 0.033μF; 0603≥ 0.15μF; 0805≥ 0.68μF;1206≥ 2.2μF;1210≥ 4.7μF</td> </tr> <tr> <td>10%</td> <td>0603≥ 0.68μF;0805≥ 2.2μF; 1206≥ 4.7μF;1210≥ 22μF</td> </tr> <tr> <td rowspan="3">10V</td> <td rowspan="3">5%</td> <td>10%</td> <td>0402≥ 0.33μF;0603≥ 0.33μF; 0805≥ 2.2μF;1206≥ 2.2μF;1210≥ 22μF;</td> </tr> <tr> <td>15%</td> <td>0201≥ 0.1μF; 0402≥ 1μF</td> </tr> <tr> <td>6.3V</td> <td>10%</td> <td>0603≥ 10μF; 0805≥ 4.7μF; 1206≥ 47μF; 1210≥ 100μF;</td> </tr> <tr> <td></td> <td></td> <td>20%</td> <td>0402≥ 2.2μF</td> </tr> </tbody> </table> Y5V: <table border="1"> <thead> <tr> <th>Rated vol.</th> <th>D.F.≤</th> <th colspan="2">Exception of D.F.≤</th> </tr> </thead> <tbody> <tr> <td>≥ 50V</td> <td>5%</td> <td>7%</td> <td>0603≥ 0.1μF; 0805≥ 0.47μF; 1206≥ 4.7μF</td> </tr> <tr> <td>35V</td> <td>7%</td> <td>---</td> <td>---</td> </tr> <tr> <td rowspan="2">25V</td> <td rowspan="2">5%</td> <td>7%</td> <td>0402≥ 0.047μF;0603≥ 0.1μF; 0805≥ 0.33μF;1206≥ 1μF; 1210≥ 4.7μF</td> </tr> <tr> <td>9%</td> <td>0402≥ 0.068μF;0603≥ 0.47μF; 1206≥ 4.7μF; 1210≥ 22μF</td> </tr> <tr> <td>16V (C&lt;1.0μF)</td> <td>7%</td> <td>9%</td> <td>0402≥ 0.068μF; 0603≥ 0.68μF</td> </tr> <tr> <td></td> <td></td> <td>12.5%</td> <td>0402≥ 0.22μF</td> </tr> <tr> <td>16V (C≥ 1.0μF)</td> <td>9%</td> <td>12.5%</td> <td>0603≥ 2.2μF; 0805≥ 3.3μF; 1206≥ 10μF; 1210≥ 22μF; 1812≥ 47μF</td> </tr> <tr> <td>10V</td> <td>12.5%</td> <td>20%</td> <td>0402≥ 0.47μF</td> </tr> <tr> <td>6.3V</td> <td>20%</td> <td>---</td> <td>---</td> </tr> </tbody> </table>	Rated vol.	D.F. ≤	Exception of D.F. ≤		≥ 50V	2.5%	3%	0603≥ 0.047μF; 0805≥ 0.18μF;1206≥ 0.47μF	5%	0805≥ 1μF; 1210≥ 10μF	7%	0603≥ 0.33μF; 1206≥ 4.7μF	25V	3.5%	10%	0402≥ 0.10μF;0603≥ 0.47μF; 0805≥ 2.2μF; 1206≥ 6.8μF	16V	5%	0402≥ 0.033μF; 0603≥ 0.15μF; 0805≥ 0.68μF;1206≥ 2.2μF;1210≥ 4.7μF	10%	0603≥ 0.68μF;0805≥ 2.2μF; 1206≥ 4.7μF;1210≥ 22μF	10V	5%	10%	0402≥ 0.33μF;0603≥ 0.33μF; 0805≥ 2.2μF;1206≥ 2.2μF;1210≥ 22μF;	15%	0201≥ 0.1μF; 0402≥ 1μF	6.3V	10%	0603≥ 10μF; 0805≥ 4.7μF; 1206≥ 47μF; 1210≥ 100μF;			20%	0402≥ 2.2μF	Rated vol.	D.F.≤	Exception of D.F.≤		≥ 50V	5%	7%	0603≥ 0.1μF; 0805≥ 0.47μF; 1206≥ 4.7μF	35V	7%	---	---	25V	5%	7%	0402≥ 0.047μF;0603≥ 0.1μF; 0805≥ 0.33μF;1206≥ 1μF; 1210≥ 4.7μF	9%	0402≥ 0.068μF;0603≥ 0.47μF; 1206≥ 4.7μF; 1210≥ 22μF	16V (C<1.0μF)	7%	9%	0402≥ 0.068μF; 0603≥ 0.68μF			12.5%	0402≥ 0.22μF	16V (C≥ 1.0μF)	9%	12.5%	0603≥ 2.2μF; 0805≥ 3.3μF; 1206≥ 10μF; 1210≥ 22μF; 1812≥ 47μF	10V	12.5%	20%	0402≥ 0.47μF	6.3V	20%	---	---
Rated vol.	D.F. ≤	Exception of D.F. ≤																																																																									
≥ 50V	2.5%	3%	0603≥ 0.047μF; 0805≥ 0.18μF;1206≥ 0.47μF																																																																								
		5%	0805≥ 1μF; 1210≥ 10μF																																																																								
		7%	0603≥ 0.33μF; 1206≥ 4.7μF																																																																								
25V	3.5%	10%	0402≥ 0.10μF;0603≥ 0.47μF; 0805≥ 2.2μF; 1206≥ 6.8μF																																																																								
		16V	5%	0402≥ 0.033μF; 0603≥ 0.15μF; 0805≥ 0.68μF;1206≥ 2.2μF;1210≥ 4.7μF																																																																							
			10%	0603≥ 0.68μF;0805≥ 2.2μF; 1206≥ 4.7μF;1210≥ 22μF																																																																							
10V	5%	10%	0402≥ 0.33μF;0603≥ 0.33μF; 0805≥ 2.2μF;1206≥ 2.2μF;1210≥ 22μF;																																																																								
		15%	0201≥ 0.1μF; 0402≥ 1μF																																																																								
		6.3V	10%	0603≥ 10μF; 0805≥ 4.7μF; 1206≥ 47μF; 1210≥ 100μF;																																																																							
		20%	0402≥ 2.2μF																																																																								
Rated vol.	D.F.≤	Exception of D.F.≤																																																																									
≥ 50V	5%	7%	0603≥ 0.1μF; 0805≥ 0.47μF; 1206≥ 4.7μF																																																																								
35V	7%	---	---																																																																								
25V	5%	7%	0402≥ 0.047μF;0603≥ 0.1μF; 0805≥ 0.33μF;1206≥ 1μF; 1210≥ 4.7μF																																																																								
		9%	0402≥ 0.068μF;0603≥ 0.47μF; 1206≥ 4.7μF; 1210≥ 22μF																																																																								
16V (C<1.0μF)	7%	9%	0402≥ 0.068μF; 0603≥ 0.68μF																																																																								
		12.5%	0402≥ 0.22μF																																																																								
16V (C≥ 1.0μF)	9%	12.5%	0603≥ 2.2μF; 0805≥ 3.3μF; 1206≥ 10μF; 1210≥ 22μF; 1812≥ 47μF																																																																								
10V	12.5%	20%	0402≥ 0.47μF																																																																								
6.3V	20%	---	---																																																																								
4.	Dielectric Strength	* To apply voltage (≤100V) 250%. * Duration: 1 to 5 sec. * Charge and discharge current less than 50mA.	* No evidence of damage or flash over during test.																																																																								
5.	Insulation Resistance	To apply rated voltage for max. 120 sec.	10GΩ or RxC≥ 500Ω-F whichever is smaller. Class II (X7R, X5R, Y5V) <table border="1"> <thead> <tr> <th>Rated voltage</th> <th>Insulation Resistance</th> </tr> </thead> <tbody> <tr> <td>100V: X7R</td> <td rowspan="4">10GΩ or RxC≥ 100 Ω-F whichever is smaller.</td> </tr> <tr> <td>16V:0402≥0.22μF</td> </tr> <tr> <td>10V:0201≥47nF;0402≥0.47μF;0603≥0.47μF ; 0805≥2.2μF;1206≥4.7μF;1210≥47μF</td> </tr> <tr> <td>6.3V</td> </tr> </tbody> </table>	Rated voltage	Insulation Resistance	100V: X7R	10GΩ or RxC≥ 100 Ω-F whichever is smaller.	16V:0402≥0.22μF	10V:0201≥47nF;0402≥0.47μF;0603≥0.47μF ; 0805≥2.2μF;1206≥4.7μF;1210≥47μF	6.3V																																																																	
Rated voltage	Insulation Resistance																																																																										
100V: X7R	10GΩ or RxC≥ 100 Ω-F whichever is smaller.																																																																										
16V:0402≥0.22μF																																																																											
10V:0201≥47nF;0402≥0.47μF;0603≥0.47μF ; 0805≥2.2μF;1206≥4.7μF;1210≥47μF																																																																											
6.3V																																																																											
6.	Temperature Coefficient	With no electrical load. <table border="1"> <thead> <tr> <th>T.C.</th> <th>Operating Temp</th> </tr> </thead> <tbody> <tr> <td>NPO</td> <td>-55~125°C at 25°C</td> </tr> <tr> <td>X7R</td> <td>-55~125°C at 25°C</td> </tr> <tr> <td>X5R</td> <td>-55~ 85°C at 25°C</td> </tr> <tr> <td>Y5V</td> <td>-25~ 85°C at 20°C</td> </tr> </tbody> </table>	T.C.	Operating Temp	NPO	-55~125°C at 25°C	X7R	-55~125°C at 25°C	X5R	-55~ 85°C at 25°C	Y5V	-25~ 85°C at 20°C	<table border="1"> <thead> <tr> <th>T.C.</th> <th>Capacitance Change</th> </tr> </thead> <tbody> <tr> <td>NPO</td> <td>Within ±30ppm/°C</td> </tr> <tr> <td>X7R</td> <td>Within ±15%</td> </tr> <tr> <td>X5R</td> <td>Within ±15%</td> </tr> <tr> <td>Y5V</td> <td>Within +30%/-80%</td> </tr> </tbody> </table>	T.C.	Capacitance Change	NPO	Within ±30ppm/°C	X7R	Within ±15%	X5R	Within ±15%	Y5V	Within +30%/-80%																																																				
T.C.	Operating Temp																																																																										
NPO	-55~125°C at 25°C																																																																										
X7R	-55~125°C at 25°C																																																																										
X5R	-55~ 85°C at 25°C																																																																										
Y5V	-25~ 85°C at 20°C																																																																										
T.C.	Capacitance Change																																																																										
NPO	Within ±30ppm/°C																																																																										
X7R	Within ±15%																																																																										
X5R	Within ±15%																																																																										
Y5V	Within +30%/-80%																																																																										
7.	Adhesive Strength of Termination	* Pressurizing force : 5N (≤0603) and 10N (>0603) * Test time: 10±1 sec.	* No remarkable damage or removal of the terminations.																																																																								

No.	Item	Test Condition	Requirements															
8.	Vibration Resistance	<ul style="list-style-type: none"> <li>* Vibration frequency: 10~55 Hz/min.</li> <li>* Total amplitude: 1.5mm</li> <li>* Test time: 6 hrs. (Two hrs each in three mutually perpendicular directions.)</li> </ul>	<ul style="list-style-type: none"> <li>* No remarkable damage.</li> <li>* Cap change and Q/D.F.: To meet initial spec.</li> </ul>															
9.	Solderability	<ul style="list-style-type: none"> <li>* Solder temperature: 235±5°C</li> <li>* Dipping time: 2±0.5 sec.</li> </ul>	95% min. coverage of all metalized area.															
10.	Bending Test	<ul style="list-style-type: none"> <li>* The middle part of substrate shall be pressurized by means of the pressurizing rod at a rate of about 1 mm per second until the deflection becomes 1 mm and then the pressure shall be maintained for 5±1 sec.</li> <li>* Measurement to be made after keeping at room temp. for 24±2 hrs. (Class I) or 48±4 hrs. (Class II).</li> </ul>	<ul style="list-style-type: none"> <li>* No remarkable damage.</li> <li>* Cap change : NP0: within ±5% or 0.5pF whichever is larger X7R, X5R: within ±12.5% Y5V: within ±30% (This capacitance change means the change of capacitance under specified flexure of substrate from the capacitance measured before the test.)</li> </ul>															
11.	Resistance to Soldering Heat	<ul style="list-style-type: none"> <li>* Solder temperature: 260±5°C</li> <li>* Dipping time: 10±1 sec</li> <li>* Preheating: 120 to 150°C for 1 minute before immerse the capacitor in a eutectic solder.</li> <li>* Before initial measurement (Class II only): Perform 150+0/-10°C for 1 hr and then set for 48±4 hrs at room temp.</li> <li>* Measurement to be made after keeping at room temp. for 24±2 hrs. (Class I) or 48±4 hrs. (Class II).</li> </ul>	<ul style="list-style-type: none"> <li>* No remarkable damage.</li> <li>* Cap change: NP0: within ±2.5% or 0.25pF whichever is larger X7R, X5R: within ±7.5% Y5V: within ±20%</li> <li>* Q/D.F., I.R. and dielectric strength: To meet initial requirements.</li> <li>* 25% max. leaching on each edge.</li> </ul>															
12.	Temperature Cycle	<ul style="list-style-type: none"> <li>* Conduct the five cycles according to the temperatures and time.</li> </ul> <table border="1" style="margin-left: 20px;"> <thead> <tr> <th>Step</th> <th>Temp. (°C)</th> <th>Time (min.)</th> </tr> </thead> <tbody> <tr> <td>1</td> <td>Min. operating temp. +0/-3</td> <td>30±3</td> </tr> <tr> <td>2</td> <td>Room temp.</td> <td>2~3</td> </tr> <tr> <td>3</td> <td>Max. operating temp. +3/-0</td> <td>30±3</td> </tr> <tr> <td>4</td> <td>Room temp.</td> <td>2~3</td> </tr> </tbody> </table> <ul style="list-style-type: none"> <li>* Before initial measurement (Class II only): Perform 150+0/-10°C for 1 hr and then set for 48±4 hrs at room temp.</li> <li>* Measurement to be made after keeping at room temp. for 24±2 hrs. (Class I) or 48±4 hrs. (Class II).</li> </ul>	Step	Temp. (°C)	Time (min.)	1	Min. operating temp. +0/-3	30±3	2	Room temp.	2~3	3	Max. operating temp. +3/-0	30±3	4	Room temp.	2~3	<ul style="list-style-type: none"> <li>* No remarkable damage.</li> <li>* Cap change : NP0: within ±2.5% or 0.25pF whichever is larger X7R, X5R: within ±7.5% Y5V: within ±20%</li> <li>* Q/D.F., I.R. and dielectric strength: To meet initial requirements.</li> </ul>
Step	Temp. (°C)	Time (min.)																
1	Min. operating temp. +0/-3	30±3																
2	Room temp.	2~3																
3	Max. operating temp. +3/-0	30±3																
4	Room temp.	2~3																



No.	Item	Test Condition	Requirements																																																																											
13.	Humidity (Damp Heat) Steady State	* Test temp.: 40±2°C * Humidity: 90~95% RH * Test time: 500+24/-0hrs. * Measurement to be made after keeping at room temp. for 24±2 hrs. (Class I) or 48±4 hrs. (Class II).	* No remarkable damage. * Cap change: NP0: within ±5% or 0.5pF whichever is larger X7R, X5R: ≥10V, within ±12.5%; 6.3V, within ±25% Y5V: ≥10V, within ±30%; 6.3V, within +30/-40% * Q/D.F. value: NP0: More than 30pF Q≥350, 10pF≤C≤30pF, Q≥275+2.5C Less than 10pF Q≥200+10C X7R, X5R: <table border="1"> <thead> <tr> <th>Rated vol.</th> <th>D.F.≤</th> <th colspan="2">Exception of D.F.≤</th> </tr> </thead> <tbody> <tr> <td rowspan="2">≥ 50V</td> <td rowspan="2">3%</td> <td>6%</td> <td>0603≥ 0.047μF; 0805≥ 0.18μF; 1206≥ 0.47μF</td> </tr> <tr> <td>10%</td> <td>0805≥ 1μF; 1210≥ 10μF</td> </tr> <tr> <td rowspan="2">25V</td> <td rowspan="2">5%</td> <td>14%</td> <td>0603≥ 0.33μF; 1206≥ 4.7μF</td> </tr> <tr> <td>15%</td> <td>0402≥ 0.10μF; 0603≥ 0.47μF; 0805≥ 2.2μF; 1206≥ 6.8μF</td> </tr> <tr> <td rowspan="2">16V</td> <td rowspan="2">5%</td> <td>10%</td> <td>0603≥ 0.15μF; 0805≥ 0.68μF; 1206≥ 2.2μF; 1210≥ 4.7μF</td> </tr> <tr> <td>15%</td> <td>0402≥ 0.033μF; 0603≥ 0.68μF; 0805≥ 2.2μF 1206≥ 4.7μF; 1210≥ 22μF</td> </tr> <tr> <td rowspan="2">10V</td> <td rowspan="2">7.5%</td> <td>15%</td> <td>0402≥ 0.33μF; 0603≥ 0.33μF; 0805≥ 2.2μF 1206≥ 2.2μF; 1210≥ 22μF</td> </tr> <tr> <td>20%</td> <td>0201≥ 0.1μF ;0402≥ 1μF</td> </tr> <tr> <td>6.3V</td> <td>15%</td> <td>30%</td> <td>0402≥ 2.2μF ;0603≥ 10μF; 0805≥ 4.7μF; 1206≥ 47μF; 1210≥ 100μF</td> </tr> </tbody> </table> Y5V: <table border="1"> <thead> <tr> <th>Rated vol.</th> <th>D.F.≤</th> <th colspan="2">Exception of D.F.≤</th> </tr> </thead> <tbody> <tr> <td>≥ 50V</td> <td>7.5%</td> <td>10%</td> <td>0603≥ 0.1μF; 0805≥ 0.47μF; 1206≥ 4.7μF</td> </tr> <tr> <td>35V</td> <td>10%</td> <td>---</td> <td>---</td> </tr> <tr> <td rowspan="2">25V</td> <td rowspan="2">7.5%</td> <td>10%</td> <td>0402≥ 0.047μF; 0603≥ 0.1μF; 0805≥ 0.33μF; 1206≥ 1μF; 1210≥ 4.7μF</td> </tr> <tr> <td>15%</td> <td>0402≥ 0.068μF; 0603≥ 0.47μF; 1206≥ 4.7μF; 1210≥ 22μF</td> </tr> <tr> <td rowspan="2">16V (C&lt;1.0μF)</td> <td rowspan="2">10%</td> <td>12.5%</td> <td>0402≥ 0.068μF; 0603≥ 0.68μF</td> </tr> <tr> <td>20%</td> <td>0402≥ 0.22μF</td> </tr> <tr> <td>16V (C≥ 1.0μF)</td> <td>12.5%</td> <td>20%</td> <td>0603≥ 2.2μF; 0805≥ 3.3μF; 1206≥ 10μF; 1210≥ 22μF; 1812≥ 47μF;</td> </tr> <tr> <td>10V</td> <td>20%</td> <td>30%</td> <td>0402≥ 0.47μF</td> </tr> <tr> <td>6.3V</td> <td>30%</td> <td>---</td> <td>---</td> </tr> </tbody> </table> *I.R.: ≥10V, 1GΩ or 50 Ω-F whichever is smaller. Class II (X7R, X5R, Y5V) <table border="1"> <thead> <tr> <th>Rated voltage</th> <th>Insulation Resistance</th> </tr> </thead> <tbody> <tr> <td>100V: X7R</td> <td rowspan="4">1GΩ or RxC≥ 10 Ω-F whichever is smaller.</td> </tr> <tr> <td>16V:0402≥0.22μF</td> </tr> <tr> <td>10V:0201≥47nF;0402≥0.47μF;0603≥0.47μF ; 0805≥2.2μF;1206≥4.7μF;1210≥47μF</td> </tr> <tr> <td>6.3V</td> </tr> </tbody> </table>	Rated vol.	D.F.≤	Exception of D.F.≤		≥ 50V	3%	6%	0603≥ 0.047μF; 0805≥ 0.18μF; 1206≥ 0.47μF	10%	0805≥ 1μF; 1210≥ 10μF	25V	5%	14%	0603≥ 0.33μF; 1206≥ 4.7μF	15%	0402≥ 0.10μF; 0603≥ 0.47μF; 0805≥ 2.2μF; 1206≥ 6.8μF	16V	5%	10%	0603≥ 0.15μF; 0805≥ 0.68μF; 1206≥ 2.2μF; 1210≥ 4.7μF	15%	0402≥ 0.033μF; 0603≥ 0.68μF; 0805≥ 2.2μF 1206≥ 4.7μF; 1210≥ 22μF	10V	7.5%	15%	0402≥ 0.33μF; 0603≥ 0.33μF; 0805≥ 2.2μF 1206≥ 2.2μF; 1210≥ 22μF	20%	0201≥ 0.1μF ;0402≥ 1μF	6.3V	15%	30%	0402≥ 2.2μF ;0603≥ 10μF; 0805≥ 4.7μF; 1206≥ 47μF; 1210≥ 100μF	Rated vol.	D.F.≤	Exception of D.F.≤		≥ 50V	7.5%	10%	0603≥ 0.1μF; 0805≥ 0.47μF; 1206≥ 4.7μF	35V	10%	---	---	25V	7.5%	10%	0402≥ 0.047μF; 0603≥ 0.1μF; 0805≥ 0.33μF; 1206≥ 1μF; 1210≥ 4.7μF	15%	0402≥ 0.068μF; 0603≥ 0.47μF; 1206≥ 4.7μF; 1210≥ 22μF	16V (C<1.0μF)	10%	12.5%	0402≥ 0.068μF; 0603≥ 0.68μF	20%	0402≥ 0.22μF	16V (C≥ 1.0μF)	12.5%	20%	0603≥ 2.2μF; 0805≥ 3.3μF; 1206≥ 10μF; 1210≥ 22μF; 1812≥ 47μF;	10V	20%	30%	0402≥ 0.47μF	6.3V	30%	---	---	Rated voltage	Insulation Resistance	100V: X7R	1GΩ or RxC≥ 10 Ω-F whichever is smaller.	16V:0402≥0.22μF	10V:0201≥47nF;0402≥0.47μF;0603≥0.47μF ; 0805≥2.2μF;1206≥4.7μF;1210≥47μF	6.3V
Rated vol.	D.F.≤	Exception of D.F.≤																																																																												
≥ 50V	3%	6%	0603≥ 0.047μF; 0805≥ 0.18μF; 1206≥ 0.47μF																																																																											
		10%	0805≥ 1μF; 1210≥ 10μF																																																																											
25V	5%	14%	0603≥ 0.33μF; 1206≥ 4.7μF																																																																											
		15%	0402≥ 0.10μF; 0603≥ 0.47μF; 0805≥ 2.2μF; 1206≥ 6.8μF																																																																											
16V	5%	10%	0603≥ 0.15μF; 0805≥ 0.68μF; 1206≥ 2.2μF; 1210≥ 4.7μF																																																																											
		15%	0402≥ 0.033μF; 0603≥ 0.68μF; 0805≥ 2.2μF 1206≥ 4.7μF; 1210≥ 22μF																																																																											
10V	7.5%	15%	0402≥ 0.33μF; 0603≥ 0.33μF; 0805≥ 2.2μF 1206≥ 2.2μF; 1210≥ 22μF																																																																											
		20%	0201≥ 0.1μF ;0402≥ 1μF																																																																											
6.3V	15%	30%	0402≥ 2.2μF ;0603≥ 10μF; 0805≥ 4.7μF; 1206≥ 47μF; 1210≥ 100μF																																																																											
Rated vol.	D.F.≤	Exception of D.F.≤																																																																												
≥ 50V	7.5%	10%	0603≥ 0.1μF; 0805≥ 0.47μF; 1206≥ 4.7μF																																																																											
35V	10%	---	---																																																																											
25V	7.5%	10%	0402≥ 0.047μF; 0603≥ 0.1μF; 0805≥ 0.33μF; 1206≥ 1μF; 1210≥ 4.7μF																																																																											
		15%	0402≥ 0.068μF; 0603≥ 0.47μF; 1206≥ 4.7μF; 1210≥ 22μF																																																																											
16V (C<1.0μF)	10%	12.5%	0402≥ 0.068μF; 0603≥ 0.68μF																																																																											
		20%	0402≥ 0.22μF																																																																											
16V (C≥ 1.0μF)	12.5%	20%	0603≥ 2.2μF; 0805≥ 3.3μF; 1206≥ 10μF; 1210≥ 22μF; 1812≥ 47μF;																																																																											
10V	20%	30%	0402≥ 0.47μF																																																																											
6.3V	30%	---	---																																																																											
Rated voltage	Insulation Resistance																																																																													
100V: X7R	1GΩ or RxC≥ 10 Ω-F whichever is smaller.																																																																													
16V:0402≥0.22μF																																																																														
10V:0201≥47nF;0402≥0.47μF;0603≥0.47μF ; 0805≥2.2μF;1206≥4.7μF;1210≥47μF																																																																														
6.3V																																																																														

No	Item	Test Condition	Requirements																																																							
14	Humidity (Damp Heat) Load	* Test temp.: 40±2°C * Humidity: 90~95%RH * Test time: 500+24/-0 hrs. * To apply voltage : rated voltage. * Measurement to be made after keeping at room temp. for 24±2 hrs. (Class I) or 48±4 hrs. (Class II).	* No remarkable damage. Cap change: NP0: ±7.5% or 0.75pF whichever is larger. X7R, X5R: ≥10V, within ±12.5%; 6.3V, within ±25% Y5V: ≥10V, within ±30%; 6.3V, within +30/-40% Q/D.F. value: NP0: C≥30pF, Q≥200; C<30pF, Q≥100+10/3C X7R, X5R: <table border="1"> <thead> <tr> <th>Rated vol.</th> <th>D.F.≤</th> <th>Exception of D.F.≤</th> </tr> </thead> <tbody> <tr> <td>≥ 50V</td> <td>3%</td> <td>6% 0603≥ 0.047μF; 0805≥ 0.18μF; 1206≥ 0.47μF</td> </tr> <tr> <td rowspan="3">25V</td> <td rowspan="3">5%</td> <td>10% 0805≥ 1μF; 1210≥ 10μF</td> </tr> <tr> <td>14% 0603≥ 0.33μF; 1206≥ 4.7μF</td> </tr> <tr> <td>15% 0402≥ 0.10μF; 0603≥ 0.47μF; 0805≥ 2.2μF; 1206≥ 6.8μF</td> </tr> <tr> <td rowspan="2">16V</td> <td rowspan="2">5%</td> <td>10% 0603≥ 0.15μF; 0805≥ 0.68μF; 1206≥ 2.2μF; 1210≥ 4.7μF</td> </tr> <tr> <td>15% 0402≥ 0.033μF; 0603≥ 0.68μF; 0805≥ 2.2μF; 1206≥ 4.7μF; 1210≥ 22μF</td> </tr> <tr> <td rowspan="2">10V</td> <td rowspan="2">7.5%</td> <td>15% 0402≥ 0.33μF; 0603≥ 0.33μF; 0805≥ 2.2μF; 1206≥ 2.2μF; 1210≥ 22μF</td> </tr> <tr> <td>20% 0201≥ 0.1μF ;0402≥ 1μF</td> </tr> <tr> <td>6.3V</td> <td>15%</td> <td>30% 0402≥ 2.2μF ;0603≥ 10μF; 0805≥ 4.7μF; 1206≥ 47μF; 1210≥ 100μF</td> </tr> </tbody> </table> Y5V: <table border="1"> <thead> <tr> <th>Rated vol.</th> <th>D.F.≤</th> <th>Exception of D.F.≤</th> </tr> </thead> <tbody> <tr> <td>≥ 50V</td> <td>7.5%</td> <td>10% 0603≥ 0.1μF; 0805≥ 0.47μF; 1206≥ 4.7μF</td> </tr> <tr> <td>35V</td> <td>10%</td> <td>---</td> </tr> <tr> <td rowspan="2">25V</td> <td rowspan="2">7.5%</td> <td>10% 0402≥ 0.047μF; 0603≥ 0.1μF; 0805≥ 0.33μF; 1206≥ 1μF; 1210≥ 4.7μF</td> </tr> <tr> <td>15% 0402≥ 0.068μF; 0603≥ 0.47μF; 1206≥ 4.7μF; 1210≥ 22μF</td> </tr> <tr> <td rowspan="2">16V (C&lt;1.0μF)</td> <td rowspan="2">10%</td> <td>12.5% 0402≥ 0.068μF; 0603≥ 0.68μF</td> </tr> <tr> <td>20% 0402≥ 0.22μF</td> </tr> <tr> <td>16V (C≥ 1.0μF)</td> <td>12.5%</td> <td>20% 0603≥ 2.2μF; 0805≥ 3.3μF; 1206≥ 10μF; 1210≥ 22μF; 1812≥ 47μF;</td> </tr> <tr> <td>10V</td> <td>20%</td> <td>30% 0402≥ 0.47μF</td> </tr> <tr> <td>6.3V</td> <td>30%</td> <td>---</td> </tr> </tbody> </table> *I.R.: ≥10V, 500MΩ or 25 Ω-F whichever is smaller. Class II (X7R, X5R, Y5V) <table border="1"> <thead> <tr> <th>Rated voltage</th> <th>Insulation Resistance</th> </tr> </thead> <tbody> <tr> <td>100V: X7R</td> <td rowspan="4">500MΩ or RxC≥ 5 Ω-F whichever is smaller.</td> </tr> <tr> <td>16V: 0402≥0.22μF</td> </tr> <tr> <td>10V: 0201≥47nF; 0402≥0.47μF; 0603≥0.47μF ; 0805≥2.2μF; 1206≥4.7μF; 1210≥47μF</td> </tr> <tr> <td>6.3V</td> </tr> </tbody> </table>	Rated vol.	D.F.≤	Exception of D.F.≤	≥ 50V	3%	6% 0603≥ 0.047μF; 0805≥ 0.18μF; 1206≥ 0.47μF	25V	5%	10% 0805≥ 1μF; 1210≥ 10μF	14% 0603≥ 0.33μF; 1206≥ 4.7μF	15% 0402≥ 0.10μF; 0603≥ 0.47μF; 0805≥ 2.2μF; 1206≥ 6.8μF	16V	5%	10% 0603≥ 0.15μF; 0805≥ 0.68μF; 1206≥ 2.2μF; 1210≥ 4.7μF	15% 0402≥ 0.033μF; 0603≥ 0.68μF; 0805≥ 2.2μF; 1206≥ 4.7μF; 1210≥ 22μF	10V	7.5%	15% 0402≥ 0.33μF; 0603≥ 0.33μF; 0805≥ 2.2μF; 1206≥ 2.2μF; 1210≥ 22μF	20% 0201≥ 0.1μF ;0402≥ 1μF	6.3V	15%	30% 0402≥ 2.2μF ;0603≥ 10μF; 0805≥ 4.7μF; 1206≥ 47μF; 1210≥ 100μF	Rated vol.	D.F.≤	Exception of D.F.≤	≥ 50V	7.5%	10% 0603≥ 0.1μF; 0805≥ 0.47μF; 1206≥ 4.7μF	35V	10%	---	25V	7.5%	10% 0402≥ 0.047μF; 0603≥ 0.1μF; 0805≥ 0.33μF; 1206≥ 1μF; 1210≥ 4.7μF	15% 0402≥ 0.068μF; 0603≥ 0.47μF; 1206≥ 4.7μF; 1210≥ 22μF	16V (C<1.0μF)	10%	12.5% 0402≥ 0.068μF; 0603≥ 0.68μF	20% 0402≥ 0.22μF	16V (C≥ 1.0μF)	12.5%	20% 0603≥ 2.2μF; 0805≥ 3.3μF; 1206≥ 10μF; 1210≥ 22μF; 1812≥ 47μF;	10V	20%	30% 0402≥ 0.47μF	6.3V	30%	---	Rated voltage	Insulation Resistance	100V: X7R	500MΩ or RxC≥ 5 Ω-F whichever is smaller.	16V: 0402≥0.22μF	10V: 0201≥47nF; 0402≥0.47μF; 0603≥0.47μF ; 0805≥2.2μF; 1206≥4.7μF; 1210≥47μF	6.3V
Rated vol.	D.F.≤	Exception of D.F.≤																																																								
≥ 50V	3%	6% 0603≥ 0.047μF; 0805≥ 0.18μF; 1206≥ 0.47μF																																																								
25V	5%	10% 0805≥ 1μF; 1210≥ 10μF																																																								
		14% 0603≥ 0.33μF; 1206≥ 4.7μF																																																								
		15% 0402≥ 0.10μF; 0603≥ 0.47μF; 0805≥ 2.2μF; 1206≥ 6.8μF																																																								
16V	5%	10% 0603≥ 0.15μF; 0805≥ 0.68μF; 1206≥ 2.2μF; 1210≥ 4.7μF																																																								
		15% 0402≥ 0.033μF; 0603≥ 0.68μF; 0805≥ 2.2μF; 1206≥ 4.7μF; 1210≥ 22μF																																																								
10V	7.5%	15% 0402≥ 0.33μF; 0603≥ 0.33μF; 0805≥ 2.2μF; 1206≥ 2.2μF; 1210≥ 22μF																																																								
		20% 0201≥ 0.1μF ;0402≥ 1μF																																																								
6.3V	15%	30% 0402≥ 2.2μF ;0603≥ 10μF; 0805≥ 4.7μF; 1206≥ 47μF; 1210≥ 100μF																																																								
Rated vol.	D.F.≤	Exception of D.F.≤																																																								
≥ 50V	7.5%	10% 0603≥ 0.1μF; 0805≥ 0.47μF; 1206≥ 4.7μF																																																								
35V	10%	---																																																								
25V	7.5%	10% 0402≥ 0.047μF; 0603≥ 0.1μF; 0805≥ 0.33μF; 1206≥ 1μF; 1210≥ 4.7μF																																																								
		15% 0402≥ 0.068μF; 0603≥ 0.47μF; 1206≥ 4.7μF; 1210≥ 22μF																																																								
16V (C<1.0μF)	10%	12.5% 0402≥ 0.068μF; 0603≥ 0.68μF																																																								
		20% 0402≥ 0.22μF																																																								
16V (C≥ 1.0μF)	12.5%	20% 0603≥ 2.2μF; 0805≥ 3.3μF; 1206≥ 10μF; 1210≥ 22μF; 1812≥ 47μF;																																																								
10V	20%	30% 0402≥ 0.47μF																																																								
6.3V	30%	---																																																								
Rated voltage	Insulation Resistance																																																									
100V: X7R	500MΩ or RxC≥ 5 Ω-F whichever is smaller.																																																									
16V: 0402≥0.22μF																																																										
10V: 0201≥47nF; 0402≥0.47μF; 0603≥0.47μF ; 0805≥2.2μF; 1206≥4.7μF; 1210≥47μF																																																										
6.3V																																																										

No	Item	Test Condition	Requirements																																																																																																																																					
15.	High Temperature Load (Endurance)	<p>Test temp. : NP0, X7R/X7E: 125±3°C X5R, Y5V: 85±3°C Test time: 1000+24/-0 hrs. To apply voltage: (1) 6.3V or C ≥ 10µF or TT series: 150% of rated voltage. (2) 10V ≤ Ur &lt; 500V: 200% of rated voltage. (3) 500V: 150% of rated voltage. (4) Ur ≥ 630V: 120% of rated voltage. (5) 100% of rated voltage for below range.</p> <table border="1"> <thead> <tr> <th>Size</th> <th>Dielectric</th> <th>Rated voltage</th> <th>Capacitance range</th> </tr> </thead> <tbody> <tr> <td>0201</td> <td>X5R</td> <td>6.3V, 10V</td> <td>C ≥ 0.1µF</td> </tr> <tr> <td>0402</td> <td>X5R, Y5V</td> <td>6.3V, 10V</td> <td>C ≥ 1.0µF</td> </tr> <tr> <td rowspan="2">0603</td> <td>X5R</td> <td rowspan="2">6.3V, 10V</td> <td>C ≥ 4.7µF</td> </tr> <tr> <td>Y5V</td> <td>TT ≥ 2.2µF</td> </tr> <tr> <td rowspan="2">0805</td> <td>X5R</td> <td rowspan="2">6.3V</td> <td>C ≥ 22µF</td> </tr> <tr> <td>Y5V</td> <td>TT ≥ 10µF</td> </tr> <tr> <td rowspan="2">1206</td> <td>X5R</td> <td rowspan="2">6.3V</td> <td>C ≥ 47µF</td> </tr> <tr> <td>Y5V</td> <td>TT ≥ 22µF</td> </tr> </tbody> </table> <p>(6) 150% of rated voltage for below range.</p> <table border="1"> <thead> <tr> <th>Size</th> <th>Dielectric</th> <th>Rated voltage</th> <th>Capacitance range</th> </tr> </thead> <tbody> <tr> <td rowspan="2">0402</td> <td>X5R</td> <td>10V, 16V</td> <td>C ≥ 0.22µF</td> </tr> <tr> <td>Y5V</td> <td>16V</td> <td>C ≥ 0.47µF</td> </tr> <tr> <td rowspan="2">0603</td> <td>X5R</td> <td>10V, 16V</td> <td>C ≥ 1.0µF</td> </tr> <tr> <td>Y5V</td> <td>16V</td> <td>C ≥ 2.2µF</td> </tr> <tr> <td rowspan="2">0805</td> <td>X5R</td> <td>10V</td> <td>C ≥ 4.7µF</td> </tr> <tr> <td>Y5V</td> <td>16V</td> <td>C ≥ 4.7µF</td> </tr> </tbody> </table> <p>* Measurement to be made after keeping at room temp. for 24±2 hrs. (Class I) or 48±4 hrs. (Class II).</p>	Size	Dielectric	Rated voltage	Capacitance range	0201	X5R	6.3V, 10V	C ≥ 0.1µF	0402	X5R, Y5V	6.3V, 10V	C ≥ 1.0µF	0603	X5R	6.3V, 10V	C ≥ 4.7µF	Y5V	TT ≥ 2.2µF	0805	X5R	6.3V	C ≥ 22µF	Y5V	TT ≥ 10µF	1206	X5R	6.3V	C ≥ 47µF	Y5V	TT ≥ 22µF	Size	Dielectric	Rated voltage	Capacitance range	0402	X5R	10V, 16V	C ≥ 0.22µF	Y5V	16V	C ≥ 0.47µF	0603	X5R	10V, 16V	C ≥ 1.0µF	Y5V	16V	C ≥ 2.2µF	0805	X5R	10V	C ≥ 4.7µF	Y5V	16V	C ≥ 4.7µF	<p>* No remarkable damage. Cap change: NP0: ±3.0% or ±0.3pF whichever is larger X7R, X5R: ≥10V, within ±12.5%; 6.3V, within ±25% Y5V: ≥10V, within ±30%; 6.3V, within ±30/-40% Q/D.F. value: NP0: More than 30pF, Q ≥ 350 10pF ≤ C &lt; 30pF, Q ≥ 275+2.5C Less than 10pF, Q ≥ 200+10C X7R, X5R:</p> <table border="1"> <thead> <tr> <th>Rated vol.</th> <th>D.F. ≤</th> <th colspan="2">Exception of D.F. ≤</th> </tr> </thead> <tbody> <tr> <td rowspan="2">≥ 50V</td> <td rowspan="2">3%</td> <td>6%</td> <td>0603 ≥ 0.047µF; 0805 ≥ 0.18µF; 1206 ≥ 0.47µF</td> </tr> <tr> <td>10%</td> <td>0805 ≥ 1µF; 1210 ≥ 10µF</td> </tr> <tr> <td rowspan="3">25V</td> <td rowspan="3">5%</td> <td>14%</td> <td>0603 ≥ 0.33µF; 1206 ≥ 4.7µF</td> </tr> <tr> <td>15%</td> <td>0402 ≥ 0.10µF; 0603 ≥ 0.47µF; 0805 ≥ 2.2µF; 1206 ≥ 6.8µF</td> </tr> <tr> <td>10%</td> <td>0603 ≥ 0.15µF; 0805 ≥ 0.68µF; 1206 ≥ 2.2µF; 1210 ≥ 4.7µF</td> </tr> <tr> <td rowspan="2">16V</td> <td rowspan="2">5%</td> <td>15%</td> <td>0402 ≥ 0.033µF; 0603 ≥ 0.68µF; 0805 ≥ 2.2µF; 1206 ≥ 4.7µF; 1210 ≥ 22µF</td> </tr> <tr> <td>10%</td> <td>0603 ≥ 0.15µF; 0805 ≥ 0.68µF; 1206 ≥ 2.2µF; 1210 ≥ 4.7µF</td> </tr> <tr> <td rowspan="2">10V</td> <td rowspan="2">7.5%</td> <td>15%</td> <td>0402 ≥ 0.33µF; 0603 ≥ 0.33µF; 0805 ≥ 2.2µF; 1206 ≥ 2.2µF; 1210 ≥ 22µF</td> </tr> <tr> <td>20%</td> <td>0201 ≥ 0.1µF; 0402 ≥ 1µF</td> </tr> <tr> <td>6.3V</td> <td>15%</td> <td>30%</td> <td>0402 ≥ 2.2µF; 0603 ≥ 10µF; 0805 ≥ 4.7µF; 1206 ≥ 47µF; 1210 ≥ 100µF</td> </tr> </tbody> </table> <p>Y5V:</p> <table border="1"> <thead> <tr> <th>Rated vol.</th> <th>D.F. ≤</th> <th colspan="2">Exception of D.F. ≤</th> </tr> </thead> <tbody> <tr> <td>≥ 50V</td> <td rowspan="2">7.5%</td> <td>10%</td> <td>0603 ≥ 0.1µF; 0805 ≥ 0.47µF; 1206 ≥ 4.7µF</td> </tr> <tr> <td>35V</td> <td>---</td> <td>---</td> </tr> <tr> <td rowspan="2">25V</td> <td rowspan="2">7.5%</td> <td>10%</td> <td>0402 ≥ 0.047µF; 0603 ≥ 0.1µF; 0805 ≥ 0.33µF; 1206 ≥ 1µF; 1210 ≥ 4.7µF</td> </tr> <tr> <td>15%</td> <td>0402 ≥ 0.068µF; 0603 ≥ 0.47µF; 1206 ≥ 4.7µF; 1210 ≥ 22µF</td> </tr> <tr> <td rowspan="2">16V (C &lt; 1.0µF)</td> <td rowspan="2">10%</td> <td>12.5%</td> <td>0402 ≥ 0.068µF; 0603 ≥ 0.68µF</td> </tr> <tr> <td>20%</td> <td>0402 ≥ 0.22µF</td> </tr> <tr> <td rowspan="2">16V (C ≥ 1.0µF)</td> <td rowspan="2">12.5%</td> <td>20%</td> <td>0603 ≥ 2.2µF; 0805 ≥ 3.3µF; 1206 ≥ 10µF; 1210 ≥ 22µF; 1812 ≥ 47µF;</td> </tr> <tr> <td>30%</td> <td>0402 ≥ 0.47µF</td> </tr> <tr> <td>10V</td> <td>20%</td> <td>30%</td> <td>---</td> </tr> <tr> <td>6.3V</td> <td>30%</td> <td>---</td> <td>---</td> </tr> </tbody> </table> <p>*I.R.: ≥10V, 1GΩ or 50 Ω-F whichever is smaller. Class II (X7R, X5R, Y5V)</p> <table border="1"> <thead> <tr> <th>Rated voltage</th> <th>Insulation Resistance</th> </tr> </thead> <tbody> <tr> <td>100V: X7R</td> <td rowspan="4">1GΩ or Rx C ≥ 10 Ω-F whichever is smaller.</td> </tr> <tr> <td>16V: 0402 ≥ 0.22µF</td> </tr> <tr> <td>10V: 0201 ≥ 47nF; 0402 ≥ 0.47µF; 0603 ≥ 0.47µF; 0805 ≥ 2.2µF; 1206 ≥ 4.7µF; 1210 ≥ 47µF</td> </tr> <tr> <td>6.3V</td> </tr> </tbody> </table>	Rated vol.	D.F. ≤	Exception of D.F. ≤		≥ 50V	3%	6%	0603 ≥ 0.047µF; 0805 ≥ 0.18µF; 1206 ≥ 0.47µF	10%	0805 ≥ 1µF; 1210 ≥ 10µF	25V	5%	14%	0603 ≥ 0.33µF; 1206 ≥ 4.7µF	15%	0402 ≥ 0.10µF; 0603 ≥ 0.47µF; 0805 ≥ 2.2µF; 1206 ≥ 6.8µF	10%	0603 ≥ 0.15µF; 0805 ≥ 0.68µF; 1206 ≥ 2.2µF; 1210 ≥ 4.7µF	16V	5%	15%	0402 ≥ 0.033µF; 0603 ≥ 0.68µF; 0805 ≥ 2.2µF; 1206 ≥ 4.7µF; 1210 ≥ 22µF	10%	0603 ≥ 0.15µF; 0805 ≥ 0.68µF; 1206 ≥ 2.2µF; 1210 ≥ 4.7µF	10V	7.5%	15%	0402 ≥ 0.33µF; 0603 ≥ 0.33µF; 0805 ≥ 2.2µF; 1206 ≥ 2.2µF; 1210 ≥ 22µF	20%	0201 ≥ 0.1µF; 0402 ≥ 1µF	6.3V	15%	30%	0402 ≥ 2.2µF; 0603 ≥ 10µF; 0805 ≥ 4.7µF; 1206 ≥ 47µF; 1210 ≥ 100µF	Rated vol.	D.F. ≤	Exception of D.F. ≤		≥ 50V	7.5%	10%	0603 ≥ 0.1µF; 0805 ≥ 0.47µF; 1206 ≥ 4.7µF	35V	---	---	25V	7.5%	10%	0402 ≥ 0.047µF; 0603 ≥ 0.1µF; 0805 ≥ 0.33µF; 1206 ≥ 1µF; 1210 ≥ 4.7µF	15%	0402 ≥ 0.068µF; 0603 ≥ 0.47µF; 1206 ≥ 4.7µF; 1210 ≥ 22µF	16V (C < 1.0µF)	10%	12.5%	0402 ≥ 0.068µF; 0603 ≥ 0.68µF	20%	0402 ≥ 0.22µF	16V (C ≥ 1.0µF)	12.5%	20%	0603 ≥ 2.2µF; 0805 ≥ 3.3µF; 1206 ≥ 10µF; 1210 ≥ 22µF; 1812 ≥ 47µF;	30%	0402 ≥ 0.47µF	10V	20%	30%	---	6.3V	30%	---	---	Rated voltage	Insulation Resistance	100V: X7R	1GΩ or Rx C ≥ 10 Ω-F whichever is smaller.	16V: 0402 ≥ 0.22µF	10V: 0201 ≥ 47nF; 0402 ≥ 0.47µF; 0603 ≥ 0.47µF; 0805 ≥ 2.2µF; 1206 ≥ 4.7µF; 1210 ≥ 47µF	6.3V
Size	Dielectric	Rated voltage	Capacitance range																																																																																																																																					
0201	X5R	6.3V, 10V	C ≥ 0.1µF																																																																																																																																					
0402	X5R, Y5V	6.3V, 10V	C ≥ 1.0µF																																																																																																																																					
0603	X5R	6.3V, 10V	C ≥ 4.7µF																																																																																																																																					
	Y5V		TT ≥ 2.2µF																																																																																																																																					
0805	X5R	6.3V	C ≥ 22µF																																																																																																																																					
	Y5V		TT ≥ 10µF																																																																																																																																					
1206	X5R	6.3V	C ≥ 47µF																																																																																																																																					
	Y5V		TT ≥ 22µF																																																																																																																																					
Size	Dielectric	Rated voltage	Capacitance range																																																																																																																																					
0402	X5R	10V, 16V	C ≥ 0.22µF																																																																																																																																					
	Y5V	16V	C ≥ 0.47µF																																																																																																																																					
0603	X5R	10V, 16V	C ≥ 1.0µF																																																																																																																																					
	Y5V	16V	C ≥ 2.2µF																																																																																																																																					
0805	X5R	10V	C ≥ 4.7µF																																																																																																																																					
	Y5V	16V	C ≥ 4.7µF																																																																																																																																					
Rated vol.	D.F. ≤	Exception of D.F. ≤																																																																																																																																						
≥ 50V	3%	6%	0603 ≥ 0.047µF; 0805 ≥ 0.18µF; 1206 ≥ 0.47µF																																																																																																																																					
		10%	0805 ≥ 1µF; 1210 ≥ 10µF																																																																																																																																					
25V	5%	14%	0603 ≥ 0.33µF; 1206 ≥ 4.7µF																																																																																																																																					
		15%	0402 ≥ 0.10µF; 0603 ≥ 0.47µF; 0805 ≥ 2.2µF; 1206 ≥ 6.8µF																																																																																																																																					
		10%	0603 ≥ 0.15µF; 0805 ≥ 0.68µF; 1206 ≥ 2.2µF; 1210 ≥ 4.7µF																																																																																																																																					
16V	5%	15%	0402 ≥ 0.033µF; 0603 ≥ 0.68µF; 0805 ≥ 2.2µF; 1206 ≥ 4.7µF; 1210 ≥ 22µF																																																																																																																																					
		10%	0603 ≥ 0.15µF; 0805 ≥ 0.68µF; 1206 ≥ 2.2µF; 1210 ≥ 4.7µF																																																																																																																																					
10V	7.5%	15%	0402 ≥ 0.33µF; 0603 ≥ 0.33µF; 0805 ≥ 2.2µF; 1206 ≥ 2.2µF; 1210 ≥ 22µF																																																																																																																																					
		20%	0201 ≥ 0.1µF; 0402 ≥ 1µF																																																																																																																																					
6.3V	15%	30%	0402 ≥ 2.2µF; 0603 ≥ 10µF; 0805 ≥ 4.7µF; 1206 ≥ 47µF; 1210 ≥ 100µF																																																																																																																																					
Rated vol.	D.F. ≤	Exception of D.F. ≤																																																																																																																																						
≥ 50V	7.5%	10%	0603 ≥ 0.1µF; 0805 ≥ 0.47µF; 1206 ≥ 4.7µF																																																																																																																																					
35V		---	---																																																																																																																																					
25V	7.5%	10%	0402 ≥ 0.047µF; 0603 ≥ 0.1µF; 0805 ≥ 0.33µF; 1206 ≥ 1µF; 1210 ≥ 4.7µF																																																																																																																																					
		15%	0402 ≥ 0.068µF; 0603 ≥ 0.47µF; 1206 ≥ 4.7µF; 1210 ≥ 22µF																																																																																																																																					
16V (C < 1.0µF)	10%	12.5%	0402 ≥ 0.068µF; 0603 ≥ 0.68µF																																																																																																																																					
		20%	0402 ≥ 0.22µF																																																																																																																																					
16V (C ≥ 1.0µF)	12.5%	20%	0603 ≥ 2.2µF; 0805 ≥ 3.3µF; 1206 ≥ 10µF; 1210 ≥ 22µF; 1812 ≥ 47µF;																																																																																																																																					
		30%	0402 ≥ 0.47µF																																																																																																																																					
10V	20%	30%	---																																																																																																																																					
6.3V	30%	---	---																																																																																																																																					
Rated voltage	Insulation Resistance																																																																																																																																							
100V: X7R	1GΩ or Rx C ≥ 10 Ω-F whichever is smaller.																																																																																																																																							
16V: 0402 ≥ 0.22µF																																																																																																																																								
10V: 0201 ≥ 47nF; 0402 ≥ 0.47µF; 0603 ≥ 0.47µF; 0805 ≥ 2.2µF; 1206 ≥ 4.7µF; 1210 ≥ 47µF																																																																																																																																								
6.3V																																																																																																																																								

**APPENDIXES**

**▣ Tape & reel dimensions**




Fig. 6 The dimension of paper tape




Fig. 7 The dimension of plastic tape

Size	0402	0603	0805			1206			1210			1812	
Thickness	N	S, X	A	B	C, D, I	B	C, J, D	G, P	C, D	G, K	M	D, K	M
A <sub>0</sub>	0.62±0.05	1.02±0.05	1.50±0.10	1.50±0.10	<1.57	2.00±0.10	<1.85	<1.95	<2.97	<2.97	<2.97	<3.81	<3.81
B <sub>0</sub>	1.12±0.05	1.80±0.05	2.30±0.10	2.30±0.10	<2.40	3.50±0.10	<3.46	<3.67	<3.73	<3.73	<3.73	<5.30	<5.30
T	0.60±0.05	0.95±0.05	0.75±0.05	0.95±0.05	0.23±0.05	0.95±0.05	0.23±0.05	0.23±0.05	0.23±0.05	0.23±0.05	0.23±0.05	0.25±0.05	0.25±0.05
K <sub>0</sub>	-	-	-	-	<2.50	-	<2.50	<2.50	<2.50	<2.50	<3.00	<2.50	<3.00
W	8.00±0.10	8.00±0.10	8.00±0.10	8.00±0.10	8.00±0.10	8.00±0.10	8.00±0.10	8.00±0.10	8.00±0.10	8.00±0.10	8.00±0.10	12.0±0.20	12.0±0.20
P <sub>0</sub>	4.00±0.10	4.00±0.10	4.00±0.10	4.00±0.10	4.00±0.10	4.00±0.10	4.00±0.10	4.00±0.10	4.00±0.10	4.00±0.10	4.00±0.10	4.00±0.10	4.00±0.10
10xP <sub>0</sub>	40.0±0.10	40.0±0.10	40.0±0.10	40.0±0.10	40.0±0.10	40.0±0.10	40.0±0.10	40.0±0.10	40.0±0.10	40.0±0.10	40.0±0.10	40.0±0.10	40.0±0.10
P <sub>1</sub>	2.00±0.05	4.00±0.10	4.00±0.10	4.00±0.10	4.00±0.10	4.00±0.10	4.00±0.10	4.00±0.10	4.00±0.10	4.00±0.10	4.00±0.10	8.00±0.10	8.00±0.10
P <sub>2</sub>	2.00±0.05	2.00±0.05	2.00±0.05	2.00±0.05	2.00±0.05	2.00±0.05	2.00±0.05	2.00±0.05	2.00±0.05	2.00±0.05	2.00±0.05	2.00±0.05	2.00±0.05
D <sub>0</sub>	1.55±0.05	1.55±0.05	1.55±0.05	1.55±0.05	1.50±0.05	1.50±0.05	1.50±0.05	1.50±0.05	1.50±0.05	1.50±0.05	1.50±0.05	1.50±0.05	1.50±0.05
D <sub>1</sub>	-	-	-	-	1.00±0.10	-	1.00±0.10	1.00±0.10	1.00±0.10	1.00±0.10	1.00±0.10	1.50±0.10	1.50±0.10
E	1.75±0.05	1.75±0.05	1.75±0.05	1.75±0.05	1.75±0.10	1.75±0.10	1.75±0.10	1.75±0.10	1.75±0.10	1.75±0.10	1.75±0.10	1.75±0.10	1.75±0.10
F	3.50±0.05	3.50±0.05	3.50±0.05	3.50±0.05	3.50±0.05	3.50±0.05	3.50±0.05	3.50±0.05	3.50±0.05	3.50±0.05	3.50±0.05	5.50±0.05	5.50±0.05





Fig. 8 The dimension of reel

Size	0402, 0603, 0805, 1206, 1210			1812
Reel size	7"	10"	13"	7"
C	13.0+0.5/-0.2	13.0+0.5/-0.2	13.0+0.5/-0.2	13.0+0.5/-0.2
W <sub>1</sub>	8.4+1.5/-0	8.4+1.5/-0	8.4+1.5/-0	12.4+2.0/-0
A	178.0±0.10	250.0±1.0	330.0±1.0	178.0±0.10
N	60.0+1.0/-0	100.0±1.0	100±1.0	60.0+1.0/-0

▣ Description of customer label



- a. Customer name
- b. WTC order series and item number
- c. Customer P/O
- d. Customer P/N
- e. Description of product
- f. Quantity
- g. Bar code including quantity & WTC P/N or customer
- h. WTC P/N
- i. Shipping date
- j. Order bar code including series and item numbers
- k. Serial number of label

▣ Constructions

No.	Name	X7R, X5R, Y5V
①	Ceramic material	BaTiO <sub>3</sub> based
②	Inner electrode	Ni
③	Termination	Inner layer
④		Middle layer
⑤		Outer layer
		Sn (Matt)




Fig. 9 The construction of MLCC

▣ Storage and handling conditions

- (1) To store products at 5 to 40°C ambient temperature and 20 to 70% related humidity conditions.
- (2) The product is recommended to be used within one year after shipment. Check solderability in case of shelf life extension is needed.

Cautions:

- a. Don't store products in a corrosive environment such as sulfide, chloride gas, or acid. It may cause oxidization of electrode, which easily be resulted in poor soldering.
- b. To store products on the shelf and avoid exposure to moisture.
- c. Don't expose products to excessive shock, vibration, direct sunlight and so on.

☑ Recommended soldering conditions

The lead-free termination MLCCs are not only to be used on SMT against lead-free solder paste, but also suitable against lead-containing solder paste. If the optimized solder joint is requested, increasing soldering time, temperature and concentration of N<sub>2</sub> within oven are recommended.




Fig. 10 Recommended IR reflow soldering profile for SMT process with SnAgCu series solder paste.




Fig. 11 Recommended wave soldering profile for SMT process with SnAgCu series solder.