

















Rail Mounted Clips

Please note that these clips are intended solely for use with Aavid Thermalloy Max Clip Extrusion Profiles.


<p>Part Number: MAX01NG Low force clip</p> <p>RoHS  </p>	
<p>Force: 22 N [4.9 lbs]</p>	
<p>Width: 10 mm [0.39 in]</p>	
<p>Thickness: 0.5 mm [0.02 in]</p>	
<p>Part Number: MAX01-HNG High force clip</p> <p>RoHS  </p>	
<p>Force: 80 N [18.0 lbs]</p>	
<p>Width: 10 mm [0.39 in]</p>	
<p>Thickness: 0.7 mm [0.03 in]</p>	
<p>Part Number: MAX02NG Standard force clip</p> <p>RoHS  </p>	
<p>Force: 35 N [7.9 lbs]</p>	
<p>Width: 12 mm [0.47 in]</p>	
<p>Thickness: 0.5 mm [0.02 in]</p>	
<p>Part Number: MAX02-HNG High force clip</p> <p>RoHS  </p>	
<p>Force: 60 N [13.5 lbs]</p>	
<p>Width: 13 mm [0.51 in]</p>	
<p>Thickness: 0.6 mm [0.02 in]</p>	
<p>Part Number: MAX03NG Standard force clip</p> <p>RoHS  </p>	
<p>Force: 45 N [10.1 lbs]</p>	
<p>Width: 15 mm [0.59 in]</p>	
<p>Thickness: 0.5 mm [0.02 in]</p>	

Part Number: MAX03-HNG


High force clip

**Force:** 80 N [18.0 lbs]**Width:** 18 mm [0.71 in]**Thickness:** 0.6 mm [0.02 in]**Part Number: MAX04NG**


Standard force clip

**Force:** 60 N [13.5 lbs]**Width:** 20 mm [0.79 in]**Thickness:** 0.5 mm [0.02 in]**Part Number: MAX09NG**


Short standard force clip

**Force:** 45 N [10.1 lbs]**Width:** 10 mm [0.39 in]**Thickness:** 0.5 mm [0.02 in]**Part Number: MAX10NG**


Long standard force clip







**Force:** 40 N [9.0 lbs]**Width:** 12 mm [0.47 in]**Thickness:** 0.6 mm [0.02 in]**Part Number: MAX12NG**

Low force clip

**Force:** 25 N [5.6 lbs]**Width:** 6 mm [0.24 in]**Thickness:** 0.6 mm [0.02 in]**Part Number: MAX11NG**

Extra long standard force clip

**Force:** 40 N [9.0 lbs]**Width:** 12 mm [0.47 in]**Thickness:** 0.6 mm [0.02 in]

<p>Part Number: MAX23NG High force clip for use with thick insulator</p> <p style="text-align: right;">RoHS ✓ Compliant</p>	
<p>Force: 100 N [22.5 lbs]</p>	
<p>Width: 18 mm [0.71 in]</p>	
<p>Thickness: 0.6 mm [0.02 in]</p>	
<p>Part Number: MAX20NG Standard force clip for use with thick insulator</p> <p style="text-align: right;">RoHS ✓ Compliant</p>	
<p>Force: 47 N [10.6 lbs]</p>	
<p>Width: 12 mm [0.47 in]</p>	
<p>Thickness: 0.6 mm [0.02 in]</p>	
<p>Part Number: MAX13NG Standard force clip with locating features</p> <p style="text-align: right;">RoHS ✓ Compliant</p>	
<p>Force: 45 N [10.1 lbs]</p>	
<p>Width: 17 mm [0.67 in]</p>	
<p>Thickness: 0.5 mm [0.02 in]</p>	
<p>Part Number: MAX14NG Low force clip with locating features</p> <p style="text-align: right;">RoHS ✓ Compliant</p>	
<p>Force: 20 N [4.5 lbs]</p>	
<p>Width: 13 mm [0.51 in]</p>	
<p>Thickness: 0.5 mm [0.02 in]</p>	
<p>Part Number: MAX15NG Standard force clip with locating features</p> <p style="text-align: right;">RoHS ✓ Compliant</p>	
<p>Force: 60 N [13.5 lbs]</p>	
<p>Width: 18 mm [0.71 in]</p>	
<p>Thickness: 0.6 mm [0.02 in]</p>	
<p>Part Number: MAX16NG Standard force clip with locating features</p> <p style="text-align: right;">RoHS ✓ Compliant</p>	
<p>Force: 45 N [10.1 lbs]</p>	
<p>Width: 17 mm [0.67 in]</p>	
<p>Thickness: 0.5 mm [0.02 in]</p>	