

Coin Cell Capacitors


GREEN 70°C

- Reflow soldering method available.
- Unlike batteries, the number of charging / discharging cycles unlimited and rapid charging / discharging is possible.
- DSK OSK OSK OSK
- Unlike batteries, exceilent charge and discharge characteristics with no chemical reactions.
- φ4.8×1.71mm Max height type made lineup in the DSK series.


Specifications

Item	Performance							
Series Name	DSK series							
Max. operating voltage (V)	3.3							
Category temperature range (°C)	-10 to +70							
Tolerance at rated capacitance (%)	-20 to +80							
Rated Capacitance (F)	0.07							
Internal resistance (Ω) at 1 kHz	100							
Characteristics at high and low temperature	Percentage of capacitance change Internal resistance	Within ±50% of the value at 20°C Within ten times the initial specified value						
Endurance	Test temperature Test time	70°C 500 hours						
	Percentage of capacitance change	Within ±30% of the initial measured value						
	Internal resistance	5kΩ or less						
Shelf life	Test time: 500 hours; Same as endurance.							
Applicable standards	Conforms to JIS C5160-1 2009 (IEC 62391-1 2006)							

Outline Drawing



Recommended land pattern size Unit: mm



^{*}Please consult with us about other terminal form

Part numbering system (3.3V0.07F, terminal shaped : HL)								
DSK —	3R3	Н	703	T414	_	HL	L	
Series code	Max.operating voltage symbol		Rated capacitance symbol	Additional symbol		Terminal shaped	Taping	

Standard Ratings

Max. operating voltage (V)	Rated capacitance (F)	ELNA Parts No.	φD×L (mm)
3.3	0.07	DSK-3R3H703T414-HLL	4.8×1.4
3.3	0.07	DSK-3R3H703T414-HRL	4.0^1.4

^{*}Reflow soldering condition: 150 page.