

Terminal blocks

to **Type 017**

- ASP025** page 47
- Type 007** page 89
- Type 026** page 129
- Type 077** page 89
- Type 107** page 90

to **Type 027**

- Type 007** page 89
- Type 026** page 129
- Type 077** page 89
- Type 107** page 90
- Type 137** page 91

Note for Type 017 and Type 027

Packaging for automated processing is available on demand. Please do not hesitate to contact us.

Type 017


Header, centerline 5 mm / 0.197 inches, vertical mounting, designed for THR, optional Tape on Reel packaging for automated processing, round contact pins 1.3 mm / 0.051 inches

Technical Data

	V / A	300 / 15
	V / A	300 / 15
		250 V / 4 kV / 10 A

Insulation co-ordination according to EN 60664-1			
Clearance and creepage distances	min. 3.7 mm		
Insulating material class	CTI 400		
Overvoltage category	III	III	II
Pollution degree	3	2	2
Rated voltage	250	500	500
Rated test voltage	2.5	4	2.5
Protection category according to IEC 529	IP00		
Solder pin dimension	1 mm		
Recommended pc board hole dia.	Ø 1.3 mm		
Solder pin length	3.4 mm		
Pole size	2 - 24		
Color	black		

Dimensions in mm 1 mm = 0.0394 in.



$L = (\text{pole size} - 1) \times \text{centerline} + 4.8 \text{ mm} / 0.189 \text{ inches}$

Part numbers (P/N)

(information: page 110)

Complete the part number by adding the pole size.

Type 017

centerline 5 mm / 0.197 inches

P/N 310171

	02	03	04	05	06	07	08
	09	10	11	12	13	14	15
	17	18	19	20	21	22	23
	24						

Type 027


Header, centerline 5 mm / 0.197 inches, vertical mounting, designed for THR, optional Tape on Reel packaging for automated processing, round contact pins 1.3 mm / 0.051 inches

Technical Data

	V / A	300 / 15
	V / A	300 / 15
		250 V / 4 kV / 10 A

Insulation co-ordination according to EN 60664-1			
Clearance and creepage distances	min. 3.7 mm		
Insulating material class	CTI 400		
Overvoltage category	III	III	II
Pollution degree	3	2	2
Rated voltage	250	500	500
Rated test voltage	2.5	4	2.5
Protection category according to IEC 529	IP00		
Solder pin dimension	1 mm		
Recommended pc board hole dia.	Ø 1.3 mm		
Solder pin length	3.4 mm		
Pole size	2 - 24		
Color	black		

Dimensions in mm 1 mm = 0.0394 in.



$L = (\text{pole size} - 1) \times \text{centerline} + 4.8 \text{ mm} / 0.189 \text{ inches}$

Part numbers (P/N)

(information: page 110)

Complete the part number by adding the pole size.

Type 027

centerline 5 mm / 0.197 inches

P/N 310271

	02	03	04	05	06	07	08
	09	10	11	12	13	14	15
	17	18	19	20	21	22	23
	24						