




Features:

- Power supply with TopBoost, PowerBoost and configurable overload behavior
- Configurable digital signal input and output, optical status indication, function keys
- Communication interface for configuration and monitoring
- Optional connection to IO-Link, EtherNet/IP™, Modbus TCP or Modbus RTU
- Suitable for both parallel and series operation
- Natural convection cooling when horizontally mounted
- Pluggable connection technology
- Electrically isolated output voltage (SELV/PELV) per EN 61010-2-201/UL 61010-2-201
- Marker slot for WAGO marking cards (WMB) and WAGO marking strips

Technical data			
Input		Output	
Phases	1	Nominal output voltage U _{o nom}	DC 24 V (SELV)
Nominal input voltage U _{i nom}	1 x AC 100 ... 240 V	Output voltage range	DC 24 ... 28 V (adjustable)
Input voltage range	1 x AC 90 ... 264 V; DC 130 ... 240 V	Default setting	DC 24 V
Nominal mains frequency range	50 ... 60 Hz	Nominal output current I _{o nom}	20 A (24 VDC)
Input current I _i	≤ 2.2 A (240 VAC; nominal load); ≤ 5.9 A (100 VAC; nominal load)	Nominal output power	480 W
Inrush current	≤ 12 A (after 1 ms)	Deviation	≤ 1 %
Power factor	≥ 0.98 (240 VAC)	Residual ripple	≤ 70 mV (peak-to-peak)
Power factor correction (PFC)	active	Current limitation	1.1 x I _{o nom} (typ.)
Mains failure hold-up time	≥ 24 ms (230 VAC)	Overload behavior	TopBoost/PowerBoost/Time-limited constant current mode (other overload behaviors can be set)



Output	
PowerBoost	DC 30 A (5 s)
TopBoost	Up to 600 %

Signaling and communication	
Signaling	Optical status indication (DC OK; load; warning and error states) Digital signal input and output (DI/DO)
Communication	USB (750-923 Communication Cable) Ethernet/IP (2789-9023 Communication Module) IO-Link (2789-9080 Communication Module) Modbus RTU (Communication Module 2789-9015) Modbus TCP (2789-9052 Communication Module)

Efficiency/power losses	
Power loss P _I	≤ 1.3 W (standby); ≤ 2.6 W (No load); ≤ 24 W (230 VAC; nominal load)
Efficiency (typ.)	95.4 % (230 VAC; 20 A; 25 °C)

Circuit protection	
Internal fuse	T 10 A / 250 VAC
Backup fusing (required)	An external DC fuse is required for the DC input voltage.
Backup fusing (recommended)	16 A (for USA/Canada: 15 A)

Safety and protection	
Isolation voltage (pri.-sec., AC)	3510 V
Isolation voltage (pri.-PE, AC)	2200 V
Isolation voltage (sec.-PE)	DC 0.5 kV
Isolation voltage (sec.-signal)	DC 0.5 kV
Protection class	I
Protection type	IP20; per EN 60529
Resistance to reverse feed	≤ DC 35 V
Overvoltage category	III (≤ 2000 m a.s.l.); II (
Pollution degree	2
Transient suppression (primary)	Yes
Overvoltage protection; secondary	Internal protective circuit ≤ 35 VDC (in the event of a fault)
Short-circuit-protected	Yes
Open-circuit-proof	Yes
Parallel operation	Yes
Series operation	Yes
MTBF	

Connection data	
Connection type 1	Input/signaling
Connection technology	CAGE CLAMP®
WAGO connector	WAGO 721 Series
Solid conductor	0.08 ... 2.5 mm² / 28 ... 12 AWG
Fine-stranded conductor	0.08 ... 2.5 mm² / 28 ... 12 AWG
Fine-stranded conductor; with insulated ferrule	0.25 ... 1.5 mm² / 20 ... 16 AWG
Fine-stranded conductor; with uninsulated ferrule	0.25 ... 2.5 mm² / 20 ... 14 AWG
Strip length	8 ... 9 mm / 0.31 ... 0.35 inches
Connection type 2	Output
Connection technology 2	Push-in CAGE CLAMP®
WAGO connector 2	WAGO 831 Series
Solid conductor 2	0.5 ... 10 mm² / 20 ... 8 AWG
Fine-stranded conductor 2	0.5 ... 10 mm² / 20 ... 8 AWG
Fine-stranded conductor; with insulated ferrule 2	0.5 ... 6 mm²
Fine-stranded conductor; with uninsulated ferrule 2	0.5 ... 6 mm²
Strip length 2	13 ... 15 mm / 0.51 ... 0.59 inches



Physical data	
Width	70 mm / 2.756 inches
Height	130 mm / 5.118 inches
Depth from upper-edge of DIN-rail	130 mm / 5.118 inches
Note (dimensions)	Height without connector Height with connector: 169 mm

Mechanical data	
Mounting type	DIN-35 rail

Material data	
Fire load	0.797 MJ
Weight	1450 g

Environmental requirements	
Ambient temperature (operation)	-25 ... +70 °C (Device starts at -40 °C (type-tested))
Ambient temperature (storage)	-40 ... +85 °C
Relative humidity	5 ... 96 % (no condensation permissible)
Derating	-1 %/V (
Climatic category	3K3 (per EN 60721)
Operating altitude (max.)	5000 m

Standards and specifications	
Conformity marking	CE
Standards/specifications	EN 61010-1 EN 61010-2-201 EN 61204-3 UL 61010-1 UL 61010-2-201 SEMI F47

Commercial data	
ETIM 8.0	EC002540
ETIM 7.0	EC002540
PU (SPU)	1 pcs
Packaging type	Box
Country of origin	CN
GTIN	4055143878364
Customs tariff number	85044083900

Environmental Product Compliance	
RoHS Compliance Status	Compliant, No Exemption

Approvals / Certificates



General approvals



Approval	Standard	Certificate Name
UL Underwriters Laboratories Inc.	UL 61010-2-201	E255817

Declarations of conformity and manufacturer's declarations

Approval	Standard	Certificate Name
EU-Declaration of Confor- mity WAGO GmbH & Co. KG	-	-
MFD with product refe- rence WAGO GmbH & Co. KG	-	-
UK-Declaration of Confor- mity WAGO GmbH & Co. KG	-	-

Approvals for hazardous areas



Approval	Standard	Certificate Name
UL Underwriters Laboratories Inc. (HAZARDOUS LOCA- TIONS)	UL 121201	A-E198726

Downloads

Environmental Product Compliance

Compliance Search
Environmental Product Compliance 2787-2147



Documentation

Manual
Product Manual Power supply; Pro 2; 1-phase; 24 VDC output voltage; 20 A output current

V 1.2.2
18.02.2022

pdf
8262.81 KB



Bid Text			
2787-2147_EUSA	04.07.2019	docx 23.26 KB	↓
2787-2147_EUSA	04.07.2019	xml 7.90 KB	↓
ausschreiben.de 2787-2147			↓



Instruction Leaflet

WAGO Stromversor- gung Pro 2	V 1.1.0 26.04.2021	pdf 4461.95 KB
---------------------------------	-----------------------	-------------------



CAD/CAE-Data



CAD data			
2D/3D Models	2787-2147		↓

CAE data			
EPLAN Data Portal	2787-2147		↓
ZUKEN Portal	2787-2147		↓

Engineering-Software				
Configuration and Commissioning Software				
WAGO Interface Configuration Software G2 FULL	1.00.10.01 20.01.2022	exe 112213.07 KB		↓
WAGO Interface Configuration Software G2 SMALL	1.00.10.01 20.01.2022	exe 30238.22 KB		↓

Runtime Software				
Firmware				
2787-2147, Stromversorgung; Pro 2	V 010513 12.10.2021	zip 1087.36 KB		↓

1 Compatible Products
1.1 Optional Accessories
1.1.1 Cables and connectors
1.1.1.1 Communication cable



Item No.: [750-923/000-001](#)
Configuration cable; USB connector;
Length: 5 m

1.1.2 Communication
1.1.2.1 Communication cable



Item No.: [750-923](#)
Configuration cable; USB connector;
Length: 2.5 m

1.1.2.2 Communication module



Item No.: 2789-9023 Communication module; EtherNet/IP; communication capability	Item No.: 2789-9080 Communication module; IO-Link; communication capability	Item No.: 2789-9015 Communication module; Modbus RTU; RJ45; communication capability	Item No.: 2789-9052 Communication module; Modbus TCP; communication capability
---	---	--	--

1.1.3 Marking

1.1.3.1 Marker



Item No.: 2009-115 WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; white

1.1.3.2 Marker carrier



Item No.: 2789-1233 Marker carrier; for WMB or marking strips; Length: 33 mm
--

1.1.3.3 Marking strip



Item No.: 2009-110 Marking strips; for Smart Printer; on reel; not stretchable; plain; snap-on type; white
--

1.1.4 Tool

1.1.4.1 Operating tool



Item No.: 210-720 Operating tool; Blade: 3.5 x 0.5 mm; with a partially insulated shaft; multicoloured	Item No.: 210-721 Operating tool; Blade: 5.5 x 0.8 mm; with a partially insulated shaft; multicoloured
--	--