

PHOTOCOUPLER **PS9821-1,-2**

HIGH CMR, 15 Mbps OPEN COLLECTOR OUTPUT TYPE 8-PIN SSOP (SO-8) -NEPOC Series3.3 V HIGH-SPEED PHOTOCOUPLER

DESCRIPTION

The PS9821-1 and PS9821-2 are active-low type high-speed photocouplers that use a GaAlAs light-emitting diode on the input side and a photodetector IC that includes a photodiode and a signal processor on the same chip on the output side.


The PS9821-1, -2 are designed specifically for high common mode transient immunity (CMR) and low pulse width distortion, PS9821-2 is suitable for high density applications.

FEATURES

- Low power consumption (Vcc = 3.3 V)
- Pulse width distortion (| tphl-tplh | = 35 ns MAX.)
- High common mode transient immunity (CMH, CML = $\pm 15 \text{ kV}/\mu \text{s MIN.}$)
- 40% reduction of mounting area (5-pin SOP × 2)
- · High-speed (15 Mbps)
- High isolation voltage (BV = 2 500 Vr.m.s.)
- · Open collector output
- Ordering number of tape product: PS9821-1-F3, F4: 1 500 pcs/reel
 : PS9821-2-F3, F4: 1 500 pcs/reel
- Pb-Free product
- · Safety standards
 - UL approved: File No. E72422
 - DIN EN60747-5-2 (VDE0884 Part2) approved No.40008347 (option)

APPLICATIONS

- · Measurement equipment
- PDP
- FA Network




TRUTH TABLE


LED	Output
ON	L
OFF	Н

The information in this document is subject to change without notice. Before using this document, please confirm that this is the latest version.

PACKAGE DIMENSIONS (UNIT: mm)



MARKING EXAMPLE



<R> ORDERING INFORMATION

Part Number	Order Number	Solder Plating Specification	Packing Style	Safety Standards Approval	Application Part Number*
PS9821-1	PS9821-1-A	Pb-Free	20 pcs (Tape 20 pcs cut)	Standard products	PS9821-1
PS9821-1-F3	PS9821-1-F3-A		Embossed Tape 1 500 pcs/reel	(UL approved)	
PS9821-1-F4	PS9821-1-F4-A				
PS9821-2	PS9821-2-A		20 pcs (Tape 20 pcs cut)		PS9821-2
PS9821-2-F3	PS9821-2-F3-A		Embossed Tape 1 500 pcs/reel		
PS9821-2-F4	PS9821-2-F4-A				
PS9821-1-V	PS9821-1-V-A		20 pcs (Tape 20 pcs cut)	DIN EN60747-5-2	PS9821-1
PS9821-1-V-F3	PS9821-1-V-F3-A		Embossed Tape 1 500 pcs/reel	(VDE0884 Part2)	
PS9821-1-V-F4	PS9821-1-V-F4-A			approved (Option)	
PS9821-2-V	PS9821-2-V-A		20 pcs (Tape 20 pcs cut)		PS9821-2
PS9821-2-V-F3	PS9821-2-V-F3-A		Embossed Tape 1 500 pcs/reel		
PS9821-2-V-F4	PS9821-2-V-F4-A				

^{*1} For the application of the Safety Standard, following part number should be used.

ABSOLUTE MAXIMUM RATINGS (TA = 25°C, unless otherwise specified)

Parameter		Symbol	Ratings		Unit		
			PS9821-1	PS9821-2			
Diode	Forward Current	lF	20 *1	15 ^{*2}	mA		
	Reverse Voltage	VR	5		V/ch		
Detector	Supply Voltage	Vcc	-	7	V		
	Output Voltage	Vo	7		V/ch		
	Output Current	lo	25		mA/ch		
	Power Dissipation *3	Pc	40		mW/ch		
Isolation Voltage*4		BV	2 500		Vr.m.s.		
Operating Ambient Temperature		TA	-40 to +85		°C		
Storage -	Temperature	T _{stg}	-55 to +125		-55 to +125		°C

- *1 Reduced to 0.3 mA/ $^{\circ}$ C at T_A = 60 $^{\circ}$ C or more.
- *2 Reduced to 0.1 mA/°C at $T_A = 60$ °C or more.
- *3 Applies to output pin Vo (collector pin). Reduced to 1.5 mW/ $^{\circ}$ C at T_A = 65 $^{\circ}$ C or more.
- *4 AC voltage for 1 minute at T_A = 25°C, RH = 60% between input and output. Pins 1-4 shorted together, 5-8 shorted together.

RECOMMENDED OPERATING CONDITIONS

Parameter	Symbol	MIN.	TYP.	MAX.	Unit
Low Level Input Voltage	V _{FL}	0		0.8	V
High Level Input Current	lғн	6.3	10	12.5	mA
Supply Voltage	Vcc	2.7		3.6	٧
Pull-up Resistance	R∟	330		4 k	Ω
TLL (R _L = 1.0 kΩ, loads)	N			5	


ELECTRICAL CHARACTERISTICS (1/2) ($T_A = -40 \text{ to } +85^{\circ}\text{C}$, unless otherwise specified)

	Parameter	Symbol	Conditions	MIN.	TYP. *1	MAX.	Unit
Diode	Forward Voltage	VF	IF = 10 mA, T _A = 25°C	1.4	1.65	1.8	V
	Reverse Current	lR	VR = 3.0 V, TA = 25°C			10	μΑ
	Terminal Capacitance	Ct	V _F = 0 V, f = 1 MHz, T _A = 25°C		30		pF
Detector	High Level Output Current	Іон	Vcc = Vo = 3.3 V, I _F = 0.8 mA		1	80	μΑ
			Vcc = Vo = 5.5 V, I _F = 0.8 mA		1*2		
	Low Level Output Voltage *3	Vol	$Vcc = 3.3 \text{ V}, I_F = 5.0 \text{ mA}, I_{OL} = 13 \text{ mA}$		0.2	0.6	V
			$Vcc = 5.5 \text{ V}, I_F = 5.0 \text{ mA}, I_{OL} = 13 \text{ mA}$		0.2*2		
	High Level Supply Current	Іссн	Vcc = 3.3 V, I _F = 0 mA, Vo = open		4	7	mA
	(PS9821-1)		Vcc = 5.5 V, I _F = 0 mA, Vo = open		5 ^{*2}		
	High Level Supply Current		Vcc = 3.3 V, I _F = 0 mA, Vo = open		8	14	
	(PS9821-2)		Vcc = 5.5 V, IF = 0 mA, Vo = open		10 ^{*2}		
	Low Level Supply Current	Iccl	Vcc = 3.3 V, I _F = 10 mA, Vo = open		7	10	
	(PS9821-1)		Vcc = 5.5 V, I _F = 10 mA, Vo = open		9*²		
	Low Level Supply Current		Vcc = 3.3 V, I _F = 10 mA, Vo = open		14	20	
	(PS9821-2)		Vcc = 5.5 V, I _F = 10 mA, Vo = open		18 ^{*2}		
Coupled	Threshold Input Current	IFHL	$Vcc = 3.3 \text{ V}, Vo = 0.8 \text{ V}, RL = 350 \Omega$		2.5	5	mA
	$(H \rightarrow L)$		$Vcc = 5 \text{ V}, Vo = 0.8 \text{ V}, RL = 350 \Omega$		2.5 ^{*2}		
	Isolation Resistance	Rı-o	$V_{I-O} = 1 \text{ kV}_{DC}, RH = 40 \text{ to } 60\%,$ $T_A = 25^{\circ}C$	10 ¹¹			Ω
	Insulation Resistance (Input-Input), (PS9821-2)	Rı-ı	$V_{I-I} = 1 \text{ kVpc}, \text{ RH} = 40 \text{ to } 60\%,$ $T_A = 25^{\circ}\text{C}$	10 ¹⁰			Ω
	Isolation Capacitance	C _{I-O}	V = 0 V, f = 1 MHz, T _A = 25°C		0.6		pF
	Insulation Capacitance (Input-Input), (PS9821-2)	C _{I-I}	V = 0 V, f = 1 MHz, T _A = 25°C		0.3		pF
	Propagation Delay Time	t PHL	T _A = 25°C		45	75	ns
	$(H \rightarrow L)^{*4}$		$Vcc = 3.3 \text{ V}, \text{ RL} = 350 \Omega, \text{ IF} = 7.5 \text{ mA}$			100	
			$Vcc = 5 \text{ V}, \text{ RL} = 350 \Omega, \text{ IF} = 7.5 \text{ mA}$		38 ^{*2}		
	Propagation Delay Time	t PLH	T _A = 25°C		50	75	
	$(L \rightarrow H)^{*4}$		$Vcc = 3.3 \text{ V}, \text{ RL} = 350 \Omega, \text{ IF} = 7.5 \text{ mA}$			100	
			$Vcc = 5 \text{ V}, \text{ R}_L = 350 \Omega, \text{ I}_F = 7.5 \text{ mA}$		43 ^{*2}		
	Rise Time	tr	$Vcc = 3.3 \text{ V}, \text{ RL} = 350 \Omega, \text{ IF} = 7.5 \text{ mA}$		20		
			$Vcc = 5 \text{ V}, \text{ R}_L = 350 \Omega, \text{ I}_F = 7.5 \text{ mA}$		20 ^{*2}		
	Fall Time	t f	$\mbox{Vcc} = 3.3 \mbox{ V, RL} = 350 \Omega, \mbox{ IF} = 7.5 \mbox{ mA}$		5		
			$Vcc = 5 \text{ V}, \text{ RL} = 350 \Omega, \text{ IF} = 7.5 \text{ mA}$		5 ^{*2}		
	Pulse Width Distortion (PWD)	tplH—tpHL	Vcc = 3.3 V, R _L = 350 Ω , I _F = 7.5 mA		5	35	
			$Vcc = 5 \text{ V}, \text{ RL} = 350 \Omega, \text{ IF} = 7.5 \text{ mA}$		5 ^{*2}		
	Propagation Delay Skew	t psk	$Vcc = 3.3 \text{ V}, \text{ RL} = 350 \Omega, \text{ IF} = 7.5 \text{ mA}$			40	

ELECTRICAL CHARACTERISTICS (2/2) (TA = -40 to +85°C, unless otherwise specified)


	Parameter	Symbol	Conditions	MIN.	TYP. *1	MAX.	Unit
Coupled	Common Mode Transient Immunity at High	СМн	$V_{CC} = 3.3 \text{ V}, \text{ RL} = 350 \ \Omega, \text{ T}_{A} = 25^{\circ}\text{C},$ $I_{F} = 0 \text{ mA}, \text{ Vo} > 2 \text{ V}, \text{ VcM} = 1 \text{ kV}$	15	20		kV/μs
	Level Output ^{*5}		$V_{CC} = 5 \text{ V}, \text{ R}_{L} = 350 \ \Omega, \text{ T}_{A} = 25^{\circ}\text{C},$ $I_{F} = 0 \text{ mA}, \text{ Vo} > 2 \text{ V}, \text{ V}_{CM} = 1 \text{ kV}$		20 ^{*2}		
	Common Mode Transient Immunity at Low	CML	$\label{eq:Vcc} \begin{array}{l} \mbox{Vcc} = 3.3 \ \mbox{V}, \ \mbox{RL} = 350 \ \Omega, \ \mbox{T}_{\mbox{\scriptsize A}} = 25^{\circ}\mbox{C}, \\ \mbox{IF} = 7.5 \ \mbox{mA}, \ \mbox{Vo} < 0.8 \ \mbox{V}, \ \mbox{Vcm} = 1 \ \mbox{kV} \end{array}$	15	20		
	Level Output ^{'5}		$\label{eq:Vcc} \begin{array}{l} \mbox{Vcc} = 5 \mbox{ V, } \mbox{R}_{L} = 350 \ \Omega, \mbox{T}_{A} = 25 \mbox{°C}, \\ \mbox{I}_{F} = 7.5 \mbox{ mA, Vo} < 0.8 \mbox{ V, V}_{CM} = 1 \mbox{ kV} \end{array}$		20 ^{*2}		


- *1 Typical values at T_A = 25°C
- *2 These values are reference values.
- *3 Because Vol of 2 V or more may be output when LED current input and when output supply of Vcc = 2.6 V or less, it is important to confirm the characteristics (operation with the power supply on and off) during design, before using this device.
- *4 Test circuit for propagation delay time




 $\textbf{Remark} \quad \textbf{C} \textbf{\llcorner includes probe and stray wiring capacitance}.$

*5 Test circuit for common mode transient immunity










USAGE CAUTIONS

- 1. This product is weak for static electricity by designed with high-speed integrated circuit so protect against static electricity when handling.
- **2.** By-pass capacitor of 0.1 μ F is used between Vcc and GND near device. Also, ensure that the distance between the leads of the photocoupler and capacitor is no more than 10 mm.
- 3. Avoid storage at a high temperature and high humidity.


TYPICAL CHARACTERISTICS (TA = 25°C, unless otherwise specified)








OUTPUT VOLTAGE vs. INPUT CURRENT




Remark The graphs indicate nominal characteristics.







SUPPLY CURRENT vs. AMBIENT TEMPERATURE




LOW LEVEL OUTPUT VOLTAGE vs. AMBIENT TEMPERATURE




THRESHOLD INPUT CURRENT vs. AMBIENT TEMPERATURE



PULSE WIDTH DISTORTION vs. AMBIENT TEMPERATURE




PROPAGATION DELAY TIME vs. INPUT CURRENT




Remark The graphs indicate nominal characteristics.


PROPAGATION DELAY TIME vs. AMBIENT TEMPERATURE




SWITCHING TIME vs. AMBIENT TEMPERATURE



TAPING SPECIFICATIONS (UNIT: mm)



RECOMMENDED MOUNT PAD DIMENSIONS (UNIT: mm)



NOTES ON HANDLING

1. Recommended soldering conditions

(1) Infrared reflow soldering

Peak reflow temperature
 260°C or below (package surface temperature)


Time of peak reflow temperature
 Time of temperature higher than 220°C
 60 seconds or less

Time to preheat temperature from 120 to 180°C 120±30 s
 Number of reflows Three

Flux
 Rosin flux containing small amount of chlorine (The flux with a

maximum chlorine content of 0.2 Wt% is recommended.)

Recommended Temperature Profile of Infrared Reflow



Time (s)

(2) Wave soldering

• Temperature 260°C or below (molten solder temperature)

• Time 10 seconds or less

• Preheating conditions 120°C or below (package surface temperature)

• Number of times One (Allowed to be dipped in solder including plastic mold portion.)

• Flux Rosin flux containing small amount of chlorine (The flux with a maximum chlorine

content of 0.2 Wt% is recommended.)

(3) Soldering by soldering iron

Peak temperature (lead part temperature) 350°C or below
 Time (each pins) 3 seconds or less

Flux
 Rosin flux containing small amount of chlorine (The flux with a

maximum chlorine content of 0.2 Wt% is recommended.)

(a) Soldering of leads should be made at the point 1.5 to 2.0 mm from the root of the lead.

(b) Please be sure that the temperature of the package would not be heated over 100°C.

(4) Cautions

Fluxes

Avoid removing the residual flux with freon-based and chlorine-based cleaning solvent.

2. Cautions regarding noise

Be aware that when voltage is applied suddenly between the photocoupler's input and output or between collector-emitters at startup, the output transistor may enter the on state, even if the voltage is within the absolute maximum ratings.

USAGE CAUTIONS

- 1. Protect against static electricity when handling.
- 2. Avoid storage at a high temperature and high humidity.

- The information in this document is current as of May, 2006. The information is subject to change
 without notice. For actual design-in, refer to the latest publications of NEC Electronics data sheets or
 data books, etc., for the most up-to-date specifications of NEC Electronics products. Not all
 products and/or types are available in every country. Please check with an NEC Electronics sales
 representative for availability and additional information.
- No part of this document may be copied or reproduced in any form or by any means without the prior
 written consent of NEC Electronics. NEC Electronics assumes no responsibility for any errors that may
 appear in this document.
- NEC Electronics does not assume any liability for infringement of patents, copyrights or other intellectual property rights of third parties by or arising from the use of NEC Electronics products listed in this document or any other liability arising from the use of such products. No license, express, implied or otherwise, is granted under any patents, copyrights or other intellectual property rights of NEC Electronics or others.
- Descriptions of circuits, software and other related information in this document are provided for illustrative
 purposes in semiconductor product operation and application examples. The incorporation of these
 circuits, software and information in the design of a customer's equipment shall be done under the full
 responsibility of the customer. NEC Electronics assumes no responsibility for any losses incurred by
 customers or third parties arising from the use of these circuits, software and information.
- While NEC Electronics endeavors to enhance the quality, reliability and safety of NEC Electronics products, customers agree and acknowledge that the possibility of defects thereof cannot be eliminated entirely. To minimize risks of damage to property or injury (including death) to persons arising from defects in NEC Electronics products, customers must incorporate sufficient safety measures in their design, such as redundancy, fire-containment and anti-failure features.
- NEC Electronics products are classified into the following three quality grades: "Standard", "Special" and "Specific"

The "Specific" quality grade applies only to NEC Electronics products developed based on a customer-designated "quality assurance program" for a specific application. The recommended applications of an NEC Electronics product depend on its quality grade, as indicated below. Customers must check the quality grade of each NEC Electronics product before using it in a particular application.

- "Standard": Computers, office equipment, communications equipment, test and measurement equipment, audio and visual equipment, home electronic appliances, machine tools, personal electronic equipment and industrial robots.
- "Special": Transportation equipment (automobiles, trains, ships, etc.), traffic control systems, anti-disaster systems, anti-crime systems, safety equipment and medical equipment (not specifically designed for life support).
- "Specific": Aircraft, aerospace equipment, submersible repeaters, nuclear reactor control systems, life support systems and medical equipment for life support, etc.

The quality grade of NEC Electronics products is "Standard" unless otherwise expressly specified in NEC Electronics data sheets or data books, etc. If customers wish to use NEC Electronics products in applications not intended by NEC Electronics, they must contact an NEC Electronics sales representative in advance to determine NEC Electronics' willingness to support a given application.

(Note)

- (1) "NEC Electronics" as used in this statement means NEC Electronics Corporation and also includes its majority-owned subsidiaries.
- (2) "NEC Electronics products" means any product developed or manufactured by or for NEC Electronics (as defined above).

M8E 02.11-1

Caution

GaAs Products

This product uses gallium arsenide (GaAs).

GaAs vapor and powder are hazardous to human health if inhaled or ingested, so please observe the following points.

- Follow related laws and ordinances when disposing of the product. If there are no applicable laws and/or ordinances, dispose of the product as recommended below.
 - Commission a disposal company able to (with a license to) collect, transport and dispose of materials that contain arsenic and other such industrial waste materials.
- 2. Exclude the product from general industrial waste and household garbage, and ensure that the product is controlled (as industrial waste subject to special control) up until final disposal.
- Do not burn, destroy, cut, crush, or chemically dissolve the product.
- Do not lick the product or in any way allow it to enter the mouth.

▶ For further information, please contact

NEC Compound Semiconductor Devices Hong Kong Limited

E-mail: contact@ncsd-hk.necel.com

Hong Kong Head Office TEL: +852-3107-7303 FAX: +852-3107-7309
Taipei Branch Office TEL: +886-2-8712-0478 FAX: +886-2-2545-3859
Korea Branch Office TEL: +82-2-558-2120 FAX: +82-2-558-5209

NEC Electronics (Europe) GmbH http://www.eu.necel.com/

TEL: +49-211-6503-0 FAX: +49-211-6503-1327

California Eastern Laboratories, Inc. http://www.cel.com/

TEL: +1-408-988-3500 FAX: +1-408-988-0279

Compound Semiconductor Devices Division NEC Electronics Corporation URL: http://www.ncsd.necel.com/



4590 Patrick Henry Drive Santa Clara, CA 95054-1817 Telephone: (408) 919-2500

Facsimile: (408) 988-0279

Subject: Compliance with EU Directives

CEL certifies, to its knowledge, that semiconductor and laser products detailed below are compliant with the requirements of European Union (EU) Directive 2002/95/EC Restriction on Use of Hazardous Substances in electrical and electronic equipment (RoHS) and the requirements of EU Directive 2003/11/EC Restriction on Penta and Octa BDE.

CEL Pb-free products have the same base part number with a suffix added. The suffix –A indicates that the device is Pb-free. The -AZ suffix is used to designate devices containing Pb which are exempted from the requirement of RoHS directive (*). In all cases the devices have Pb-free terminals. All devices with these suffixes meet the requirements of the RoHS directive.

This status is based on CEL's understanding of the EU Directives and knowledge of the materials that go into its products as of the date of disclosure of this information.

Restricted Substance per RoHS	Concentration Limit per RoHS (values are not yet fixed)	Concentration in CEL	on contained devices	
Lead (Pb)	< 1000 PPM	-A Not Detected	-AZ (*)	
Mercury	< 1000 PPM	Not Detected		
Cadmium	< 100 PPM	Not Detected		
Hexavalent Chromium	< 1000 PPM	Not Detected		
PBB	< 1000 PPM	Not Detected		
PBDE	< 1000 PPM	Not Detected		

If you should have any additional questions regarding our devices and compliance to environmental standards, please do not hesitate to contact your local representative.

Important Information and Disclaimer: Information provided by CEL on its website or in other communications concerting the substance content of its products represents knowledge and belief as of the date that it is provided. CEL bases its knowledge and belief on information provided by third parties and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. CEL has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. CEL and CEL suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall CEL's liability arising out of such information exceed the total purchase price of the CEL part(s) at issue sold by CEL to customer on an annual basis.

See CEL Terms and Conditions for additional clarification of warranties and liability.