Chip Bead ; CIB/CIM Series
For EMI Suppression



Feature

- Smallest beads suitable for surface mounting
- Perfect shape for automatic mounting, with no directionality.
- Excellent solderability and high heat resistance for either flow or reflow soldering.
- Monolithic inorganic material construction for high reliability.
- Closed magnetic circuit configuration avoids crosstalk and is suitable for high density PCBs.

Application

- High frequency EMI prevention application to computers, printers, VCRs, TVs and mobile phones.

The CIB/CIM Series are used for EMI suppression filter. These beads suppress electro-magnetic wave noise by increased impedance, especially by increased resistance at noise frequency.

CIB Series
The CIB Series is composed of mono-layer internal conductor that allows low impedance and low DC resistance.

CIM Series
The CIM Series display high impedance because it is composed of a multilayered internal conductor and has excellent attenuation characteristics for wide band frequencies.

Operating Temp	-55~+125℃
Storage Temp	-10~+40℃

Dimensions



Unit: mm

SIZE CODE	L	W	t	d
03	0.6±0.03	0.3±0.03	0.3±0.03	0.15±0.05
05	1.0±0.05	0.5±0.05	0.5±0.05	0.25±0.1
10	1.6±0.15	0.8±0.15	0.8±0.15	0.3±0.2
21	2.0±0.2	1.25±0.2	0.9±0.2	0.5+0.2,-0.3
31	3.2±0.2	1.6±0.2	1.1±0.2	0.5+0.2,-0.3
32	3.2±0.2	2.5±0.2	1.3±0.2	0.5±0.3
41	4.5±0.2	1.6±0.2	1.6±0.2/1.2±0.2	0.5±0.3
43	4.5±0.2	3.2±0.2	1.5±0.2	0.5±0.3

Part Numbering

CI	M	03	J	121	N	C
(1)	(2)	(3)	(4)	(5)	(6)	(7)

(1) Chip Beads
(2) B : Mono-layer type, M : Multi-layer type
(3) Dimension
(4) Material Code
P,U : Broad impedance, especially suppresses noise in the 10~200MHz range
J : Suppresses noise in the 100~300MHz range
K : Suppresses noise in the 200MHz above
N : Suppresses noise in the 200~500MHz range
(5) Nominal impedance (110 : 11Ω ; 121 : 120Ω)
(6) Thickness option (N : Standard , A : Thinner than standard , B : Thicker than standard)
(7) Packaging(C : paper tape, E : embossed tape)

CIM 0603(0201) Type

Part No.	Thickness (mm)	Impedance (Ω)±25% @100 MHz	DC Resistance (Ω) Max.	Rated Current (mA) Max.
CIM 03N 300	0.3±0.03	30	0.8	150
CIM 03N 800	0.3±0.03	80	1.2	100
CIM 03U 800	0.3±0.03	80	0.5	200
CIM 03U 121	0.3±0.03	120	0.8	200
CIM 03U 241	0.3±0.03	240	1.0	100
CIM 03J 121	0.3±0.03	120	0.8	200
CIM 03J 241	0.3±0.03	240	1.0	100

Electrical Characteristics

CIM03N300



CIM03N800



CIM03U800



CIM03U121



CIM03U241



CIM03J121



CIM03J241



CIM 1005(0402) Type

Part No.	Thickness (mm)	Impedance (Ω)±25% @100 MHz	DC Resistance (Ω) Max.	Rated Current (mA) Max.
CIM 05U 100	0.5±0.05	10	0.05	1200
CIM 05U 300	0.5±0.05	30	0.10	700
CIM 05U 600	0.5±0.05	60	0.15	600
CIM 05U 800	0.5±0.05	80	0.20	600
CIM 05U 121	0.5±0.05	120	0.25	500
CIM 05U 221	0.5±0.05	220	0.35	400
CIM 05U 241	0.5±0.05	240	0.35	400
CIM 05U 301	0.5±0.05	300	0.45	400
CIM 05U 471	0.5±0.05	470	0.55	300
CIM 05U 601	0.5±0.05	600	0.60	300
CIM 05U 102	0.5±0.05	1000	1.00	200
CIM 05 J 300	0.5±0.05	30	0.20	700
CIM 05 J 600	0.5±0.05	60	0.20	600
CIM 05 J 800	0.5±0.05	80	0.25	600
CIM 05 J 121	0.5±0.05	120	0.30	500
CIM 05 J 221	0.5±0.05	220	0.35	400
CIM 05 J 241	0.5±0.05	240	0.35	400
CIM 05 J 301	0.5±0.05	300	0.45	400
CIM 05 J 471	0.5±0.05	470	0.55	300
CIM 05 J 601	0.5±0.05	600	0.60	300
CIM 05 J 102	0.5±0.05	1000	0.80	250
CIM 05 J 152	0.5±0.05	1500	1.00	250
CIM 05 J 182	0.5±0.05	1800	1.40	100
CIM 05 N 750	0.5±0.05	75	0.35	300
CIM 05 N 121	0.5±0.05	120	0.55	300
CIM 05 N 221	0.5±0.05	220	0.80	200
CIM 05 F 050	0.5±0.05	5	0.08	500
CIM 05 F 100	0.5±0.05	10	0.10	300
CIM 05 F 220	0.5±0.05	22	0.20	300
CIM 05 F 470	0.5±0.05	47	0.35	300
CIM 05 F 750	0.5±0.05	75	0.40	300
CIM 05 F 121	0.5±0.05	120	0.55	300
CIM 05 F 221	0.5±0.05	220	0.80	200

Electrical Characteristics

CIM05U100



CIM05U300



CIM05U600



CIM05U800



CIM05U121



CIM05U241



CIM05U301



CIM05U471



CIM05U601



CIM05U102



CIM05N750



CIM05N121



CIM05N221



Electrical Characteristics

CIM05J300



CIM05J600



CIM05J800



CIM05J121



CIM05J241



CIM05J301



CIM05J471



CIM05J601



CIM05J102



CIM05J152



CIM05J182



CIM05F470



CIM05F121



CIB/CIM 1608(0603) Type

Part No.	Thickness (mm)	Impedance (Ω)±25% @100 MHz	DC Resistance (Ω) Max.	Rated Current (mA) Max.
CIB 10P 100	0.8±0.15	10	0.05	1000
CIB 10P 220	0.8±0.15	22	0.05	1500
CIB 10P 260	0.8±0.15	26	0.08	1000
CIB 10P 300	0.8±0.15	30	0.08	1000
CIB 10J 300	0.8±0.15	30	0.08	1000
CIB 10P 330	0.8±0.15	33	0.08	1000
CIM 10U 800	0.8±0.15	80	0.15	600
CIM 10U 121	0.8±0.15	120	0.15	500
CIM 10U 221	0.8±0.15	220	0.30	400
CIM 10U 241	0.8±0.15	240	0.30	400
CIM 10U 471	0.8±0.15	470	0.35	300
CIM 10U 601	0.8±0.15	600	0.45	300
CIM 10U 102	0.8±0.15	1000	0.60	250
CIM 10U 202	0.8±0.15	2000(at 70MHz)	1.20	200
CIM 10J 400	0.8±0.15	40	0.12	600
CIM 10J 470	0.8±0.15	47	0.12	600
CIM 10J 600	0.8±0.15	60	0.12	600
CIM 10J 750	0.8±0.15	75	0.12	550
CIM 10J 800	0.8±0.15	80	0.20	550
CIM 10J 121	0.8±0.15	120	0.20	500
CIM 10J 151	0.8±0.15	150	0.20	400
CIM 10J 221	0.8±0.15	220	0.30	400
CIM 10J241	0.8±0.15	240	0.30	400
CIM 10J301	0.8±0.15	300	0.35	400
CIM 10J331	0.8±0.15	330	0.35	400
CIM 10J 471	0.8±0.15	470	0.35	300
CIM 10J 601	0.8±0.15	600	0.45	300
CIM 10J 751	0.8±0.15	750	0.55	300
CIM 10J 102	0.8±0.15	1000	0.70	250
CIM 10J 152	0.8±0.15	1500	1.00	250
CIM 10J 252	0.8±0.15	2500	1.50	200
CIM 10K 152	0.8±0.15	1500	0.80	250
CIM 10K 202	0.8±0.15	2000	1.00	200
CIM 10K 252	0.8±0.15	2500	1.20	200
CIM 10N 700	0.8±0.15	70	0.30	500
CIM 10N 121	0.8±0.15	120	0.45	400
CIM 10N 241	0.8±0.15	240	0.60	300
CIM 10F 470	0.8±0.15	47	0.25	550
CIM 10F 600	0.8±0.15	60	0.25	550
CIM 10F 121	0.8±0.15	120	0.30	500
CIM 10F 331	0.8±0.15	330	0.58	400
CIM 10F471	0.8±0.15	470	0.85	300

Electrical Characteristics

CIB10P100



CIB10P220



CIB10P260



CIB10P300



CIB10J300



CIB10P330



CIM10U121



CIM10U221



CIM10U241



CIM10U471



CIM10U601



CIM10U102



CIM10U202



Electrical Characteristics

CIM10J400



CIM10J470



CIM10J600



CIM10J750



CIM10J800



CIM10J121



CIM10J151



CIM10J241



CIM10J301



CIM10J471



CIM10J601



CIM10J751



CIM10J102



CIM10J152



CIM10K152



CIM10K202



CIM10K252



CIM10N700



CIM10N121



CIM10N241



CIM10F600



CIM10F121



CIB/CIM 2012(0805) Type

Part No.	Thickness (mm)	Impedance (Ω)±25% @100 MHz	DC Resistance (Ω) Max.	Rated Current (mA) Max.
CIB 21P 110	0.9±0.2	11	0.05	2000
CIB 21P 150	0.9±0.2	15	0.05	2000
CIB 21P 260	0.9±0.2	26	0.05	2000
CIB 21P 330	0.9±0.2	33	0.05	1500
CIB 21P 470	0.9±0.2	47	0.05	1500
CIM 21U 800	0.9±0.2	80	0.10	900
CIM 21U 101	0.9±0.2	100	0.10	500
CIM 21U 121	0.9±0.2	120	0.10	500
CIM 21U 151	0.9±0.2	150	0.15	400
CIM 21U 241	0.9±0.2	240	0.15	400
CIM 21U 301	0.9±0.2	300	0.15	400
CIM 21U 471	0.9±0.2	470	0.25	400
CIM 21U 601	0.9±0.2	600	0.30	400
CIM 21U 102	0.9±0.2	1000(at 70MHz)	0.45	400
CIM 21U 202	0.9±0.2	2000(at 70MHz)	0.70	300
CIB 21J 260	0.9±0.2	26	0.05	2000
CIB 21J 400	0.9±0.2	40	0.05	2000
CIM 21J 600	0.9±0.2	60	0.08	900
CIM 21J 800	0.9±0.2	80	0.08	900
CIM 21J 121	0.9±0.2	120	0.15	600
CIM 21J 151	0.9±0.2	150	0.15	500
CIM 21J 221	0.9±0.2	220	0.02	400
CIM 21J 241	0.9±0.2	240	0.20	400
CIM 21J 301	0.9±0.2	300	0.25	400
CIM 21J 471	0.9±0.2	470	0.25	400
CIM 21J 601	0.9±0.2	600	0.25	400
CIM 21J 102	0.9±0.2	1000	0.40	400
CIM 21J 152	0.9±0.2	1500(at 70MHz)	0.55	300
CIM 21J 182	0.9±0.2	1800(at 70MHz)	0.45	300
CIM 21J 202	0.9±0.2	2000(at 70MHz)	0.50	300
CIM 21K 152	0.9±0.2	1500	0.45	300
CIM 21K 252	0.9±0.2	2500	0.80	250
CIM 21N 700	0.9±0.2	70	0.20	600
CIM 21N 121	0.9±0.2	120	0.25	500
CIM 21N 241	0.9±0.2	240	0.3	400

Electrical Characteristics

CIB21P110



CIB21P150



CIB21P260



CIB21P330



CIB21P470



CIM21U800



CIM21U101



CIM21U121



CIM21U151



CIM21U241



CIM21U301



CIM21U471



CIM21U601



CIM21U102



Electrical Characteristics

CIM21U202



CIB21J260



CIB21J400



CIM21J600



CIM21J800



CIM21J121



CIM21J151



CIM21J221



CIM21J241



CIM21J301



CIM21J471



CIM21J601



Electrical Characteristics

CIM21J102



CIM21J152



CIM21J182



CIM21J202



CIM21K152



CIM21K222



CIM21K252



CIM21N700



CIM21N121



CIM21N241



CIB/CIM 3216(1206) Type

Part No.	Thickness (mm)	Impedance (Ω)±25% @100 MHz	DC Resistance (Ω) Max.	Rated Current (mA) Max.
CIB 31P 260	1.1±0.2	26	0.05	2000
CIB 31P 310	1.1±0.2	31	0.05	2000
CIB 31P 500	1.1±0.2	50	0.05	2000
CIB 31P 700	1.1±0.2	70	0.1	1500
CIM 31U 101	1.1±0.2	100	0.15	500
CIM 31U 601	1.1±0.2	600	0.3	400
CIM 31J 151	1.1±0.2	150	0.2	500
CIM 31J 221	1.1±0.2	220	0.2	400
CIM 31J 301	1.1±0.2	300	0.25	400
CIM 31J 601	1.1±0.2	600	0.3	400
CIM 31J 801	1.1±0.2	800	0.4	400
CIM 31J 102	1.1±0.2	1000	0.45	400
CIM 31J 152	1.1±0.2	1500(at 70MHz)	0.55	300

Other Types

Part No.	Thickness (mm)	Impedance (Ω)±25% @100 MHz	DC Resistance (Ω) Max.	Rated Current (mA) Max.
CIB 32P 310	1.3±0.2	31	0.02	3000
CIB 32P 600	1.3±0.2	60	0.02	1500
CIB 41P 800	1.6±0.2	80	0.03	1000
CIB 41P 151	1.6±0.2	150	0.05	1000
CIB 43P 131	1.5±0.2	130	0.04	600
CIB 43P 151	1.5±0.2	150	0.04	600

Customized products are available.
Test equipment : Agilent E4991A+16197A (0603)
Agilent 4291B+16192A (1005)
Agilent 4291B+16193A (1608 and others)

Electrical Characteristics

CIB31P260



CIB31P310



CIB31P500



CIB31P700



CIM31U101



CIM31U601



CIM31J151



CIM31J221



CIM31J301



CIM31J601



CIM31J801



CIM31J102



CIM31J152



Electrical Characteristics

CIB32P310



CIB32P600



CIB41P800



CIB41P151



CIB43P131



CIB43P151