# PRELIMINARY

# NEC LCD Technologies, Ltd.

# TFT COLOR LCD MODULE

NL6448BC26-20F

21 cm (8.4 Type) VGA

# PRELIMINARY DATA SHEET =

DOD-PP-0565 (1st edition)

All information is subject to change without notice. Please confirm the sales representative before starting to design your system.

#### INTRODUCTION

The Copyright to this document belongs to NEC LCD Technologies, Ltd. (hereinafter called "NEC"). No part of this document will be used, reproduced or copied without prior written consent of NEC.

NEC does and will not assume any liability for infringement of patents, copyrights or other intellectual property rights of any third party arising out of or in connection with application of the products described herein except for that directly attributable to mechanisms and workmanship thereof. No license, express or implied, is granted under any patent, copyright or other intellectual property right of NEC.

Some electronic parts/components would fail or malfunction at a certain rate. In spite of every effort to enhance reliability of products by NEC, the possibility of failures and malfunction might not be avoided entirely. To prevent the risks of damage to death, human bodily injury or other property arising out thereof or in connection therewith, each customer is required to take sufficient measures in its safety designs and plans including, but not limited to, redundant system, fire-containment and anti-failure.

The products are classified into three quality grades: "Standard", "Special", and "Specific" of the highest grade of a quality assurance program at the choice of a customer. Each quality grade is designed for applications described below. Any customer who intends to use a product for application other than that of Standard quality grade is required to contact an NEC sales representative in advance.

The **Standard** quality grade applies to the products developed, designed and manufactured in accordance with the NEC standard quality assurance program, which are designed for such application as any failure or malfunction of the products (sets) or parts/components incorporated therein a customer uses are, directly or indirectly, free of any damage to death, human bodily injury or other property, like general electronic devices.

Examples: Computers, office automation equipment, communications equipment, test and measurement equipment, audio and visual equipment, home electronic appliances, machine tools, personal electronic equipment, industrial robots, etc.

The **Special** quality grade applies to the products developed, designed and manufactured in accordance with an NEC quality assurance program stricter than the standard one, which are designed for such application as any failure or malfunction of the products (sets) or parts/components incorporated therein a customer uses might directly cause any damage to death, human bodily injury or other property, or such application under more severe condition than that defined in the Standard quality grade without such direct damage.

Examples: Control systems for transportation equipment (automobiles, trains, ships, etc.), traffic control systems, anti-disaster systems, anti-crime systems, medical equipment not specifically designed for life support, safety equipment, etc.

The **Specific** quality grade applies to the products developed, designed and manufactured in accordance with the standards or quality assurance program designated by a customer who requires an extremely higher level of reliability and quality for such products.

Examples: Military systems, aircraft control equipment, aerospace equipment, nuclear reactor control systems, medical equipment/devices/systems for life support, etc.

The quality grade of this product is the "Standard" unless otherwise specified in this document.

# **CONTENTS**

INTRODUCTION	2
1. OUTLINE	Δ
1.1 STRUCTURE AND PRINCIPLE	
1.2 APPLICATION	
1.3 FEATURES	
2. GENERAL SPECIFICATIONS	
3. BLOCK DIAGRAM	
4. DETAILED SPECIFICATIONS	S
4.1 MECHANICAL SPECIFICATIONS	
4.2 ABSOLUTE MAXIMUM RATINGS	
4.3 ELECTRICAL CHARACTERISTICS	
4.3.1 LCD panel signal processing board	
4.3.2 Backlight	
4.3.3 Power supply voltage ripple	
4.3.4 Fuse	
4.4 POWER SUPPLY VOLTAGE SEQUENCE	11
4.4.1 LCD panel signal processing board	11
4.4.2 Backlight lighting circuit	11
4.5 CONNECTIONS AND FUNCTIONS FOR INTERFACE PINS	
4.5.1 LCD panel signal processing board	
4.5.2 Backlight	
4.5.3 Positions of plug and socket	
4.6 DISPLAY COLORS AND INPUT DATA SIGNALS	
4.7 DISPLAY POSITIONS AND SCANNING DIRECTIONS	
4.7.1 Setting the LCD module in the landscape position (horizontal)	
4.7.2 Setting the LCD module in the portrait position (vertical)	
4.8 INPUT SIGNAL TIMINGS	17
4.8.1 Outline of input signal timings	
4.8.2 Timing characteristics	18
4.8.3 Input signal timing chart	20
4.9 OPTICS	23
4.9.1 Optical characteristics	23
4.9.2 Definition of contrast ratio	24
4.9.3 Definition of luminance uniformity	
4.9.4 Definition of response times	24
4.9.5 Definition of viewing angles	
5. RELIABILITY TESTS	25
6. PRECAUTIONS	
6.1 MEANING OF CAUTION SIGNS	26
6.2 CAUTIONS	
6.3 ATTENTIONS	
6.3.1 Handling of the product	
6.3.2 Environment	
6.3.3 Characteristics	
6.3.4 Other	
7. OUTLINE DRAWINGS	
7.1 FRONT VIEW	
7.2 REAR VIEW	29
REVISION HISTORY	30

#### 1. OUTLINE

#### 1.1 STRUCTURE AND PRINCIPLE

Color LCD module NL6448BC26-20F is composed of the amorphous silicon thin film transistor liquid crystal display (a-Si TFT LCD) panel structure with driver LSIs for driving the TFT (Thin Film Transistor) array and a backlight.

The a-Si TFT LCD panel structure is injected liquid crystal material into a narrow gap between the TFT array glass substrate and a color-filter glass substrate.

Color (Red, Green, Blue) data signals from a host system (e.g. signal generator, etc.) are modulated into best form for active matrix system by a signal processing circuit, and sent to the driver LSIs which drive the individual TFT arrays.

The TFT array as an electro-optical switch regulates the amount of transmitted light from the backlight assembly, when it is controlled by data signals. Color images are created by regulating the amount of transmitted light through the TFT array of red, green and blue dots.

#### 1.2 APPLICATION

• For industrial use

#### 1.3 FEATURES

- High luminance
- High contrast
- Wide viewing angle
- Wide temperature range
- 6-bit digital RGB signals
- Reversible-scan direction
- LED backlight type
- Replaceable LED holder for backlight
- Suitable for setting in the portrait position (See "4.7.2 Setting the LCD module in the portrait position (vertical)".

#### Comparison table of NL6448BC26-20F and NL6448BC26-22F

Item	NL6448BC26-20F	NL6448BC26-22F
Designed viewing direction	At DPS= low or open: Normal scan  • Viewing direction without image reversal : right side (3 o'clock)  • Viewing direction with contrast peak : left side (9 o'clock)  • Viewing angle with optimum grayscale (γ≒ 2.2) : normal axis(perpendicular)	At DPS= low or open: Normal scan  • Viewing direction without image reversal  : up side (12 o'clock)  • Viewing direction with contrast peak  : down side (6 o'clock)  • Viewing angle with optimum grayscale (γ≒ 2.2)  : normal axis(perpendicular)




# NEC NEC LCD Technologies, Ltd.

## 2. GENERAL SPECIFICATIONS

Display area	170.88 (H) × 128.16 (V) mm
Diagonal size of display	21cm (8.4inches)
Drive system	a-Si TFT active matrix
Display color	262,144 colors
Pixel	640 (H) × 480 (V) pixels
Pixel arrangement	RGB (Red dot, Green dot, Blue dot) vertical stripe
Dot pitch	0.089 (H) × 0.267 (V) mm
Pixel pitch	0.267 (H) × 0.267 (V) mm
Module size	200.0 (W) × 152.0 (H) × 10.5 (D) mm (typ.)
Weight	TBDg (typ.)
Contrast ratio	1,000:1 (typ.)
Viewing angle	At the contrast ratio ≥10:1  • Horizontal: Right side 80° (typ.), Left side 80° (typ.)  • Vertical: Up side 80° (typ.), Down side 80° (typ.)
Designed viewing direction	<ul> <li>At DPS= Low or open: Normal scan</li> <li>Viewing direction without image reversal: right side (3 o'clock)</li> <li>Viewing direction with contrast peak: left side (9 o'clock)</li> <li>Viewing angle with optimum grayscale (γ≒ 2.2): normal axis (perpendicular)</li> </ul>
Polarizer surface	Clear
Polarizer pencil-hardness	3H (min.) [by JIS K5400]
Color gamut	At LCD panel center 40% (typ.) [against NTSC color space]
Response time	$Ton+Toff (10\% \longleftrightarrow 90\%)$ 18ms (typ.)
Luminance	$At IL = 25mA$ $800cd/m^2 \text{ (typ.)}$
Signal system	6-bit digital signals for data of RGB colors, Dot clock (CLK), Data enable (DE), Horizontal synchronous signal (Hsync), Vertical synchronous signal (Vsync)
Power supply voltage	LCD panel signal processing board: 3.3V or 5.0V
Backlight	LED backlight type:  Replaceable part  Lamp holder set: Type No. 84LHS12
Power consumption	At IL= 25mA, Checkered flag pattern (4.1) W (typ., Power dissipation of the inverter is not included.)

#### 3. BLOCK DIAGRAM



Note1: Relations between GND (Signal ground) and FG (Frame ground) in the LCD module are as follows.

|--|

Note2: GND and FG must be connected to customer equipment's ground, and it is recommended that these grounds are connected together in customer equipment.


# PRELIMINARY

# NEC NEC LCD Technologies, Ltd.

NL6448BC26-20F

Note3: Backlight in detail

# Backlight



#### 4. DETAILED SPECIFICATIONS

## 4.1 MECHANICAL SPECIFICATIONS

Parameter	Specification		Unit
Module size	$200.0 \pm 0.5 \text{ (W)} \times 152.0 \pm 0.5 \text{ (H)} \times 10.5 \pm 0.5 \text{ (D)}$	Note1	mm
Display area	170.88 (H) × 128.16 (V)	Note1	mm
Weight	TBD (typ.), TBD (max.)		g

Note1: See "7. OUTLINE DRAWINGS".


## 4.2 ABSOLUTE MAXIMUM RATINGS

Parameter			Symbol	Rating	Unit	Remarks
Power supply voltage	LCD panel signal processing board		VCC	-0.3 to +6.5	V	-
Input voltage	Display No		VD	-0.3 to VCC+0.3	V	
for signals	Function Not		VF	-0.3 to VCC+0.3	V	-
Backlight	Power di	ssipation	PD	1.1	W	per one circuit
Bucklight	Forward	current	IL	Note3	mA	per one circuit
;	Storage temperature		Tst	-30 to +80	°C	-
Operating	Front surface		TopF	-20 to +70	°C	Note4
Operating temperature		Rear surface	TopR	-20 to +70	°C	Note5
Relative humidity Note6				≤ 95	%	Ta≤ 40°C
			RH	≤ 85	%	40 <ta≤ 50°c<="" td=""></ta≤>
			KII	≤ 55	%	50°C <ta≤ 60°c<="" td=""></ta≤>
				≤ 36	%	60°C <ta≤ 70°c<="" td=""></ta≤>
	Absolute humidity Note6		АН	≤ 70 Note7	g/m <sup>3</sup>	Ta> 70°C

Note1: CLK, Hsync, Vsync, DE, DATA (R0 to R5, G0 to G5, B0 to B5)

Note2: DPS

Note3: Forward current



Note4: Measured at center of LCD panel surface (including self-heat)

Note5: Measured at center of LCD module's rear shield surface (including self-heat)

Note6: No condensation

Note7: Water amount at Ta= 70°C and RH= 36%

#### 4.3 ELECTRICAL CHARACTERISTICS

## 4.3.1 LCD panel signal processing board

 $(Ta=25^{\circ}C)$ 

				ı	ı	,	(1a-25 C)
Parameter		Symbol	min.	typ.	max.	Unit	Remarks
Power supply voltage		VCC	3.0	3.3	3.6	V	at VCC= 3.3V
Tower supply voite	igc	VCC	4.75	5.0	5.25	V	at VCC= 5.0V
Power supply current		ICC	-	280 Note1	380 Note2	mA	at VCC= 3.3V
		icc	-	180 Note1	250 Note2	mA	at VCC= 5.0V
Logic input voltage for	High	VDH	0.7VCC	-	VCC	V	
display signals	Low	VDL	0	-	0.3VCC	V	CMOS level
Input voltage for DPS	High	VFH	0.7VCC	-	VCC	V	CIVIOS IEVEI
signal	Low	VFL	0	-	0.3VCC	V	

Note1: Checkered flag pattern [by EIAJ ED-2522]

Note2: Pattern for maximum current

# PRELIMINARY

# **NEC** NEC LCD Technologies, Ltd.

NL6448BC26-20F

# 4.3.2 Backlight

(Ta=25°C, Note1, Note2)

Parameter	Symbol	min.	typ.	max.	Unit	Remarks
Forward current	IL	-	25	27.5	mA	Note3
Forward Voltage	VL	-	29.7	34.2	V	at IL= 25 mA

Note1: Please drive with constant current.

Note2: The Luminance uniformity may be changed depending on the current variation between 4 circuits.

It is recommended that the current value difference between each circuit is less than 5%.

Note3: See "4.2 ABSOLUTE MAXIMUM RATINGS Note3".

# 4.3.3 Power supply voltage ripple

This product works, even if the ripple voltage levels are beyond the permissible values as following the table, but there might be noise on the display image.

Power supply voltage		Ripple voltage Note1 (Measure at input terminal of power supply)	Unit
VCC	3.3V	≤ 100	mVp-p
VCC	5.0V	≤ 100	mVp-p

Note1: The permissible ripple voltage includes spike noise.


#### 4.3.4 Fuse

Parameter		Fuse	Rating	Fusing current	Damada	
1 arameter	Туре	Supplier	Katilig	rusing current	Remarks	
VCC	ECC16202 A P	KAMAYA ELECTRIC	2.0A	4.0A	Note1	
VCC	VCC FCC16202AB CO., LTD		32V	4.0A	Note1	

Note1: The power supply capacity should be more than the fusing current. If it is less than the fusing current, the fuse may not blow in a short time, and then nasty smell, smoke and so on may occur.

#### 4.4 POWER SUPPLY VOLTAGE SEQUENCE


#### 4.4.1 LCD panel signal processing board



Note1: In terms of voltage variation (voltage drop) while VCC rising edge is below 3.0V in "VCC = 3.3V" or 4.75V in "VCC = 5.0V", a protection circuit may work, and then this product may not work.

Note2: Display signals (CLK, Hsync, Vsync, DE, DATA (R0 to R5, G0 to G5, B0 to B5)) and function signal (DPS) must be Low or High-impedance, exclude the VALID period (See above sequence diagram), in order to avoid that internal circuits is damaged. If some of display and function signals of this product are cut while this product is working, even if the signal input to it once again, it might not work normally. VCC should be cut when the display and function signals are stopped.

#### 4.4.2 Backlight lighting circuit



Note1: These are the display and function signals for LCD panel signal processing board.

Note2: The backlight should be turned on within the valid period of display and function signals, in order to avoid unstable data display.

#### 4.5 CONNECTIONS AND FUNCTIONS FOR INTERFACE PINS

## 4.5.1 LCD panel signal processing board

CN1 socket (LCD module side): DF9C-31P-1V (2\*) (Hirose Electric Co., Ltd. (HRS))

Adaptable plug: DF9-31S-1V (2\*), DF9-31S-1V (3\*) (Hirose Electric Co., Ltd. (HRS))

Pin No.	Symbol	Signal	Remarks
1	GND	Ground	Note1
2	CLK	Dot clock	
3	Hsync	Horizontal synchronous signal	-
4	Vsync	Vertical synchronous signal	]
5	GND	Ground	Note1
6	R0	Red data (LSB)	Least significant bit
7	R1	Red data	
8	R2	Red data	]
9	R3	Red data	<u>-</u>
10	R4	Red data	]
11	R5	Red data (MSB)	Most significant bit
12	GND	Ground	Note1
13	G0	Green data (LSB)	Least significant bit
14	G1	Green data	
15	G2	Green data	]
16	G3	Green data	- -
17	G4	Green data	]
18	G5	Green data (MSB)	Most significant bit
19	GND	Ground	Note1
20	В0	Blue data (LSB)	Least significant bit
21	B1	Blue data	
22	B2	Blue data	
23	В3	Blue data	_
24	B4	Blue data	
25	B5	Blue data (MSB)	Most significant bit
26	GND	Ground	Note1
27	DE	Selection of DE / Fixed mode	High or Open: Fixed mode Data enable signal: DE mode
28	VCC	Power supply	Note1
29	VCC	Power supply	110101
30	N.C.	-	Keep this pin Open.
31	DPS	Selection of scan direction	High: Reverse scan Low or Open: Normal scan Note2

Note1: All GND and VCC terminals should be used without any non-connected lines.


Note2: See "4.7 DISPLAY POSITIONS AND SCANNING DIRECTIONS ".

# 4.5.2 Backlight

CN2 plug (LCD module side): SM08B-SRSS-TB (J.S.T. Mfg. Co., Ltd.)
Adaptable socket: SHR-08V-S (J.S.T. Mfg. Co., Ltd.)

Pin No.	Symbol	Signal	Remarks
1	A1	Anode1	-
2	K1	Cathode1	-
3	A2	Anode2	-
4	K2	Cathode2	-
5	A3	Anode3	-
6	K3	Cathode3	-
7	A4	Anode4	-
8	K4	Cathode4	-

# 4.5.3 Positions of plug and socket



# 4.6 DISPLAY COLORS AND INPUT DATA SIGNALS

This product can display in equivalent to 262,144 colors in 64 gray scales. Also the relation between display colors and input data signals is as the following table.

Display	colors						Data	ata signal (0: Low level, 1: High level)											
Display	COIOIS	R 5	R4	R3	R 2	R 1	R0	G5	G4	G3	G2	G1	G0	B 5	B4	В3	B 2	B 1	B 0
	Black	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	Blue	0	0	0	0	0	0	0	0	0	0	0	0	1	1	1	1	1	1
ors	Red	1	1	1	1	1	1	0	0	0	0	0	0	0	0	0	0	0	0
Basic colors	Magenta	1	1	1	1	1	1	0	0	0	0	0	0	1	1	1	1	1	1
sic	Green	0	0	0	0	0	0	1	1	1	1	1	1	0	0	0	0	0	0
Bå	Cyan	0	0	0	0	0	0	1	1	1	1	1	1	1	1	1	1	1	1
	Yellow	1	1	1	1	1	1	1	1	1	1	1	1	0	0	0	0	0	0
	White	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
	Black	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
o.		0	0	0	0	0	1	0	0	0	0	0	0	0	0	0	0	0	0
scal	dark	0	0	0	0	1	0	0	0	0	0	0	0	0	0	0	0	0	0
Red gray scale	<b>↑</b>			:	:						:						:		
d gr	$\downarrow$			:							:						:		
Rec	bright	1	1	1	1	0	1	0	0	0	0	0	0	0	0	0	0	0	0
		1	1	1	1	1	0	0	0	0	0	0	0	0	0	0	0	0	0
	Red	1	1	1	1	1	1	0	0	0	0	0	0	0	0	0	0	0	0
	Black	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
ale		0	0	0	0	0	0	0	0	0	0	0	1	0	0	0	0	0	0
sc /	dark	0	0	0	0	0	0	0	0	0	0	1	0	0	0	0	0	0	0
Green gray scale	<b>↑</b>			:	:						:						:		
en	<b>↓</b>		0		:	0	0				:	0		0	0	0	:	0	0
Gre	bright	0	0	0	0	0	0	1	1	1	1	0	1	0	0	0	0	0	0
	Green	0	0	0	0	0	0	1	1	1	1	1	0	0	0	0	0	0	0
			0	0	0	0	0	1	1	1	1	0	1	0	0	0	0	0	0
	Black	0	0	0	0	0	0	0	0	0	0		0	0	0	0	0	0	0
ale	, ,	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	1
' SC	dark ↑	U	U	0	U	0	0	0	U	U	. 0	0	0	0	U	U	. 0	1	U
Blue gray scale	↑ ↓			:															
g en		0	0	0		Λ	Ω	0	0	0	. ^	Λ	Ω	1	1	1	. 1	Ω	1
Blì	bright	0	0	0	0	0	0	0	0	0	0	0	0	1	1	1	1	0	1
	Blue	0	0	0	0	0	0	0	0	0	0	0	0	1	1 1	1 1	1 1	1	1
	Diuc	U	U	U	U	U	U	U	U	U	U	U	U	1	1	1	1	1	1

#### 4.7 DISPLAY POSITIONS AND SCANNING DIRECTIONS

#### 4.7.1 Setting the LCD module in the landscape position (horizontal)

## (1) Display positions

The following table is the coordinates per pixel (See figure of "4.7.1 (2) Scanning directions".).

			\ 0	( )	- 0	
C( 0, 0)	C( 1, 0)	•••	C( X, 0)	•••	C(638, 0)	C(639, 0)
C( 0, 1)	C( 1, 1)	•••	C( X, 1)	•••	C(638, 1)	C(639, 1)
•	•	•	•	•	•	•
•	•	• • •	•	• • •	•	•••
•	•	•	•	•	•	•
C( 0, Y)	C( 1, Y)	•••	C( X, Y)	•••	C(638, Y)	C(639, Y)
•	•	•	•	•	•	•
•	•	• • •	•	• • •	•	•
•	•	•	•	•	•	•
C( 0, 478)	C( 1,478)	•••	C( X,478)	•••	C(638,478)	C(639,478)
C( 0,479)	C( 1,479)	•••	C( X,479)	•••	C(638,479)	C(639,479)

#### (2) Scanning directions

The following figures are seen from a front view. Also the arrow shows the direction of scan.




Figure 1. DPSH= Low or Open (Normal scan)
DPSV= High (Normal scan)




Figure 2. DPSH= High (Reverse scan) DPSV= High (Normal scan)




Figure 3. DPSH= Low or Open (Normal scan)
DPSV= Low or Open (Reverse scan)




Figure 4. DPSH= High (Reverse scan)
DPSV= Low or Open (Reverse scan)

Note1: Meaning of C (X, Y) and D (X, Y)

C (X, Y): The coordinates of the display position (See "**4.7.1** (1) **Display positions**".) D (X, Y): The data number of input signal for LCD panel signal processing board

#### 4.7.2 Setting the LCD module in the portrait position (vertical)

# (1) Display positions

The following table is the coordinates per pixel (See figure of "4.7.2 (2) Scanning directions".).

C(639, 0)	C(639, 1)	•••	C(639, Y)	•••	C(639,478)	C(639,479)
C(638, 0)	C(638, 1)	•••	C(638, Y)	•••	C(638,478)	C(638,479)
•	•	•	•	•	•	•
•	•	• • •	•	• • •	•	• • •
•	•	•	•	•	•	•
C( X, 0)	C( X, 1)	•••	C(X, Y)	•••	C( X,478)	C( X,479)
•	•	•	•	•	•	•
•	•	• • •	•	• • •	•	•
•	•	•	•	•	•	•
C( 1, 0)	C( 1, 1)	• • •	C( 1, Y)	•••	C( 1,478)	C( 1,479)
C( 0, 0)	C( 0, 1)	•••	C( 0, Y)	•••	C( 0, 478)	C( 0,479)

# (2) Scanning directions

The following figures are seen from a front view. Also the arrow shows the direction of scan.




Figure 1. DPSH= Low or Open (Normal scan)
DPSV= High (Normal scan)




Figure 2. DPSH= High (Reverse scan) DPSV= High (Normal scan)




Figure 3. DPSH= Low or Open (Normal scan)
DPSV= Low or Open (Reverse scan)




Figure 4. DPSH= High (Reverse scan)
DPSV= Low or Open (Reverse scan)

Note1: Meaning of C (X, Y) and D (X, Y)

C(X,Y): The coordinates of the display position (See "4.7.2 (1) **Display positions**".)

 $D\left( X,Y\right) :$  The data number of input signal for LCD panel signal processing board


# **NEC** NEC LCD Technologies, Ltd.

#### 4.8 INPUT SIGNAL TIMINGS

## 4.8.1 Outline of input signal timings


## • Horizontal signal

#### Note1



## • Vertical signal

# Note1



Note1: This diagram indicates virtual signal for set up to timing. Note2: Fixed mode cannot be used while working of DE mode.

Note3: See "4.8.3 Input signal timing chart" for numeration of pulse.

# 4.8.2 Timing characteristics

# (a) Fixed mode

(Note1)

Parameter			Symbol	min.	typ.	max.	Unit	Remarks
	Frequency		1/tc	21.0	25.175	29.0	MHz	39.72ns (typ.)
CLK	Dı	ıty	tcd	0.4	0.5	0.6	-	
	Rise time	, Fall time	terf	-	-	10	ns	-
DATA	CLK-DATA	Setup time	tds	3	-	ı	ns	
(R0-R5) (G0-G5)	CLK-DATA	Hold time	tdh	5	-	1	ns	-
(B0-B5)	Rise time	, Fall time	tdrf	1	-	10	ns	
	Cv	cle	th	30.0	31.778	33.6	μs	31.468kHz (typ.)
	Су	CIE	ui		800		CLK	
	Display	period	thd		640		CLK	
	Front	-porch	thf	16			CLK	-
Hsync	Pulse	width	thp	10	96	ı	CLK	
Tisync	Back-porch		thb	1	48	134	CLK	
	Total of pulse width and back-porch		thp + thb	144			CLK	Note2
	CLK- Hsync	Setup time	ths	3	-	ı	ns	
	CLK- Hsylic	Hold time	thh	5	-	1	ns	-
	Rise time	thrf	-	-	10	ns		
	Cv	cle	tv	16.1	16.683	17.2	ms	59.94Hz (typ.)
	Су	cie	tv	525			Н	
	Display	period	tvd	480			Н	
	Front	-porch	tvf		12		Н	-
Vsync	Pulse	width	tvp	1	2	1	Н	
V Sync	Back-	porch	tvb	1	31	32	Н	
	Total of pulse wid	th and back-porch	tvp + tvb		33		Н	Note2
	Hsync-Vsync	Setup time	tvhs	3	-	-	ns	
	115ylic- v Sylic	Hold time	tvhh	5	-	1	ns	-
	Rise time, Fall t		tvrf	-	-	10	ns	

Note1: Definition of parameters is as follows.

tc= 1CLK, tcd= tch/tc, th= 1H

Note2: Keep tvp + tvb and thp + thb within the table. If it is out of specification, display position will be shifted to right/left side or up/down.

# PRELIMINARY

# **NEC** NEC LCD Technologies, Ltd.

NL6448BC26-20F

# (b) DE mode

(Note1, Note2, Note3)

Parameter			Symbol	min.	typ.	max.	Unit	Remarks
	Fre	1/tc	21.0	25.175	29.0	MHz	39.72ns (typ.)	
CLK	]	Duty	tcd	0.4	0.5	0.6	-	
	Rise tin	ne, Fall time	terf	-	-	10	ns	-
DATA	CLUDATA	Setup time	tds	3	-	-	ns	
(R0-R5) (G0-G5)	CLK-DATA	Hold time	tdh	5	-	-	ns	-
(B0-B5)	Rise tim	ne, Fall time	tdrf	-	-	10	ns	
		Cycle	th	30.0	31.778	33.6	μs	31.468kHz (typ.)
	Horizontal	Сусіе	tii	-	800	-	CLK	
		Display period	thd		640		CLK	-
		G 1	4	16.1	16.683	17.2	ms	59.94Hz (typ.)
DE	Vertical (One frame)	Cycle	tv	-	525	-	Н	
		Display period	tvd		480		Н	
	CLK-DE	Setup time	tdes	3	-	-	ns	-
	CLK-DE	Hold time	tdeh	5	-	-	ns	
	Rise tim	ne, Fall time	tderf	-	-	10	ns	

Note1: Definition of parameters is as follows.


tc= 1CLK, tcd= tch/tc, th= 1H

Note2: Hsync signal (CN1-Pin No.3) and Vsync signal (CN1-Pin No.4) are not used inside the product at DE mode, but do not keep these pins open to avoid noise problem.

Note3: Vertical cycle (tv) should be specified in integral multiple of Horizontal cycle (th).


# 4.8.3 Input signal timing chart

# (a) Fixed mode





# (b) DE mode


# Horizontal timing



# (c) Common item of Fixed mode and DE mode







#### 4.9 OPTICS

# 4.9.1 Optical characteristics

(Note1, Note2)


Paramete	r	Condition	Symbol	min.	typ.	max.	Unit	Measuring instrument	Remarks	
Luminano	ce	White at center $\theta R = 0^{\circ}$ , $\theta L = 0^{\circ}$ , $\theta U = 0^{\circ}$ , $\theta D = 0^{\circ}$	L	TBD	800	-	cd/m <sup>2</sup>	BM-5A	-	
Contrast ra	tio	White/Black at center $\theta R = 0^{\circ}$ , $\theta L = 0^{\circ}$ , $\theta U = 0^{\circ}$ , $\theta D = 0^{\circ}$	CR	600	1,000	1	ı	BM-5A	Note3	
Luminance unit	formity	White $\theta R = 0^{\circ}$ , $\theta L = 0^{\circ}$ , $\theta U = 0^{\circ}$ , $\theta D = 0^{\circ}$	LU	-	1.25	1.4	-	BM-5A	Note4	
	White	x coordinate	Wx	0.263	0.313	0.363	-			
	Wille	y coordinate	Wy	0.279	0.329	0.379	-			
	Red	x coordinate	Rx	-	TBD	-	-			
Chromaticity	Keu	y coordinate	Ry	-	TBD	-	-			
Cinomaticity	Green	x coordinate	Gx	-	TBD	-	-	SR-3	Note5	
	Green	y coordinate	Gy	-	TBD	-	-	3K-3	Notes	
	Blue	x coordinate	Bx	-	TBD	-	-			
	Blue	y coordinate	By	-	TBD	-	-			
Color gam	ut	$\theta$ R= 0°, $\theta$ L= 0°, $\theta$ U= 0°, $\theta$ D= 0° at center, against NTSC color space	C	35	40	1	%			
Dosponso ti	ma	White to Black	Ton	-	3	5	ms	BM-5A	Note6	
Response ti	ille	Black to White	Toff	-	15	21	ms	DIVI-JA	Note7	
	Right	θU= 0°, θD= 0°, CR≥ 10	θR	70	80	-	0			
Wiin 1	Left	θU= 0°, θD= 0°, CR≥ 10	θL	70	80	-	0	EZ	N-4-0	
Viewing angle	Up	$\theta R = 0^{\circ}, \ \theta L = 0^{\circ}, \ CR \ge 10$	θU	70	80	-	0	Contrast	Note8	
	Down	$\theta R = 0^{\circ},  \theta L = 0^{\circ},  CR \ge 10$	θD	70	80	-	0			


Note1: These are initial characteristics.

Note2: Measurement conditions are as follows.

Ta= 25°C, VCC= 3.3V, IL= 25mA, Display mode: VGA, Horizontal cycle= 1/31.468kHz, Vertical cycle= 1/59.94Hz, DPS= Low or Open: Normal scan

Optical characteristics are measured at luminance saturation after 20minutes from working the product, in the dark room. Also measurement methods are as follows.





Note3: See "4.9.2 Definition of contrast ratio".

Note4: See "4.9.3 Definition of luminance uniformity".

Note5: These coordinates are found on CIE 1931 chromaticity diagram.

Note6: Product surface temperature: TopF= TBD°C

Note7: See "4.9.4 Definition of response times".

Note8: See "4.9.5 Definition of viewing angles".

#### 4.9.2 Definition of contrast ratio


The contrast ratio is calculated by using the following formula.

#### 4.9.3 Definition of luminance uniformity

The luminance uniformity is calculated by using following formula.


$$Luminance \ uniformity \ (LU) = \ \frac{Maximum \ luminance \ from \ \textcircled{1} \ to \ \textcircled{5}}{Minimum \ luminance \ from \ \textcircled{1} \ to \ \textcircled{5}}$$

The luminance is measured at near the 5 points shown below.




#### 4.9.4 Definition of response times

Response time is measured, the luminance changes from "white" to "black", or "black" to "white" on the same screen point, by photo-detector. Ton is the time it takes the luminance change from 90% down to 10%. Also Toff is the time it takes the luminance change from 10% up to 90% (See the following diagram.).



#### 4.9.5 Definition of viewing angles




#### **5. RELIABILITY TESTS**

Test item	Condition	Judgment		
High temperature and humidity (Operation)	<ul> <li>① 60 ± 2°C, RH= 90%, 240hours</li> <li>② Display data is black.</li> </ul>			
High temperature (Operation)	<ul> <li>① 70 ± 3°C, 240hours</li> <li>② Display data is black.</li> </ul>			
Heat cycle (Operation)	① -20 ± 3°C1hour 70 ± 3°C1hour ② 50cycles, 4 hours/cycle ③ Display data is black.			
Thermal shock (Non operation)	<ul> <li>30 ± 3°C30minutes 80 ± 3°C30minutes</li> <li>100cycles, 1hour/cycle</li> <li>Temperature transition time is within 5 minutes.</li> </ul>	No display malfunctions Note1		
ESD (Operation)	<ol> <li>150pF, 150Ω, ±10kV</li> <li>9 places on a panel surface Note2</li> <li>10 times each places at 1 sec interval</li> </ol>			
Dust (Operation)	<ol> <li>Sample dust: No. 15 (by JIS-Z8901))</li> <li>15 seconds stir</li> <li>8 times repeat at 1 hour interval</li> </ol>			
Vibration (Non operation)	<ol> <li>5 to 100Hz, 19.6m/s²</li> <li>1 minute/cycle</li> <li>X, Y, Z directions</li> <li>120 times each directions</li> </ol>	No display malfunctions No physical damages		
Mechanical shock (Non operation)	<ul> <li>539m/ s², 11ms</li> <li>±X, ±Y, ±Z directions</li> <li>5 times each directions</li> </ul>	Note1		

Note1: Display and appearance are checked under environmental conditions equivalent to the inspection conditions of defect criteria.

Note2: See the following figure for discharge points.



#### 6. PRECAUTIONS

#### 6.1 MEANING OF CAUTION SIGNS

The following caution signs have very important meaning. Be sure to read "6.2 CAUTIONS" and "6.3 ATTENTIONS", after understanding these contents!



This sign has the meaning that customer will be injured by himself or the product will sustain a damage, if customer has wrong operations.



This sign has the meaning that customer will be injured by himself, if customer has wrong operations.

#### 6.2 CAUTIONS



- \* Do not touch the working backlight. There is a danger of burn injury.
- \* Do not shock and press the LCD panel and the backlight! There is a danger of breaking, because they are made of glass. (Shock: To be not greater 539m/s² and to be not greater 11ms, Pressure: To be not greater 19.6N (\$\phi\$16mm jig))

# 6.3 ATTENTIONS



#### 6.3.1 Handling of the product

- ① Take hold of both ends without touching the circuit board when the product (LCD module) is picked up from inner packing box to avoid broken down or misadjustment, because of stress to mounting parts on the circuit board.
- ② Do not hook nor pull cables such as lamp cable, and so on, in order to avoid any damage.
- 3 When the product is put on the table temporarily, display surface must be placed downward.
- 4 When handling the product, take the measures of electrostatic discharge with such as earth band, ionic shower and so on, because the product may be damaged by electrostatic.
- ⑤ The torque for product mounting screws must never exceed 0.294N·m. Higher torque might result in distortion of the bezel.
- The product must be installed using mounting holes without undue stress such as bends or twist (See outline drawings). And do not add undue stress to any portion (such as bezel flat area). Bends or twist described above and undue stress to any portion may cause display mura.
- ① Do not press or rub on the sensitive product surface. When cleaning the product surface, use of the cloth with ethanolic liquid such as screen cleaner for LCD is recommended.
- On not push nor pull the interface connectors while the product is working.
- When handling the product, use of an original protection sheet on the product surface (polarizer) is recommended for protection of product surface. Adhesive type protection sheet may change color or characteristics of the polarizer.
- Usually liquid crystals don't leak through the breakage of glasses because of the surface tension of thin layer and the construction of LCD panel. But, if you contact with liquid crystal for the worst, please wash it out with soap.

# PRELIMINARY

# **NEC** NEC LCD Technologies, Ltd.

NL6448BC26-20F

#### 6.3.2 Environment

- ① Do not operate or store in high temperature, high humidity, dewdrop atmosphere or corrosive gases. Keep the product in packing box with antistatic pouch in room temperature to avoid dusts and sunlight, when storing the product.
- ② In order to prevent dew condensation occurring by temperature difference, the product packing box should be opened after enough time being left under the environment of an unpacking room. Evaluate the leaving time sufficiently because a situation of dew condensation occurring is changed by the environmental temperature and humidity. (Recommended leaving time: 6 hours or more with packing state)
- 3 Do not operate in high magnetic field. Circuit boards may be broken down by it.
- 4 This product is not designed as radiation hardened.

#### 6.3.3 Characteristics

#### The following items are neither defects nor failures.


- ① Characteristics of the LCD (such as response time, luminance, color uniformity and so on) may be changed depending on ambient temperature. If the product is stored under condition of low temperature for a long time, it may cause display mura. In this case, the product should be operated after enough time being left under condition of operating temperature.
- ② Display mura, flicker, vertical seam or small spot may be observed depending on display patterns.
- 3 Do not display the fixed pattern for a long time because it may cause image sticking. Use a screen saver, if the fixed pattern is displayed on the screen.
- 4 The display color may be changed depending on viewing angle because of the use of condenser sheet in the backlight.
- ⑤ Optical characteristics may be changed depending on input signal timings.
- The interference noise between input signal frequency for this product's signal processing board and luminance control frequency of backlight driving circuit may appear on a display. Set up luminance control frequency of backlight driving circuit so that the interference noise does not appear.

#### 6.3.4 Other

- ① All GND and VCC terminals should be used without any non-connected lines.
- ② Do not disassemble a product or adjust variable resistors.
- ③ See "REPLACEMENT MANUAL FOR LAMP HOLDER SET", when replacing LED backlight.
- 4 Pay attention not to insert foreign materials inside of the product, when using tapping screws.
- ⑤ Pack the product with original shipping package, in order to avoid any damages during transportation, when returning the product to NEC for repair and so on.

## 7. OUTLINE DRAWINGS

# 7.1 FRONT VIEW




Note1: The values in parentheses are for reference.

Note2: The torque for product mounting screws must never exceed 0.294N·m.

Note3: Mounting hole portions (4 pieces)

Unit: mm

# 7.2 REAR VIEW



Note1: The values in parentheses are for reference.

Note2: The torque for product mounting screws must never exceed 0.294N·m. Note3: Mounting hole portions (4 pieces)

Unit: mm

29



# **REVISION HISTORY**

The inside of latest specifications is revised to the clerical error and the major improvement of previous edition. Only a changed part such as functions, characteristic value and so on that may affect a design of customers, are described especially below.

Edition	Document number	Prepared date	Revision contents and signature				
1st edition	DOD-PP- 0565	June 13, 2008	Revision contents  New issue  Signature of writer				
			Approved by	Checked by	Prepared by		
			T. Ogawa		A. Kumano		
			T. OGAWA	·	A. KUMANO		