

**Pb-free  
HEAT**



# MU03 Series

Single Color / Light Bar Module

## Features

Light emitting surface (Outer size)	6 x 9 mm (7 x 10 mm) (L x W)
Product features	<ul style="list-style-type: none"> <li>• Single Color (Green, Yellow Green, Orange or Red)</li> <li>• Lead-free soldering compatible</li> <li>• RoHS compliant</li> </ul>
Peak wavelength	Green : 555 nm (5201,5205) : 560 nm (5202) Yellow Green : 570 nm (4201,4205) Orange : 605 nm (3201,3205) Red : 660 nm (2201,2205)
Die materials	Green, Yellow Green : GaP Orange : GaAsP Red : GaAlAs
Soldering methods	TTW (Through The Wave) soldering and manual soldering
Soldering methods	More than 2kV(HBM)
Packing	Plastic bag

## Recommended Applications

Electric Household Appliances, OA/FA, Other General Applications

## Color and Luminous Intensity

Part No.	Material	Emitted Color	Resin Color	Intensity <sup>※1</sup> I <sub>v</sub> (mcd)			Number of Chips
				MIN.	TYP.	I <sub>F</sub>	
MU03-5201	GaP	Green	Green	3	7	20	2
MU03-5205	GaP		Milky White	5	10	20	2
MU03-5202	GaP		Green	8	16	20	2
MU03-4201	GaP	Yellow Green	Yellow	10	20	20	2
MU03-4205	GaP		Milky White	10	20	20	2
MU03-3201	GaAsP	Orange	Orange	5	10	20	2
MU03-3205	GaAsP		Milky White	5	10	20	2
MU03-2201	GaAlAs	Red	Red	10	20	20	2
MU03-2205	GaAlAs		Milky White	10	20	20	2

※1 Luminous Intensity : 2 chips

## Absolute Maximum Ratings

(Ta=25°C)

Item	Symbol	Absolute Maximum Ratings										Unit
		5201	5205	5202	4201	4205	3201	3205	2201	2205		
Power Dissipation <sup>※2</sup>	P <sub>d</sub>	125	125	150	150	150	125	125	120	120	mW	
Forward Current	I <sub>F</sub>	25	25	30	30	30	25	25	30	30	mA	
Pulse Forward Current <sup>※3</sup>	I <sub>FRM</sub>	60	60	60	60	60	60	60	60	60	mA	
Derating (Ta=25°C or higher)	ΔI <sub>F</sub>	0.33	0.33	0.40	0.40	0.40	0.33	0.33	0.40	0.40	mA/°C	
	ΔI <sub>FRM</sub>	0.80	0.80	0.80	0.80	0.80	0.80	0.80	0.80	0.80	mA/°C	
Reverse Voltage	V <sub>R</sub>	4	4	4	4	4	4	4	4	4	V	
Operating Temperature	T <sub>opr</sub>	-40~+85										°C
Storage Temperature	T <sub>stg</sub>	-40~+85										°C

※2 Power Dissipation : 2chips, The other Items : 1 chip

※3 I<sub>FRM</sub> Measurement condition : Pulse Width ≤ 2ms, Duty ≤ 1/5





## Electro-Optical Characteristics

(Ta=25°C)





Item	Conditions	Symbol		Characteristics										Unit
				5201	5205	5202	4201	4205	3201	3205	2201	2205		
Forward Voltage	I <sub>F</sub> =20mA	V <sub>F</sub>	TYP.	2.2	2.2	2.1	2.1	2.1	2.2	2.2	1.7	1.7	V	
			MAX.	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.0		2.0
Reverse Current	V <sub>R</sub> =4V	I <sub>R</sub>	MAX.	100	100	100	100	100	100	100	100	100	μA	
Peak Wavelength	I <sub>F</sub> =20mA	λ <sub>p</sub>	TYP.	555	555	560	570	570	605	605	660	660	nm	
Spectral Line Half Width	I <sub>F</sub> =20mA	Δλ	TYP.	30	30	30	30	30	30	30	30	30	nm	

※ The above Items : 1 chip





## Technical Data(5201/5205)







## Technical Data(5201/5205)



## Technical Data(5202)







## Technical Data(5202)









## Technical Data(4201/4205)







## Technical Data(4201/4205)













## Technical Data(3201/3205)







## Technical Data(3201/3205)



## Technical Data(2201/2205)




## Technical Data(2201/2205)



## Package Dimensions

(Unit: mm)

(Tolerance :  $\pm 0.25$  mm)



● ※ mark : The measure of lead root

## TTW (Through The Wave) soldering Conditions

---

Pre-heating	100 °C 60 s	(MAX.) Resin surface temperature (MAX.)
Solder Bath Temp.	265 °C	(MAX.)
Dipping Time	5 s	(MAX.)
Position	At least 2.0 mm away from the root of lead	

- 1) The dip soldering process shall be 2 times maximum.
- 2) The product shall be cooled to normal temperature before the second dipping process.

## Manual Soldering Conditions

---

Iron tip temp.	400 °C	(MAX.) (30 W Max.)
Soldering time and frequency	3 s 2 times	(MAX.) (MAX.)
Position	At least 2.0 mm away from the root of lead	



## Reliability Testing Result

Reliability Testing Result	Applicable Standard	Testing Conditions	Duration	Failure
Room Temp. Operating Life	EAJED-4701/100(101)	Ta = 25°C, If = Maximum Rated Current	1,000 h	0/10
Resistance to Soldering Heat	EAJED-4701/300(302)	260±5°C, 3mm from package base	10s	0/10
Temperature Cycling	EAJED-4701/100(105)	Minimum Rated Storage Temperature(30min) ~Normal Temperature(15min) ~Maximum Rated Storage Temperature(30min) ~Normal Temperature(15min)	5 cycles	0/10
Wet High Temp. Storage Life	EAJED-4701/100(103)	Ta = 60±2°C, RH = 90±5%	1,000 h	0/10
High Temp. Storage Life	EAJED-4701/200(201)	Ta = Maximum Rated Storage Temperature	1,000 h	0/10
Low Temp. Storage Life	EAJED-4701/200(202)	Ta = Minimum Rated Storage Temperature	1,000 h	0/10
Lead Tension	EAJED-4701/400(401)	5N, 1time	10s	0/10
Vibration, Variable Frequency	EAJED-4701/400(403)	98.1m/s <sup>2</sup> (10G), 100 ~ 2KHz sweep for 20min., XYZ each direction	2 h	0/10
Lead Bend	EAJED-4701/400(401)	2.5N, 0°←→ 90°	Twice	0/10
Shock	JSC 7201 A-8	It falls on wood engraving from height of 75cm.	3 times	0/10

## Failure Criteria

Items	Symbols	Conditions	Failure criteria
Luminous Intensity	Iv	If=20mA	Testing Min. Value < Spec. Min. Value x 0.5
Forward Voltage	V <sub>F</sub>	If=20mA	Testing Max. Value ≥ Spec. Max. Value x 1.2
Reverse Current	I <sub>R</sub>	V <sub>R</sub> =4V	Testing Max. Value ≥ Spec. Max. Value x 2.5
Cosmetic Appearance	-	-	Occurrence of notable decoloration, deformation and cracking

## Special Notice to Customers Using the Products and Technical Information Shown in This Data Sheet

- 1) The technical information shown in the data sheets are limited to the typical characteristics and circuit examples of the referenced products. It does not constitute the warranting of industrial property nor the granting of any license.
  
- 2) For the purpose of product improvement, the specifications, characteristics and technical data described in the data sheets are subject to change without prior notice. Therefore it is recommended that the most updated specifications be used in your design.
  
- 3) When using the products described in the data sheets, please adhere to the maximum ratings for operating voltage, heat dissipation characteristics, and other precautions for use. We are not responsible for any damage which may occur if these specifications are exceeded.
  
- 4) The products that have been described to this catalog are manufactured so that they will be used for the electrical instrument of the benchmark (OA equipment, telecommunications equipment, AV machine, home appliance and measuring instrument).  
The application of aircrafts, space borne application, transportation equipment, medical equipment and nuclear power control equipment, etc. needs a high reliability and safety, and the breakdown and the operation might influence the life or the human body. Please consult us beforehand if you plan to use our product for the usages of aircrafts, space borne application, transportation equipment, medical equipment and nuclear power control equipment, etc. except OA equipment, telecommunications equipment, AV machine, home appliance and measuring instrument.
  
- 5) In order to export the products or technologies described in this data sheet which are under the "Foreign Exchange and Foreign Trade Control Law," it is necessary to first obtain an export permit from the Japanese government.
  
- 6) No part of this data sheet may be reprinted or reproduced without prior written permission from Stanley Electric Co., Ltd.
  
- 7) The most updated edition of this data sheet can be obtained from the address below:  
<http://www.stanley-components.com>