
Datasheet




MODEL NAME	ССТ	CODE
	3000K	SL-Z7V3280L9WW
RM12_ZP	4000K	SL-Z7T3280L9WW
	5000K	SL-Z7R3280L9WW

SAMSUNG ELECTRONICS CO., LTD. 1, Samsung-ro, Giheung-gu, Yongin-si, Gyeonggi-do 17113, KOREA

Version	Remark	Page	Date	Traced
1.0	The Preliminary Specification established.	ALL	20.04.28	I.S.LEE
2.0	3000K Model Specification Updated	ALL	20.11.12	I.S.LEE
3.0	Packing Specification Updated	9	20.12.08	I.S.LEE
4.0	Packaging Information Errors Corrected	9	22.3.24	S.A.JOO

LED Module

RM12_ZP



LH502C Module



Table of Contents

1.	Product Code Information	 1
2.	Characteristics	 2
3.	Appearance and Structure	 5
4.	Certification and Declaration	 6
5.	Label Structure	 7
6.	Packing Structure	 ç
7.	Precautions in Handling & Use	 1(
	Appendix	 11

1. Product Code Information

- RM12_ZP with LH502C

CRI	ССТ	Product Code
	3000K	SL-Z7V3280L9WW
CRI 70	4000K	SL-Z7T3280L9WW
	5000K	SL-Z7R3280L9WW

2. Characteristics (I_F = 1050mA , t_p = 60°C)

a) Basic Information

Item	Unit	Rating	Remark
Rated Lifetime	Hour	>50,000	L70B50
Ingress Protection (IP)	-	no rating	
Ambient / Operating Temperature (ta)	°C	-30 ~ +50	
Storage Temperature	°C	-30 ~ +80	

Notes

- ※ I_F: Forward current or Operating current
- ** t_p : temperature at which performance is specified measured at "Tc point".
- * t_a : ambient temperature

b) Electro-Optical Characteristics

Item		Unit	R Unit			Remark
itan	non-		min	typ	max	Remain
	3000K		5,400	6,050		
Luminous Flux	4000K	lm	5,750	6,420	-	
	5000K		5,750	6,330	-	If = 1,050 mA
	3000K		-	162.2	-	Tp = 60 °C
Luminous Efficacy	4000K	lm/W	-	172.2	-	
	5000K		-	169.8	-	
	3000K		MacAdam 5 Step			
ССТ	4000K	K				Initial CCT Integrating Sphere
	5000K			MacAdam 7 Step		
Operating \	/oltage	V	32.6	35.5	38.5	
Power Cons	umption	W	-	37.3	-	
Color Rendering	Index (Ra)	-	70	-		
Operating 0	Current	mA		1,050	1,600	

Notes:

- 1) *tp*: temperature at which performance is specified; measured at "T_C point"
- 2) Samsung maintains a measurement tolerance of
- : Luminous flux $\pm 7\%$, Ra ± 3.0 , Voltage $\pm 5\%$, Current = $\pm 5\%$, CCT = $\pm 5\%$, CIE = ± 0.005 .

c) Light Distribution

Item	Unit	Nominal	Tolerance	Remark
Beam Angle (FWHM)	°(degree)	120	±5	

d) Temperature Characteristics

Item	Unit	Nominal* (t_p)	Life**(t∠)	Max***(t _c)
Temperature Case (Tc)	℃	60	100	105

Notes:


- * Temperature used to specify performance of the module (t_p) .
- ** Rated maximum performance temperature at which lifetime is specified in L70B50 (t_L).
- Rated maximum temperature, highest permissible temperature to avoid safety risk (t_c).

All temperatures are measured at the designated "Tc point" as indicated on the module.

Please use heat-sink(or heat dissipation solution) with proper thermal capacity(operating wattage).


f) Thermal Measurement

Performance temperatures are measured on "Tc point" as indicated on the module.



3. Appearance and Structure

a) Appearance and Dimension





Item	Unit	Dimension	Tolerance
Module Size	mm	146.6 x 45.0	± 0.3
Module Height	mm	6.0	± 0.3
Module Weight	g	40.8	± 0.5

b) Structure

Item	Specification
LED	LH502C
Connector	WAGO 2060-452
TVS DIODE	SMAJ100A
РСВ	MCPCB 1.65T, 1oz, 2Px6S


4. Certification and Declaration

Item	Compliant to	Remark
Test & Certification	UL 8750	E344519
Declaration	RoHS	Hazardous Substance & Material

5. Label Structure

a) Module Label

- 10mm x 5.5mm



Number	Item	Remark
1	Samsung Product Code	Refer to page 1
2	SMT Date	YMDD
3	SMT Line No	1~E
4	Serial No	00001~99999
(5)	ССТ	4000K
6	LED Maker	-S(Samsung)
7	Group No	-

b) Tray Label


- 100mm x 50mm



Number	ltem	Remark
1	Model Code	Refer to page 1
2	LOT ID	
3	Quantity	240
4	Production Date (year & week)	
5	Country of Origin	KOREA
6	Production Date (year / month / date)	-

c) Box Labels

- 100mm x 50mm



Number	ltem	Remark
1	Model Number (Product Code) Refer to page 1	
2	Lot No.	
3	Packing Quantity	240
4	Production Date (year & week)	-
5	UL Cert. (Environment Location)	Damp
6	UL Cert. (Electrical Ratings)	38.5Vdc , 1.6A
7	Country of Origin	KOREA
8	Production Date (year / month / date)	-

6. Packing Structure

Product	Packing	Quantity (ea)	Weight (kg)	Remark
RM12_ZP	Tray	60	Weight (includes Modules, Trays a	Weight
	Вох	240		(includes Modules, Trays and a Box)
	Pallet	5,760		(excludes Pallet)

7. Precautions in Handling & Use

- 1) This LED Module should not be used in any type of fluid such as water, oil, organic solvent, etc. When washing is required, IPA is recommended to use. When using other solvents it should be confirmed beforehand whether the solvents may react with the Module material. The banned Freon solvents should not be used. Do not clean using ultrasonic cleaner.
- 2) The LEDs are sensitive to the static electricity and surge. It is recommended to use a wrist band or anti-electrostatic glove when handling the LED Modules. If voltage exceeding the absolute maximum rating is applied to LEDs, it may cause damage or even destruction to LED devices. Damaged LEDs may show some unusual characteristics such as increase in leak current, lowered turn-on voltage, or abnormal lighting of LEDs at low current.
- 3) VOCs (Volatile Organic Compounds) can be generated from adhesives, flux, hardener or organic additives used in luminaires (fixtures). Transparent LED silicone encapsulant is permeable to those chemicals and they may lead a discoloration of encapsulant when they exposed to heat or light. This phenomenon can cause a significant loss of light emitted (output) from the luminaires (fixtures). In order to prevent these problems, we recommend users to know the physical properties of the materials used in luminaires, and they must be selected carefully.
- 4) Risk of sulfurization (or tarnishing)
 - The LED uses a silver-plated lead frame and its surface color may change to black (or dark colored) when it is exposed to sulfur (S), chlorine (CI) or other halogen compound. Sulfurization of lead frame may cause intensity degradation, change of chromaticity coordinates and, in extreme cases, open circuit. It requires caution. Due to possible sulfurization of lead frame, the LED Modules should not be used and stored together with oxidizing substances made of materials such as rubber, plain paper, lead solder cream, etc.
- 5) The resin area is very sensitive, please do not handle, press, touch or rub it.
- 6) Do not drop the Module or give shocks.
- 7) Do not store the Module in a dusty place or humid location.
- 8) Do not disassemble the Module.
- 9) Do not directly look into the lighted LED with naked eyes for a long period of time.
- 10) Please consider the creepage and clearance distance at the end product.

Appendixl. Forward Current Characteristics

Item	Unit	Forward Current	сст	typ. Rating
Luminous Flux	lm 	350mA	3000K	2,100
			4000K	2,330
			5000K	2,295
		700mA	3000K	4,150
			4000K	4,430
			5000K	4,430
		1400mA	3000K	7,500
			4000K	8,100
			5000K	8,100
		350mA	3000K	33.0
	 V		4000K	
			5000K	
		700mA	3000K	34.3
Operating Voltage			4000K	
			5000K	
		 1400mA 	3000K	36.6
			4000K	
			5000K	
Luminous Efficacy	lm/W	350mA	3000K	184.8
			4000K	199.0
			5000K	199.0
		700mA	3000K	171.2
			4000K	184.3
			5000K	184.3
			3000K	146.5
		1400mA	4000K	157.8

Legal and additional information.

About Samsung Electronics Co., Ltd.

Samsung inspires the world and shapes the future with transformative ideas and technologies. The company is redefining the worlds of TVs, smartphones, wearable devices, tablets, digital appliances, network systems, and semiconductor and LED solutions. For the latest news, please visit the Samsung Newsroom at news.samsung.com

Copyright © 2020 Samsung Electronics Co., Ltd. All rights reserved. Samsung Electronics reserves the right to modify, at its sole discretion, the design, packaging, specifications, and features shown herein without notice at any time.

Samsung Electronics Co., Ltd. 1, Samsung-ro, Giheung-gu, Yongin-si, Gyeonggi-do, 17113 KOREA www.samsung.com/led/