

Notice for TAIYO YUDEN Products

Please read this notice before using the TAIYO YUDEN products.



REMINDERS

■ Product Information in this Catalog

Product information in this catalog is as of October 2021. All of the contents specified herein and production status of the products listed in this catalog are subject to change without notice due to technical improvement of our products, etc. Therefore, please check for the latest information carefully before practical application or use of our products.

Please note that TAIYO YUDEN shall not be in any way responsible for any damages and defects in products or equipment incorporating our products, which are caused under the conditions other than those specified in this catalog or individual product specification sheets.

■ Approval of Product Specifications

Please contact TAIYO YUDEN for further details of product specifications as the individual product specification sheets are available. When using our products, please be sure to approve our product specifications or make a written agreement on the product specification with TAIYO YUDEN in advance.

■ Pre-Evaluation in the Actual Equipment and Conditions

Please conduct validation and verification of our products in actual conditions of mounting and operating environment before using our products.

■ Safety Design

When using our products for high safety and/or reliability-required equipment or circuits, please fully perform safety and/or reliability evaluation. In addition, please install (i) systems equipped with a protection circuit and a protection device and/or (ii) systems equipped with a redundant circuit or other system to prevent an unsafe status in the event of a single fault for a failsafe design to ensure safety.

■ Intellectual Property Rights

Information contained in this catalog is intended to convey examples of typical performances and/or applications of our products and is not intended to make any warranty with respect to the intellectual property rights or any other related rights of TAIYO YUDEN or any third parties nor grant any license under such rights.

■ Limited Warranty

Please note that the scope of warranty for our products is limited to the delivered our products themselves conforming to the product specifications specified in the individual product specification sheets, and TAIYO YUDEN shall not be in any way responsible for any damages resulting from a failure or defect in our products. Notwithstanding the foregoing, if there is a written agreement (e.g., supply and purchase agreement, quality assurance agreement) signed by TAIYO YUDEN and your company, TAIYO YUDEN will warrant our products in accordance with such agreement, provided, however, that our products shall be used for general-purpose and standard use in the equipment specified in this catalog or the individual product specification sheets.

■ TAIYO YUDEN's Official Sales Channel

The contents of this catalog are applicable to our products which are purchased from our sales offices or authorized distributors (hereinafter "TAIYO YUDEN's official sales channel"). Please note that the contents of this catalog are not applicable to our products purchased from any seller other than TAIYO YUDEN's official sales channel.

■ Caution for Export

Some of our products listed in this catalog may require specific procedures for export according to "U.S. Export Administration Regulations", "Foreign Exchange and Foreign Trade Control Law" of Japan, and other applicable regulations. Should you have any questions on this matter, please contact our sales staff.

■ Limited Application

1. Equipment Intended for Use

The products listed in this catalog are intended for general-purpose and standard use in general electronic equipment for consumer (e.g., AV equipment, OA equipment, home electric appliances, office equipment, information and communication equipment including, without limitation, mobile phone, and PC) and other equipment specified in this catalog or the individual product specification sheets, or the equipment approved separately by TAIYO YUDEN.

TAIYO YUDEN has the product series intended for use in the following equipment. Therefore, when using our products for these equipment, please check available applications specified in this catalog or the individual product specification sheets and use the corresponding products.

Application	Product Series		Quality Grade ^{*3}
	Equipment ^{*1}	Category (Part Number Code ^{*2})	
Automotive	Automotive Electronic Equipment (POWERTRAIN, SAFETY)	A	1
	Automotive Electronic Equipment (BODY & CHASSIS, INFOTAINMENT)	C	2
Industrial	Telecommunications Infrastructure and Industrial Equipment	B	2
Medical	Medical Devices classified as GHTF Class C (Japan Class III)	M	2
	Medical Devices classified as GHTF Classes A or B (Japan Classes I or II)	L	3
Consumer	General Electronic Equipment	S	3

*Notes: 1. Based on the general specifications required for electronic components for such equipment, which are recognized by TAIYO YUDEN, the use of each product series for the equipment is recommended. Please be sure to contact TAIYO YUDEN before using our products for equipment other than those covered by the product series.

2. On each of our part number, the 2nd code from the left is a code indicating the "Category" as shown in the above table. For details, please check the explanatory materials regarding the part numbering system of each of our products.

3. Each product series is assigned a "Quality Grade" from 1 to 3 in order of higher quality. Please do not incorporate a product into any equipment with a higher Quality Grade than the Quality Grade of such product without the prior written consent of TAIYO YUDEN.

2. Equipment Requiring Inquiry

Please be sure to contact TAIYO YUDEN for further information before using the products listed in this catalog for the following equipment (excluding intended equipment as specified in this catalog or the individual product specification sheets) which may cause loss of human life, bodily injury, serious property damage and/or serious public impact due to a failure or defect of the products and/or malfunction attributed thereto.

- (1) Transportation equipment (automotive powertrain control system, train control system, and ship control system, etc.)
- (2) Traffic signal equipment
- (3) Disaster prevention equipment, crime prevention equipment
- (4) Medical devices classified as GHTF Class C (Japan Class III)
- (5) Highly public information network equipment, data-processing equipment (telephone exchange, and base station, etc.)
- (6) Any other equipment requiring high levels of quality and/or reliability equal to the equipment listed above

3. Equipment Prohibited for Use

Please do not incorporate our products into the following equipment requiring extremely high levels of safety and/or reliability.

- (1) Aerospace equipment (artificial satellite, rocket, etc.)
- (2) Aviation equipment ^{*1}
- (3) Medical devices classified as GHTF Class D (Japan Class IV), implantable medical devices ^{*2}
- (4) Power generation control equipment (nuclear power, hydroelectric power, thermal power plant control system, etc.)
- (5) Undersea equipment (submarine repeating equipment, etc.)
- (6) Military equipment
- (7) Any other equipment requiring extremely high levels of safety and/or reliability equal to the equipment listed above

*Notes: 1. There is a possibility that our products can be used only for aviation equipment that does not directly affect the safe operation of aircraft (e.g., in-flight entertainment, cabin light, electric seat, cooking equipment) if such use meets requirements specified separately by TAIYO YUDEN. Please be sure to contact TAIYO YUDEN for further information before using our products for such aviation equipment.

2. Implantable medical devices contain not only internal unit which is implanted in a body, but also external unit which is connected to the internal unit.

4. Limitation of Liability

Please note that unless you obtain prior written consent of TAIYO YUDEN, TAIYO YUDEN shall not be in any way responsible for any damages incurred by you or third parties arising from use of the products listed in this catalog for any equipment that is not intended for use by TAIYO YUDEN, or any equipment requiring inquiry to TAIYO YUDEN or prohibited for use by TAIYO YUDEN as described above.

Automotive Application Guide

We classify automotive electronic equipment into the following four application categories and set usable application categories for each of our products. Therefore, we have the corresponding product series (the part number code of 2nd digit from the left side is "A" or "C"). When using our products for automotive electronic equipment, please be sure to check such application categories and use the corresponding product series accordingly. Should you have any questions on this matter, please contact us.

Product Series (Part Number Code of 2nd digit from the Left Side)	Category	Automotive Electronic Equipment (Typical Example)
A	POWERTRAIN	<ul style="list-style-type: none"> • Engine ECU (Electronically Controlled Fuel Injector) • Cruise Control Unit • 4WS (4 Wheel Steering) • Transmission • Power Steering • HEV/PHV/EV Core Control (Battery, Inverter, DC-DC) • Automotive Locator (Car location information providing device), etc.
	SAFETY	<ul style="list-style-type: none"> • ABS (Anti-Lock Brake System) • ESC (Electronic Stability Control) • Airbag • ADAS (Equipment that directly controls running, turning and stopping), etc.
C	BODY & CHASSIS	<ul style="list-style-type: none"> • Wiper • Automatic Door • Power Window • Keyless Entry System • Electric Door Mirror • Automobile Digital Mirror • Interior Lighting • Automobile Air Conditioning System • TPMS (Tire Pressure Monitoring System) • Anti-Theft Device (Immobilizer), etc.
	INFOTAINMENT	<ul style="list-style-type: none"> • Car Infotainment System • ITS/Telematics System • Instrument Cluster • ADAS (Sensor, Equipment that is not interlocked with safety equipment or powertrain) • Dashcam (genuine products for automotive manufacturer), etc.

Wire-wound Metal Power Inductors MCOIL™ LCDN series for Automotive Body & Chassis and Infotainment

Code in front of Series have been extracted from Part number, which describes the segment of products, such as kinds and characteristics.

AEC-Q200 Grade 3 (we conduct the evaluation at the test condition of Grade 3.)

*Operating environment Temp:-40~85°C

REFLOW

AEC-Q200

PART NUMBER

*Operating Temp. : -40~125°C(Including self-generated heat)

L	C	D	N	D	2	0	2	0	K	K	T	1	R	0	M	M	
①	②	③	④	⑤	⑥	⑦	⑧	⑨									

①Series

Code (1)(2)(3)(4)	
LCDN	Wire-wound Metal Power Inductor for Automotive Body & Chassis and Infotainment

(1) Product Group

Code	
L	Inductors

(2) Category

Code	Recommended equipment	Quality Grade
C	Automotive Electronic Equipment (Body & Chassis, Infotainment)	2

②Features

Code	Feature
D	Bottom electrode (Ag x solder)

③Dimensions (L x W)

Code	Dimensions (L x W) [mm]
2020	2.0 x 2.0
3030	3.0 x 3.0
4040	4.0 x 4.0

④Dimensions (H)

Code	Dimensions (H) [mm]
KK	1.0
MK	1.2
WK	2.0

(3) Type

Code	
D	Metal Wire-wound (Drum type)

(4) Features, Characteristics

Code	
N	Standard Power choke

⑤Packaging

Code	Packaging
T	Taping

⑥Nominal inductance

Code (example)	Nominal inductance [μH]
R47	0.47
1R0	1.0
4R7	4.7

※R=Decimal point

⑦Inductance tolerance


Code	Inductance tolerance
M	±20%
N	±30%

⑧Special code

Code	Special code
F	Ferrite coating
M	Metal coating

⑨Internal code

■ STANDARD EXTERNAL DIMENSIONS



Type	A	B	C
2020	0.65	1.35	2.0
3030	0.8	2.2	2.7
4040	1.2	2.8	3.7

Unit: mm

Type	L	W	H	e	f	Standard quantity [pcs] Taping
2020KK	2.0±0.15 (0.079±0.006)	2.0±0.15 (0.079±0.006)	1.0 max (0.039 max)	0.50±0.2 (0.02±0.008)	1.25±0.2 (0.049±0.008)	2500
2020MK	2.0±0.15 (0.079±0.006)	2.0±0.15 (0.079±0.006)	1.2 max (0.047 max)	0.50±0.2 (0.02±0.008)	1.25±0.2 (0.049±0.008)	2500
3030KK	3.0±0.1 (0.118±0.004)	3.0±0.1 (0.118±0.004)	1.0 max (0.039 max)	0.90±0.2 (0.035±0.008)	1.9±0.2 (0.075±0.008)	2000
3030MK	3.0±0.1 (0.118±0.004)	3.0±0.1 (0.118±0.004)	1.2 max (0.047 max)	0.90±0.2 (0.035±0.008)	1.9±0.2 (0.075±0.008)	2000
4040MK	4.0±0.2 (0.157±0.008)	4.0±0.2 (0.157±0.008)	1.2 max (0.047 max)	1.1±0.2 (0.043±0.008)	2.5±0.2 (0.098±0.008)	1000
4040WK	4.0±0.2 (0.157±0.008)	4.0±0.2 (0.157±0.008)	2.0 max (0.079 max)	1.1±0.2 (0.043±0.008)	2.5±0.2 (0.098±0.008)	700

Unit: mm (inch)

■ PART NUMBER

• All the Wire-wound Metal Power Inductors of the catalog lineup are RoHS compliant.

Notes)

- The exchange of individual specifications is necessary depending on your application and/or circuit condition. Please contact TAIYO YUDEN's official sales channel.
- For Automotive (AEC-Q200 Qualified) products for BODY & CHASSIS, and INFOTAINMENT. Please check "Automotive Application Guide" for further details before using the products.

< AEC-Q200 :AEC-Q200 qualified>

All the Wire-wound Metal Power Inductors for Automotive products are tested based on the test conditions and methods defined in AEC-Q200 by family item.

Please consult with TAIYO YUDEN's official sales channel for the details of the product specifications and AEC-Q200 test results, etc., and please review and approve the product specifications before ordering.

● 2020KK type [Thickness: 1.0mm max]

New part number	Old part number (for reference)	Nominal inductance [μ H]	Inductance tolerance	DC Resistance [Ω] (max.)	Rated current ※) [mA]		Measuring frequency [MHz]
					Saturation current Idc1 Max (Typ)	Temperature rise current Idc2 Max (Typ)	
LCDND2020KKT4R7MM	MDKK2020TR47MM V	0.47	±20%	0.046	3,500 (4,150)	2,200 (2,500)	1
LCDND2020KKT68MM	MDKK2020TR68MM V	0.68	±20%	0.060	3,200 (3,650)	2,000 (2,100)	1
LCDND2020KKT1R0MM	MDKK2020T1R0MM V	1	±20%	0.085	2,900 (3,400)	1,700 (1,900)	1
LCDND2020KKT1R5MM	MDKK2020T1R5MM V	1.5	±20%	0.133	1,900 (2,250)	1,350 (1,500)	1
LCDND2020KKT2R2MM	MDKK2020T2R2MM V	2.2	±20%	0.165	1,650 (1,950)	1,200 (1,350)	1
LCDND2020KKT3R3MM	MDKK2020T3R3MM V	3.3	±20%	0.275	1,300 (1,550)	940 (1,050)	1
LCDND2020KKT4R7MM	MDKK2020T4R7MM V	4.7	±20%	0.435	1,050 (1,250)	750 (850)	1
LCDND2020KKT100MM	MDKK2020T100MM V	10	±20%	0.690	750 (900)	630 (680)	1

Absolute maximum voltage: DC20V

● 2020MK type [Thickness: 1.2mm max]

New part number	Old part number (for reference)	Nominal inductance [μ H]	Inductance tolerance	DC Resistance [Ω] (max.)	Rated current ※) [mA]		Measuring frequency [MHz]
					Saturation current Idc1 Max (Typ)	Temperature rise current Idc2 Max (Typ)	
LCDND2020MKTR47MM	MDMK2020TR47MM V	0.47	±20%	0.046	4,200 (4,800)	2,300 (2,450)	1
LCDND2020MKTR68MM	MDMK2020TR68MM V	0.68	±20%	0.058	3,500 (4,100)	2,000 (2,200)	1
LCDND2020MKT1R0MM	MDMK2020T1R0MM V	1	±20%	0.064	2,550 (2,900)	1,900 (2,050)	1
LCDND2020MKT1R5MM	MDMK2020T1R5MM V	1.5	±20%	0.086	2,000 (2,300)	1,650 (1,750)	1
LCDND2020MKT2R2MM	MDMK2020T2R2MM V	2.2	±20%	0.109	1,750 (2,000)	1,450 (1,550)	1
LCDND2020MKT3R3MM	MDMK2020T3R3MM V	3.3	±20%	0.178	1,350 (1,550)	1,150 (1,200)	1
LCDND2020MKT4R7MM	MDMK2020T4R7MM V	4.7	±20%	0.242	1,150 (1,300)	950 (1,050)	1

Absolute maximum voltage: DC20V

● 3030KK type [Thickness: 1.0mm max]

New part number	Old part number (for reference)	Nominal inductance [μ H]	Inductance tolerance	DC Resistance [Ω] (max.)	Rated current ※) [mA]		Measuring frequency [MHz]
					Saturation current Idc1 Max (Typ)	Temperature rise current Idc2 Max (Typ)	
LCDND3030KKT4R7MM	MDKK3030TR47MM V	0.47	±20%	0.039	5,400 (6,500)	3,900 (4,500)	1
LCDND3030KKT1R0MM	MDKK3030T1R0MM V	1.0	±20%	0.086	4,400 (5,200)	2,400 (2,800)	1
LCDND3030KKT1R5MM	MDKK3030T1R5MM V	1.5	±20%	0.100	3,000 (3,500)	2,100 (2,400)	1
LCDND3030KKT2R2MM	MDKK3030T2R2MM V	2.2	±20%	0.144	2,500 (3,000)	1,900 (2,200)	1
LCDND3030KKT3R3MM	MDKK3030T3R3MM V	3.3	±20%	0.248	2,000 (2,400)	1,350 (1,500)	1
LCDND3030KKT4R7MM	MDKK3030T4R7MM V	4.7	±20%	0.345	1,700 (2,000)	1,150 (1,300)	1
LCDND3030KKT6R8MM	MDKK3030T6R8MM V	6.8	±20%	0.437	1,400 (1,700)	1,000 (1,150)	1
LCDND3030KKT100MM	MDKK3030T100MM V	10	±20%	0.575	1,100 (1,300)	850 (1,000)	1

Absolute maximum voltage: DC20V

● 3030MK type [Thickness: 1.2mm max]

New part number	Old part number (for reference)	Nominal inductance [μ H]	Inductance tolerance	DC Resistance [Ω] (max.)	Rated current ※) [mA]		Measuring frequency [MHz]
					Saturation current Idc1 Max (Typ)	Temperature rise current Idc2 Max (Typ)	
LCDND3030MKTR30MM	MDMK3030TR30MM V	0.30	±20%	0.020	7,600 (9,200)	5,500 (6,400)	1
LCDND3030MKTR33MM	MDMK3030TR33MM V	0.33	±20%	0.020	6,400 (8,700)	5,500 (6,400)	1
LCDND3030MKTR47MM	MDMK3030TR47MM V	0.47	±20%	0.027	6,300 (7,500)	4,700 (5,500)	1
LCDND3030MKT1R0MM	MDMK3030T1R0MM V	1.0	±20%	0.050	4,300 (5,100)	3,300 (3,900)	1
LCDND3030MKT1R5MM	MDMK3030T1R5MM V	1.5	±20%	0.074	3,400 (4,100)	2,500 (3,000)	1
LCDND3030MKT2R2MM	MDMK3030T2R2MM V	2.2	±20%	0.112	2,800 (3,600)	2,100 (2,400)	1
LCDND3030MKT3R3MM	MDMK3030T3R3MM V	3.3	±20%	0.173	2,100 (2,700)	1,650 (1,900)	1
LCDND3030MKT4R7MM	MDMK3030T4R7MM V	4.7	±20%	0.263	1,800 (2,300)	1,350 (1,550)	1

Absolute maximum voltage: DC20V

※) The saturation current value (Idc1) is the DC current value having inductance decrease down to 30%. (at 20°C)

※1-1) The temperature rise current value (Idc2) is the DC current value having temperature increase by 40°C, when mounted in FR4 High heat dissipation board (board thickness: 1.0mm copper thickness: 0.035mm, board size: 110 × 30 × 1.0mm, land size: 12.6 × 19.6mm). (at 20°C)

※1-2) The temperature rise current value (Idc2) is the DC current value having temperature increase by 40°C, when mounted in FR4 High heat dissipation board (board thickness: 1.6mm copper thickness: 0.050mm, board size: 100 × 100 × 1.6mm, land size: 14.6 × 43mm). (at 20°C)

※1-3) The temperature rise current value (Idc2) is the DC current value having temperature increase by 40°C, when mounted in FR4 High heat dissipation board (board thickness: 1.6mm copper thickness: 0.050mm, board size: 100 × 100 × 1.6mm, land size: 44.5 × 90mm). (at 20°C)

※) The rated current is the DC current value that satisfies both of current value saturation current value and temperature rise current value.

※1-1) 2020KK, 2020MK type

※1-2) 3030KK, 3030MK type

※1-3) 4040MK, 4040WK type

PART NUMBER

● 4040MK F type [Thickness: 1.2mm max]

New part number	Old part number (for reference)	Nominal inductance [μ H]	Inductance tolerance	DC Resistance [Ω] (max.)	Rated current ※) [mA]		Measuring frequency [kHz]
					Saturation current Idc1 Max (Typ)	Temperature rise current Idc2 Max (Typ)	
LCDND4040MKT1R47MF	MDMK4040TR47MF V	0.47	$\pm 20\%$	0.029	7,500 (10,000)	4,600 (5,400)	100
LCDND4040MKT1R0MF	MDMK4040T1R0MF V	1.0	$\pm 20\%$	0.047	5,200 (7,500)	3,500 (4,200)	100
LCDND4040MKT1R2MF	MDMK4040T1R2MF V	1.2	$\pm 20\%$	0.047	4,200 (6,200)	3,500 (4,200)	100
LCDND4040MKT1R5MF	MDMK4040T1R5MF V	1.5	$\pm 20\%$	0.065	3,700 (5,400)	3,300 (3,600)	100
LCDND4040MKT2R2MF	MDMK4040T2R2MF V	2.2	$\pm 20\%$	0.092	3,200 (4,500)	2,500 (2,900)	100

Absolute maximum voltage: DC25V

● 4040MK type [Thickness: 1.2mm max]

New part number	Old part number (for reference)	Nominal inductance [μ H]	Inductance tolerance	DC Resistance [Ω] (max.)	Rated current ※) [mA]		Measuring frequency [MHz]
					Saturation current Idc1 Max (Typ)	Temperature rise current Idc2 Max (Typ)	
LCDND4040MKT1R68MM	MDMK4040TR68MM V	0.68	$\pm 20\%$	0.029	6,700 (7,800)	5,000 (5,700)	1
LCDND4040MKT1R0MM	MDMK4040T1R0MM V	1.0	$\pm 20\%$	0.036	5,000 (6,200)	4,500 (5,100)	1
LCDND4040MKT1R5MM	MDMK4040T1R5MM V	1.5	$\pm 20\%$	0.065	4,500 (5,600)	3,200 (3,600)	1
LCDND4040MKT2R2MM	MDMK4040T2R2MM V	2.2	$\pm 20\%$	0.079	3,800 (4,500)	2,800 (3,200)	1
LCDND4040MKT3R3MM	MDMK4040T3R3MM V	3.3	$\pm 20\%$	0.130	3,200 (4,000)	2,200 (2,500)	1
LCDND4040MKT4R7MM	MDMK4040T4R7MM V	4.7	$\pm 20\%$	0.160	2,500 (3,000)	1,900 (2,200)	1
LCDND4040MKT6R8MM	MDMK4040T6R8MM V	6.8	$\pm 20\%$	0.230	1,900 (2,200)	1,600 (1,800)	1
LCDND4040MKT100MM	MDMK4040T100MM V	10	$\pm 20\%$	0.330	1,700 (2,000)	1,400 (1,600)	1

Absolute maximum voltage: DC25V

● 4040WK type [Thickness: 2.0mm max]

New part number	Old part number (for reference)	Nominal inductance [μ H]	Inductance tolerance	DC Resistance [Ω] (max.)	Rated current ※) [mA]		Measuring frequency [MHz]
					Saturation current Idc1 Max (Typ)	Temperature rise current Idc2 Max (Typ)	
LCDND4040WKT1R56NM	MDWK4040TR56NM V	0.56	$\pm 20\%$	0.016	9,000 (13,000)	6,500 (7,500)	1
LCDND4040WKT1R68MM	MDWK4040TR68MM V	0.68	$\pm 20\%$	0.016	8,000 (12,000)	7,300 (8,300)	1
LCDND4040WKT1R0MM	MDWK4040T1R0MM V	1.0	$\pm 20\%$	0.027	7,000 (9,400)	5,100 (5,800)	1
LCDND4040WKT1R5MM	MDWK4040T1R5MM V	1.5	$\pm 20\%$	0.041	7,000 (9,400)	4,100 (4,700)	1
LCDND4040WKT2R2MM	MDWK4040T2R2MM V	2.2	$\pm 20\%$	0.054	5,400 (7,500)	3,500 (4,000)	1
LCDND4040WKT3R3MM	MDWK4040T3R3MM V	3.3	$\pm 20\%$	0.075	3,700 (5,200)	3,000 (3,300)	1
LCDND4040WKT4R7MM	MDWK4040T4R7MM V	4.7	$\pm 20\%$	0.107	3,500 (5,000)	2,500 (2,800)	1
LCDND4040WKT6R8MM	MDWK4040T6R8MM V	6.8	$\pm 20\%$	0.158	2,900 (4,000)	2,000 (2,300)	1
LCDND4040WKT100MM	MDWK4040T100MM V	10	$\pm 20\%$	0.194	2,200 (3,100)	1,600 (1,900)	1

Absolute maximum voltage: DC25V

※) The saturation current value (Idc1) is the DC current value having inductance decrease down to 30%. (at 20°C)

※1-1) The temperature rise current value (Idc2) is the DC current value having temperature increase by 40°C, when mounted in FR4 High heat dissipation board (board thickness: 1.0mm copper thickness: 0.035mm, board size: 110 × 30 × 1.0mm, land size: 12.6 × 19.6mm). (at 20°C)

※1-2) The temperature rise current value (Idc2) is the DC current value having temperature increase by 40°C, when mounted in FR4 High heat dissipation board (board thickness: 1.6mm copper thickness: 0.050mm, board size: 100 × 100 × 1.6mm, land size: 14.6 × 43mm). (at 20°C)

※1-3) The temperature rise current value (Idc2) is the DC current value having temperature increase by 40°C, when mounted in FR4 High heat dissipation board (board thickness: 1.6mm copper thickness: 0.050mm, board size: 100 × 100 × 1.6mm, land size: 44.5 × 90mm). (at 20°C)

※) The rated current is the DC current value that satisfies both of current value saturation current value and temperature rise current value.

※1-1) 2020KK, 2020MK type







※1-2) 3030KK, 3030MK type

※1-3) 4040MK, 4040WK type

Derating of Rated Current

●LCDN series

Derating of current is necessary for LCDN series depending on ambient temperature.
Please refer to the chart shown below for appropriate derating of current.



Wire-wound Metal Power Inductors MCOIL™ LSDN/LCDN/LBDN/LLDN/LMDN series


PACKAGING

① Minimum Quantity

Type	Standard Quantity [pcs]
	Tape & Reel
1616KK	2500
2020JE	2500
2020KK	
2020MK	
3030KK	2000
3030MK	
4040JE	1000
4040MK	
4040WK	
5050PK	1000


② Tape Material

● Embossed Tape



③ Taping dimensions

● Embossed tape 8mm wide (0.315 inches wide)




Type	Chip cavity		Insertion pitch	Tape thickness	
	A	B	F	T	K
1616KK	1.79 ± 0.1 (0.071 ± 0.004)	1.79 ± 0.1 (0.071 ± 0.004)	4.0 ± 0.1 (0.157 ± 0.004)	0.25 ± 0.05 (0.010 ± 0.002)	1.1 ± 0.1 (0.043 ± 0.004)
2020JE	2.2 ± 0.1 (0.102 ± 0.004)	2.2 ± 0.1 (0.102 ± 0.004)	4.0 ± 0.1 (0.157 ± 0.004)	0.25 ± 0.05 (0.009 ± 0.002)	1.3 ± 0.1 (0.051 ± 0.004)
2020KK					
2020MK					
3030KK	3.2 ± 0.1 (0.126 ± 0.004)	3.2 ± 0.1 (0.126 ± 0.004)	4.0 ± 0.1 (0.157 ± 0.004)	0.3 ± 0.05 (0.012 ± 0.002)	1.4 ± 0.1 (0.055 ± 0.004)
3030MK					

Unit : mm (inch)

▶ This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (<http://www.ty-top.com/>).


● Embossed tape 12mm wide (0.47 inches wide)



Type	Chip cavity		Insertion pitch F	Tape thickness	
	A	B		T	K
4040JE	4.3 ± 0.1 (0.169 ± 0.004)	4.3 ± 0.1 (0.169 ± 0.004)	8.0 ± 0.1 (0.315 ± 0.004)	0.3 ± 0.05 (0.012 ± 0.002)	1.6 ± 0.1 (0.063 ± 0.004)
4040MK	4.3 ± 0.1 (0.169 ± 0.004)	4.3 ± 0.1 (0.169 ± 0.004)	8.0 ± 0.1 (0.315 ± 0.004)	0.3 ± 0.05 (0.012 ± 0.002)	2.3 ± 0.1 (0.091 ± 0.004)
5050PK	5.25 ± 0.1 (0.207 ± 0.004)	5.25 ± 0.1 (0.207 ± 0.004)	8.0 ± 0.1 (0.315 ± 0.004)	0.3 ± 0.1 (0.012 ± 0.004)	1.6 ± 0.1 (0.063 ± 0.004)


Unit: mm (inch)

④ Leader and Blank portion



► This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (<http://www.ty-top.com/>).

⑤ Reel size




Type	Reel size (Reference values)		
	ϕD	ϕd	W
1616KK	180±0.5 (7.087±0.019)	60±1.0 (2.36±0.04)	10.0±1.5 (0.394±0.059)
2020JE			
2020KK			
2020MK			
3030KK	180±3.0 (7.087±0.118)	60±2.0 (2.36±0.08)	14.0±1.5 (0.551±0.059)
3030MK			
4040JE	180±3.0 (7.087±0.118)	60±2.0 (2.36±0.08)	14.0±1.5 (0.551±0.059)
4040MK			
4040WK			
5050PK			

Unit: mm (inch)

⑥ Top Tape Strength

Top tape strength


Type	Peel-off strength
MDKK1616	0.1N~1.0N
MDJE2020	
MDKK2020	
MDMK2020	
MDKK3030	0.1N~1.3N
MDMK3030	
MDJE4040	
MDMK4040	
MDWK4040	
MDPK5050	



▶ This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (<http://www.ty-top.com/>).

**Wire-wound Metal Power Inductors MCOIL™ LCDN series
for Automotive Body & Chassis and Infotainment**
**Wire-wound Metal Power Inductors MCOIL™ LBDN series
for Telecommunications Infrastructure and Industrial Equipment**
**Wire-wound Metal Power Inductors MCOIL™ LMDN series
for Medical Devices classified as GHTF Class C (Japan Class III)**

■ RELIABILITY DATA

1. Operating Temperature Range	
Specified Value	-40~+125°C (Including self-generated heat)
Test Methods and Remarks	Including self-generated heat
2. Storage Temperature Range	
Specified Value	-40~+85°C
Test Methods and Remarks	-5 to 40°C for the product with taping.
3. Rated current	
Specified Value	Within the specified tolerance
4. Inductance	
Specified Value	Within the specified tolerance
Test Methods and Remarks	Measuring equipment : LCR Meter (HP 4285A or equivalent) Measuring frequency : 1MHz 1V (4040F:100kHz 1V)
5. DC Resistance	
Specified Value	Within the specified tolerance
Test Methods and Remarks	Measuring equipment : DC ohmmeter (HIOKI 3227 or equivalent)
6. Self resonance frequency	
Specified Value	—
7. Temperature characteristic	
Specified Value	Inductance change : Within ±10%
Test Methods and Remarks	Measurement of inductance shall be taken at temperature range within -40°C~+125°C. With reference to inductance value at +20°C., change rate shall be calculated.
8. Resistance to flexure of substrate	
Specified Value	No damage
Test Methods and Remarks	The test samples shall be soldered to the test board by the reflow. As illustrated below, apply force in the direction of the arrow indicating until deflection of the test board reaches to 2 mm. Test board size : 100 × 40 × 1.6 mm Test board material : glass epoxy-resin Solder cream thickness : 0.10 mm <div style="text-align: right;">  </div>
9. Insulation resistance : between wires	
Specified Value	—

▶ This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification.
 For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (<http://www.ty-top.com/>).

10. Insulation resistance : between wire and core

Specified Value	—
-----------------	---

11. Withstanding voltage : between wire and core

Specified Value	—
-----------------	---

12. Adhesion of terminal electrode

Specified Value	Shall not come off PC board
Test Methods and Remarks	The test samples shall be soldered to the test board by the reflow. Applied force : 10N to X and Y directions. Duration : 5s. Solder cream thickness : 0.1mm.

13. Resistance to vibration

Specified Value	Inductance change : Within $\pm 10\%$ No significant abnormality in appearance.														
Test Methods and Remarks	The test samples shall be soldered to the test board by the reflow. Then it shall be submitted to below test conditions. <table border="1" style="width: 100%;"> <tr> <td>Frequency Range</td> <td colspan="2">10~55Hz</td> </tr> <tr> <td>Total Amplitude</td> <td colspan="2">1.5mm (May not exceed acceleration 196m/s²)</td> </tr> <tr> <td>Sweeping Method</td> <td colspan="2">10Hz to 55Hz to 10Hz for 1min.</td> </tr> <tr> <td rowspan="3">Time</td> <td>X</td> <td rowspan="3">For 2 hours on each X, Y, and Z axis.</td> </tr> <tr> <td>Y</td> </tr> <tr> <td>Z</td> </tr> </table> Recovery : At least 2hrs of recovery under the standard condition after the test, followed by the measurement within 48hrs.	Frequency Range	10~55Hz		Total Amplitude	1.5mm (May not exceed acceleration 196m/s ²)		Sweeping Method	10Hz to 55Hz to 10Hz for 1min.		Time	X	For 2 hours on each X, Y, and Z axis.	Y	Z
Frequency Range	10~55Hz														
Total Amplitude	1.5mm (May not exceed acceleration 196m/s ²)														
Sweeping Method	10Hz to 55Hz to 10Hz for 1min.														
Time	X	For 2 hours on each X, Y, and Z axis.													
	Y														
	Z														

14. Solderability

Specified Value	At least 90% of surface of terminal electrode is covered by new solder.				
Test Methods and Remarks	The test samples shall be dipped in flux, and then immersed in molten solder as shown in below table. Flux : Ethanol solution containing rosin 25%. <table border="1" style="width: 100%;"> <tr> <td>Solder Temperature</td> <td>245\pm5$^{\circ}$C</td> </tr> <tr> <td>Time</td> <td>5\pm1.0 sec.</td> </tr> </table> ※Immersion depth : All sides of mounting terminal shall be immersed.	Solder Temperature	245 \pm 5 $^{\circ}$ C	Time	5 \pm 1.0 sec.
Solder Temperature	245 \pm 5 $^{\circ}$ C				
Time	5 \pm 1.0 sec.				

15. Resistance to soldering heat

Specified Value	Inductance change : Within $\pm 10\%$ No significant abnormality in appearance.
Test Methods and Remarks	The test sample shall be exposed to reflow oven at 230 \pm 5 $^{\circ}$ C for 40 seconds, with peak temperature at 260 \pm 5 $^{\circ}$ C for 5 seconds, 2 times. Test board material : glass epoxy-resin Test board thickness : 1.0mm

16. Thermal shock

Specified Value	Inductance change : Within $\pm 10\%$ No significant abnormality in appearance.																		
Test Methods and Remarks	The test samples shall be soldered to the test board by the reflow. The test samples shall be placed at specified temperature for specified time by step 1 to step 4 as shown in below table in sequence. The temperature cycle shall be repeated 1000 cycles. <table border="1" style="width: 100%;"> <thead> <tr> <th colspan="3">Conditions of 1 cycle</th> </tr> <tr> <th>Step</th> <th>Temperature ($^{\circ}$C)</th> <th>Duration (min)</th> </tr> </thead> <tbody> <tr> <td>1</td> <td>-40\pm3</td> <td>30\pm3</td> </tr> <tr> <td>2</td> <td>Room temperature</td> <td>Within 3</td> </tr> <tr> <td>3</td> <td>+85\pm2</td> <td>30\pm3</td> </tr> <tr> <td>4</td> <td>Room temperature</td> <td>Within 3</td> </tr> </tbody> </table>	Conditions of 1 cycle			Step	Temperature ($^{\circ}$ C)	Duration (min)	1	-40 \pm 3	30 \pm 3	2	Room temperature	Within 3	3	+85 \pm 2	30 \pm 3	4	Room temperature	Within 3
Conditions of 1 cycle																			
Step	Temperature ($^{\circ}$ C)	Duration (min)																	
1	-40 \pm 3	30 \pm 3																	
2	Room temperature	Within 3																	
3	+85 \pm 2	30 \pm 3																	
4	Room temperature	Within 3																	

▶ This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (<http://www.ty-top.com/>).

17. Damp heat

Specified Value	Inductance change : Within $\pm 10\%$ No significant abnormality in appearance.						
Test Methods and Remarks	The test samples shall be soldered to the test board by the reflow.						
	The test samples shall be placed in thermostatic oven set at specified temperature and humidity as shown in below table.						
	<table border="1"> <tr> <td>Temperature</td> <td>$60 \pm 2^\circ\text{C}$</td> </tr> <tr> <td>Humidity</td> <td>90~95%RH</td> </tr> <tr> <td>Time</td> <td>1000+24/-0 hour</td> </tr> </table>	Temperature	$60 \pm 2^\circ\text{C}$	Humidity	90~95%RH	Time	1000+24/-0 hour
	Temperature	$60 \pm 2^\circ\text{C}$					
Humidity	90~95%RH						
Time	1000+24/-0 hour						

18. Loading under damp heat

Specified Value	Inductance change : Within $\pm 10\%$ No significant abnormality in appearance.								
Test Methods and Remarks	The test samples shall be soldered to the test board by the reflow.								
	The test samples shall be placed in thermostatic oven set at specified temperature and humidity and applied the rated current continuously as shown in below table.								
	<table border="1"> <tr> <td>Temperature</td> <td>$60 \pm 2^\circ\text{C}$</td> </tr> <tr> <td>Humidity</td> <td>90~95%RH</td> </tr> <tr> <td>Applied current</td> <td>Rated current</td> </tr> <tr> <td>Time</td> <td>1000+24/-0 hour</td> </tr> </table>	Temperature	$60 \pm 2^\circ\text{C}$	Humidity	90~95%RH	Applied current	Rated current	Time	1000+24/-0 hour
	Temperature	$60 \pm 2^\circ\text{C}$							
	Humidity	90~95%RH							
Applied current	Rated current								
Time	1000+24/-0 hour								

19. Low temperature life test

Specified Value	Inductance change : Within $\pm 10\%$ No significant abnormality in appearance.				
Test Methods and Remarks	The test samples shall be soldered to the test board by the reflow. After that, the test samples shall be placed at test conditions as shown in below table.				
	<table border="1"> <tr> <td>Temperature</td> <td>$-40 \pm 2^\circ\text{C}$</td> </tr> <tr> <td>Time</td> <td>1000+24/-0 hour</td> </tr> </table>	Temperature	$-40 \pm 2^\circ\text{C}$	Time	1000+24/-0 hour
	Temperature	$-40 \pm 2^\circ\text{C}$			
	Time	1000+24/-0 hour			

20. High temperature life test

Specified Value	—
-----------------	---

21. Loading at high temperature life test

Specified Value	Inductance change : Within $\pm 10\%$ No significant abnormality in appearance.						
Test Methods and Remarks	The test samples shall be soldered to the test board by the reflow.						
	The test samples shall be placed in thermostatic oven set at specified temperature and applied the rated current continuously as shown in below table.						
	<table border="1"> <tr> <td>Temperature</td> <td>$85 \pm 2^\circ\text{C}$</td> </tr> <tr> <td>Applied current</td> <td>Rated current</td> </tr> <tr> <td>Time</td> <td>1000+24/-0 hour</td> </tr> </table>	Temperature	$85 \pm 2^\circ\text{C}$	Applied current	Rated current	Time	1000+24/-0 hour
	Temperature	$85 \pm 2^\circ\text{C}$					
	Applied current	Rated current					
Time	1000+24/-0 hour						

22. Standard condition

Specified Value	Standard test condition : Unless otherwise specified, temperature is $20 \pm 15^\circ\text{C}$ and $65 \pm 20\%$ of relative humidity. When there is any question concerning measurement result: In order to provide correlation data, the test shall be condition of $20 \pm 2^\circ\text{C}$ of temperature, $65 \pm 5\%$ relative humidity. Inductance is in accordance with our measured value.
-----------------	--

► This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification.
For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (<http://www.ty-top.com/>).

Wire-wound Metal Power Inductors MCOIL™ LSDN/LCDN/LBDN/LLDN/LMDN series

■ PRECAUTIONS

1. Circuit Design	
Precautions	<ul style="list-style-type: none"> ◆ Verification of operating environment, electrical rating and performance <ol style="list-style-type: none"> 1. A malfunction in medical equipment, spacecraft, nuclear reactors, etc. may cause serious harm to human life or have severe social ramifications. As such, any inductors to be used in such equipment may require higher safety and/or reliability considerations and should be clearly differentiated from components used in general purpose applications. 2. When inductors are used in places where dew condensation develops and/or where corrosive gas such as hydrogen sulfide, sulfurous acid, or chlorine exists in the air, characteristic deterioration may occur. Please do not use inductors under such environmental conditions. ◆ Operating Current (Verification of Rated current) <ol style="list-style-type: none"> 1. The operating current including inrush current for inductors must always be lower than their rated values. 2. Do not apply current in excess of the rated value because the inductance may be reduced due to the magnetic saturation effect. ◆ Temperature rise <p>Temperature rise of power choke coil depends on the installation condition in end products. Make sure that temperature rise of power choke coils in actual end products is within the specified temperature range.</p>
2. PCB Design	
Precautions	<ul style="list-style-type: none"> ◆ Land pattern design <ol style="list-style-type: none"> 1. Please refer to a recommended land pattern.
Technical considerations	<ul style="list-style-type: none"> ◆ Land pattern design <ul style="list-style-type: none"> Surface Mounting <ul style="list-style-type: none"> • Mounting and soldering conditions should be checked beforehand. • Applicable soldering process to this products is reflow soldering only.
3. Considerations for automatic placement	
Precautions	<ul style="list-style-type: none"> ◆ Adjustment of mounting machine <ol style="list-style-type: none"> 1. Excessive impact load should not be imposed on the products when mounting onto the PC boards. 2. Mounting and soldering conditions should be checked beforehand.
Technical considerations	<ul style="list-style-type: none"> ◆ Adjustment of mounting machine <ol style="list-style-type: none"> 1. When installing products, care should be taken not to apply distortion stress as it may deform the products.
4. Soldering	
Precautions	<ul style="list-style-type: none"> ◆ Reflow soldering <ol style="list-style-type: none"> 1. Please contact any of our offices for a reflow soldering, and refer to the recommended condition specified. 2. The product shall be used reflow soldering only. 3. Please do not add any stress to a product until it returns in normal temperature after reflow soldering. ◆ Lead free soldering <ol style="list-style-type: none"> 1. When using products with lead free soldering, we request to use them after confirming adhesion, temperature of resistance to soldering heat, soldering etc sufficiently. ◆ Recommended conditions for using a soldering iron (NR10050 Type) <ul style="list-style-type: none"> • Put the soldering iron on the land-pattern. • Soldering iron's temperature - Below 350°C • Duration - 3 seconds or less • The soldering iron should not directly touch the inductor.
Technical considerations	<ul style="list-style-type: none"> ◆ Reflow soldering <ol style="list-style-type: none"> 1. If products are used beyond the range of the recommended conditions, heat stresses may deform the products, and consequently degrade the reliability of the products. <ul style="list-style-type: none"> • NR30/40/50/60/80, NRV20/30, NRH24/30, NRS20/40/50/60/80 Type, NR10050 Type, NS101/125 Type <p>Recommended reflow condition (Pb free solder)</p>

▶ This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (<http://www.ty-top.com/>).

5. Cleaning	
Precautions	<ul style="list-style-type: none"> ◆ Cleaning conditions 1. Washing by supersonic waves shall be avoided.
Technical considerations	<ul style="list-style-type: none"> ◆ Cleaning conditions 1. If washed by supersonic waves, the products might be broken.
6. Handling	
Precautions	<ul style="list-style-type: none"> ◆ Handling 1. Keep the product away from all magnets and magnetic objects. ◆ Breakaway PC boards (splitting along perforations) 1. When splitting the PC board after mounting product, care should be taken not to give any stresses of deflection or twisting to the board. 2. Board separation should not be done manually, but by using the appropriate devices. ◆ Mechanical considerations 1. Please do not give the product any excessive mechanical shocks. 2. Please do not add any shock and power to a product in transportation. ◆ Pick-up pressure 1. Please do not push to add any pressure to a winding part. Please do not give any shock and push into a ferrite core exposure part. ◆ Packing 1. Please avoid accumulation of a packing box as much as possible. ◆ Board mounting 1. There shall be no pattern or via between terminals at the bottom of product. 2. Components which are located in peripheral of product shall not make contact with surface (top, side) of product.
Technical considerations	<ul style="list-style-type: none"> ◆ Handling 1. There is a case that a characteristic varies with magnetic influence. ◆ Breakaway PC boards (splitting along perforations) 1. The position of the product on PCBs shall be carefully considered to minimize the stress caused from splitting of the PCBs. ◆ Mechanical considerations 1. There is a case to be damaged by a mechanical shock. 2. There is a case to be broken by the handling in transportation. ◆ Pick-up pressure 1. Damage and a characteristic can vary with an excessive shock or stress. ◆ Packing 1. If packing boxes are accumulated, that could cause a deformation on packing tapes or a damage on the products. ◆ Board mounting 1. If there is pattern or via between terminals at the bottom of product, it may cause characteristics change. 2. If components which are located in peripheral of product make contact with surface (top, side) of product, it may cause damage or characteristics change.
7. Storage conditions	
Precautions	<ul style="list-style-type: none"> ◆ Storage 1. To maintain the solderability of terminal electrodes and to keep the packing material in good condition, temperature and humidity in the storage area should be controlled. <ul style="list-style-type: none"> ▪ Recommended conditions Ambient temperature : $-5\sim 40^{\circ}\text{C}$ Humidity : Below 70% RH ▪ The ambient temperature must be kept below 30°C. Even under ideal storage conditions, solderability of products electrodes may decrease as time passes. For this reason, product should be used within 6 months from the time of delivery. In case of storage over 6 months, solderability shall be checked before actual usage.
Technical considerations	<ul style="list-style-type: none"> ◆ Storage 1. Under a high temperature and humidity environment, problems such as reduced solderability caused by oxidation of terminal electrodes and deterioration of taping/packaging materials may take place.