

3M™ Toe Grounder

Toe Grounder

Fits high heels and shoes when heel grounders won't. Made in the USA, this quality grounder features a durable three layer sole, lot number, and 12 inch multi-strand ribbon. 3M uses time-tested construction techniques including computer controlled stitching, riveting, die cutting, and heat cutting to ensure consistent performance.

Standards

Meets the requirements of ANSI/ESD S-20.20, EIA 625, MIL-STD-1686, and MIL-HDBK-263.

Specifications


Resistor: 1 megohm
 Color: Black
 Ribbon: Multi-strand, carbon suffused nylon on polyester, sewn in sinusoidal pattern to provide side to side conductivity.
 Hook and Loop: 3/4" Black
 Elastic Strap: 3/4" Black
 Sole Exterior: 10^5 ohms

Part Numbers

TG1M Toe Grounder, 1 meg resistor

See 3M Data Sheets for these related items:

3M™ Foot Grounder Tester
 3M™ Floor Mats



How Foot Grounders Work

Foot grounders discharge static from a person to ground by connecting the person to a grounded walking surface. A conductive ribbon placed inside the wearer's shoe or sock makes electrical contact with the skin through perspiration. The ribbon is joined to a resistor which limits current should accidental exposure to electricity occur. The other end of the resistor is joined to a conductive sole. This sole contacts a grounded ESD floor mat or ESD flooring system. Foot grounders must be worn on both feet to maintain ground contact while walking.

P R O D U C T D A T A S H E E T

Toe Grounder

PRODUCT
 TOE GROUNDER

ITEM NUMBER
 SEE ABOVE

DATASHEET
 1130-A

3M Electronic Solutions Division
 6801 River Place Blvd.
 Austin, TX 78726-9000
 US and Canada: 866-722-3736
 Fax: 866-722-3735
 Intl: 919-718-0000; Fax: 919-774-8174
 email: 3Mstaticinfo@mmm.com; www.3M.com/static

3M is a trademark of 3M Company.
 All other trademarks herein are the property
 of their respective owners.

© 2008

